

PRODUCT CHARACTERISTICS

VDSS	650V
$R_{DS(on)max}(V_{GS}=10V)$	2.2Ω
Qg@type	25nC
ID	5A



APPLICATIONS

- * High frequency switching mode power supply
- * Electronic ballast
- * LED power supplies


FEATURES

- * $R_{DS(ON)} \leq 2.2\Omega$ @ $V_{GS}=10V$
- * High Switching Speed

Symbol



TO-252



TO-251

ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT5N65D	TO-252	2500 pieces /Reel
N/A	MOT5N65C	TO-251	70 pieces/Tube

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V_{DSS}	650	V
Gate-Source Voltage		V_{GSS}	±30	V
Drain Current	Continuous	I_D	5	A
	Pulsed (Note 2)	I_{DM}	10	A
Avalanche Energy	Single Pulsed (Note 3)	E_{AS}	112	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	3.2	V/ns
Power Dissipation	TO-251/252	P_D	54	W
Junction Temperature		T_J	+150	°C
Storage Temperature		T_{STG}	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating: Pulse width limited by maximum junction temperature.

3. $L = 10\text{mH}$, $I_{AS} = 4.73\text{A}$, $V_{DD} = 50\text{V}$, $R_G = 25\Omega$ Starting $T_J = 25^\circ\text{C}$

4. $I_{SD} \leq 7.0\text{A}$, $di/dt \leq 200\text{A}/\mu\text{s}$, $V_{DD} \leq BV_{DSS}$, Starting $T_J = 25^\circ\text{C}$


■ ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$, unless otherwise specified)

PARAMETER		SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage		BV _{DSS}	V _{GS} =0V, I _D = 250μA	650			V
Drain-Source Leakage Current		I _{DSS}	V _{DS} =650V, V _{GS} =0V			10	μA
Gate-Source Leakage Current	Forward	I _{GSS}	V _{GS} =30V, V _{DS} =0V			100	nA
	Reverse		V _{GS} =-30V, V _{DS} =0V			-100	nA
ON CHARACTERISTICS							
Gate Threshold Voltage		V _{GS(TH)}	V _{DS} =V _{GS} , I _D =250μA	2.0		4.0	V
Static Drain-Source On-State Resistance		R _{DS(ON)}	V _{GS} =10V, I _D =2.5A		1.92	2.2	Ω
DYNAMIC CHARACTERISTICS							
Input Capacitance		C _{ISS}	V _{GS} =0V, V _{DS} =25V, f=1.0 MHz		623		pF
Output Capacitance		C _{OSS}			62		pF
Reverse Transfer Capacitance		C _{RSS}			2.9		pF
SWITCHING CHARACTERISTICS							
Total Gate Charge (Note 1)		Q _G	V _{DS} =100V, V _{GS} =10V, I _D =2.0A I _G =1mA (Note 1, 2)		15		nC
Gate-source Charge		Q _{GS}			5.6		nC
Gate-Drain Charge		Q _{GD}			2.5		nC
Turn-on Delay Time (Note 1)		t _{D(ON)}	V _{DS} =30V, V _{GS} =10V, I _D =0.5A, R _G =25Ω (Note 1, 2)		4.4		ns
Rise Time		t _R			24		ns
Turn-off Delay Time		t _{D(OFF)}			122		ns
Fall-Time		t _F			25		ns
SOURCE- DRAIN DIODE RATINGS AND CHARACTERISTICS							
Maximum Body-Diode Continuous Current		I _S				5	A
Maximum Body-Diode Pulsed Current		I _{SM}				10	A
Drain-Source Diode Forward Voltage (Note 1)		V _{SD}	V _{GS} =0V, I _S =5.0A			1.4	V
Reverse Recovery Time (Note 1)		t _{rr}	V _{GS} =0V, I _S =5.0A,		328		ns
Reverse Recovery Charge		Q _{rr}	dl _r /dt=100A/μs (Note1)		2.65		μC


Notes: 1. Pulse Test : Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.

2. Essentially independent of operating temperature.

TEST CIRCUITS AND WAVEFORMS




Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms


TEST CIRCUITS AND WAVEFORMS(Cont.)




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform









Unclamped Inductive Switching Test Circuit









Unclamped Inductive Switching Waveforms


■ TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS(Cont.)



■ TO-251-3L PACKAGE OUTLINE DIMENSIONS



Technical drawing of a mechanical part (Fig. 1) showing a top view. The drawing includes the following dimensions and tolerances:

- Top horizontal dimension: $5.33^{+0.15}_{-0.03}$
- Top vertical dimension: $1.0^{+0.15}_{-0.05}$
- Right vertical dimension: 1.78 ± 0.2
- Bottom right vertical dimension: 6.1 ± 0.1
- Bottom horizontal dimension: 0.840 ± 0.1
- Bottom left horizontal dimension: $0.76^{+0.10}_{-0.02}$
- Left vertical dimension: 6.6
- Left horizontal dimension: 1.2 ± 0.1
- Top left corner radius: $R1.438$
- Center circle: A circle with a crosshair indicating the center.
- Bottom horizontal dimension: 2.286

