

TRUPHONE FOR THINGS SIM



TRUPHONE

TRUPHONE.COM

eSIM

Smart SIM for Seamless IoT Connectivity

Truphone's secure IoT SIM not only connects your devices securely to our global network, each one is shipped with eSIM technology as standard.

Highlights


- Simplify SIM logistics with a single SKU
- Simple out of the box connectivity experience
- Single contract for multi-country deployments with our global network and IoT platform;
- Better service management control with local operations and direct agreements with Tier 1 providers;
- Faster time-to-market with proven experience to deploy mobile services in new markets;
- Reliable global service focused on quality and fast delivery

Technical Features


- Remote SIM provisioning compliant with GSMA M2M and SIMalliance specifications
- Inbuilt bootstrap connectivity profile
- Up to 10 operator profiles
- Compliant with 2G / 3G / 4G (LTE) / CDMA / NB-IoT / CAT-M networks
- Network access applications supported: SIM / USIM / ISIM / CSIM
- Power saving features
- Secure element access control (ARF / PKCS#15)
- OTA capability over SMS, CAT-TP & HTTPS (including DNS)
- Multi-interfaces able to combine eSIM + eSE

SIM Types

SKU	SIM-S-I03-MFF2-2
Format	MFF2
Dimensions	5x6x1.27mm
Chip Manufacturer	ST Microelectronics
Chip Reference	ST33G1M2
SIM Vendor	ST Microelectronics
Low Power Support	No



SKU	SIM-S-I03-MFF2-2-LP
Format	MFF2
Dimensions	5x6x1.27mm
Chip Manufacturer	ST Microelectronics
Chip Reference	ST33G1M2
SIM Vendor	ST Microelectronics
Low Power Support	Yes




SKU	SIM-S-I03-TRI-2
Format	2FF/3FF/4FF
Dimensions	4FF: 12.3x8.8x.67mm
Chip Manufacturer	ST Microelectronics
Chip Reference	ST33G1M2
SIM Vendor	ST Microelectronics
Low Power Support	No



SKU	SIM-S-I03-TRI-2-LP
Format	2FF/3FF/4FF
Dimensions	4FF: 12.3x8.8x.67mm
Chip Manufacturer	ST Microelectronics
Chip Reference	ST33G1M2
SIM Vendor	ST Microelectronics
Low Power Support	Yes





Hardware Features

Chip Type

Supplier	ST Microelectronics
Chip Codes	ST33G1M2M
Technology	80 nm
CPU	ARM 32-bit RISC SC300

Qualification

Common Criteria EAL5+
Industrial Qualification (JEDEC JESD47)

Electrical Characteristics

Supply voltage (All formats):
Class A (5 V), Class B (3 V), Class C (1.8 V)

Operational Temperature Characteristics

Temperature Range 4FF	-25° to +85°
Extended Range MFF2	-40° to +105°

Supported Clock Division Factors

F/D = 372 (F=372, D=1)	Yes
F/D = 64 (F=512, D=8)	Yes
F/D = 32 (F=512, D=16)	Yes
F/D = 16 (F=512, D=32)	Yes
F/D = 8 (F=512, D=64)	Yes

Memory Sizes

Total Flash size	1280K
Flash available to customer	380K / 512K (Ext)
RAM Total / For applets	30K / 7K

NVRAM characteristics

Endurance cycles (min) @25°	100K / 500K (Ext)
Data retention (min) @25°	10 Y / 25 Y (Ext)
Page/Sector erase time	3ms/6ms
Page write time	2.5ms

Cryptographic Features and Accelerators

Crypto-coprocessor	Yes
3DES engine	Yes
AES engine	Yes
True RNG	Yes
CRC	Yes
CPA /DPA Countermeasures	Yes

Form Factors

3 in 1 Plug-In SIM (2FF, 3FF and 4FF)	Yes
DFN8 (MFF2)	Yes
WLCSP	Yes



Software Features

Platform

UICC	Release 12
Java Card	3.0.4
Global Platform Certified	2.2
	(Amd. A,B,C,D,E)
SIMAlliance IPP	2.1
GMSA RSP SGP.02 M2M	3.2
Power Saving Features (PSM, eDRX)	ETSI R13

Supported Applications

USIM	Release 12
ISIM	Release 12
EAP	Release 12

Multiplication Features

Single SIM/ multiple USIMs / ISIMs	Yes
Number of Logical Channels	4

Supported Java Card APIs

UICC API	Release 12
USIM API	Release 12
ISIM API	Release 12
Global Platform API	2.2.1

Supported Protocols

T=0	Yes
T=1	Yes

Memory Management

Journaling File System	Yes (Option)
Dynamic Memory Management	Yes

Administration

Administrative Commands	Release 12
-------------------------	------------

Remote Management

Remote File Management	Release 12
Remote Applet Management	Release 12
SMS Concatenation Size	configurable
BIP	Release 12
CAT_TP	Release 12
HTTPS Remote Management	Yes

Authentication Algorithms

2G COMP128-1,2,3	Yes
2G GSM-MILENAGE	Yes
3G MILENAGE	Yes
GBA Support	Yes
TUAK	Yes
ECC (NIST P-256, brainpoolIP256r1)	Yes
RSA (up to 2048 bits)	Yes



MFF2 Pin Out

This package is compatible with the MFF2 package defined by ETSI 102 671 release 12.

Figure 1. VFDFPN8 pinout (top view)




Table 1. Pin descriptions

Name	Description	Pin state
GND	Ground supply	-
SWIO	Not used	Input pull-up
RESET	External reset	Input pull-down
I/O	Input/output	Pull-down then pull-up after card activation
CLK	External clock	Pull-down
VCC	Power supply	-
NC	Not connected internally	-

Figure 2. ST4SIM-200M PCB integration recommendations

