




版次 (Vension)	变更内容 (Rev. Content)	变更者 (Change Person)

技术参数 (Technical Data)		
项 目 (Item)	UL	IEC
额定电气参数 (Rated Electrical Parameters)	300V/12A	250V/15A
压线范围 (Wire Range)	26~14AWG	1.5mm²
工频耐压 (Frequency Voltage)	AC 2000V	
冲击耐压 (Rated Surge Voltage)	4000V	
绝缘阻抗 (Insulation Resistance)	DC500V 500MΩ above	
接触电阻 (Contact Resistance)	≤8mΩ	
剥线长度 (Strpping Length)	6mm	
工作温度 (Temperature)	-40℃~+105℃	
材质和电镀 (Material and plating)		
绝缘材质 (Housing)	PA66 (UL94 V-0)	
触点材料 (Contact)	铜合金, 镀锡 (Copper alloy, Sn plated)	
螺丝 (Screws)	钢, 镀锌 (Steel, Zn plated)	
方盒 (Cage)	铜合金, 镀镍 (Copper alloy, Ni plated)	

产品命名编码:

(Product Number Code):

GS009S-5. 0-XXP-1Y-00A (H)

产品型号 (Series No.)

客户需求

(Customer Request)

极数 (No. of poles)

塑体颜色 (Housing Color)

- 1: 单倍间距
(Single Pitch)
2: 双倍间距
(Double Pitch)

- 1: 绿色 (Green) 7: 透明色
(Transparent)
2: 蓝色 (Blue)
3: 黑色 (Black) 8: 白色 (White)
4: 灰色 (Grey) 9: 黄色 (Yellow)
5: 橙色 (Orange) Y: 多种颜色
6: 红色 (Red) (Mixed Color)

P=5. 0mm, N为孔位数 (N for hole digits), 有效位数为 (Significant Digits): 02P~XXP												
N	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P	13P
L	10. 00	15. 00	20. 00	25. 00	30. 00	35. 00	40. 00	45. 00	50. 00	55. 00	60. 00	65. 00
B	5. 00	10. 00	15. 00	20. 00	25. 00	30. 00	35. 00	40. 00	45. 00	50. 00	55. 00	60. 00
N	14P	15P	16P	17P	18P	19P	20P	21P	22P	23P	24P	...
L	70. 00	75. 00	80. 00	85. 00	90. 00	95. 00	100. 00	105. 00	110. 00	115. 00	120. 00	
B	65. 00	70. 00	75. 00	80. 00	85. 00	90. 00	95. 00	100. 00	105. 00	110. 00	115. 00	

宁波高胜电子有限公司			公差范围 (Tolerance Range)	
GOOSVN NINGBO GOOSVN ELECTRONIC CO.,LTD			150~	±1.50
型号 (Type): GS009S-5. 0-XXP-1Y-00A (H)			60~150	±1.00
核准 (Approval):			30~60	±0.60
审核 (Audit):			6~30	±0.40
设计 (Design):			0~6	±0.25
比例 (Scale): FULL			角度 (Angle)	X ±2° XX ±1°
版次 (Version): T0				

A

B

C

D

E

A

B

C

D

E

版次 (Vension)	变更内容 (Rev. Content)	变更者 (Change Person)

技术参数 (Technical Data)		
项 目 (Item)	UL	IEC
额定电气参数 (Rated Electrical Parameters)	300V/12A	250V/15A
压线范围 (Wire Range)	26~14AWG	1.5mm²
工频耐压 (Frequency Voltage)	AC 2000V	
冲击耐压 (Rated Surge Voltage)	4000V	
绝缘阻抗 (Insulation Resistance)	DC500V 500MΩ above	
接触电阻 (Contact Resistance)	≤20mΩ	
剥线长度 (Strpping Length)	6mm	
工作温度 (Temperature)	-40℃~+105℃	
材质和电镀 (Material and plating)		
绝缘材质 (Housing)	PA66 (UL94 V-0)	
触点材料 (Contact)	铜合金, 镀锡 (Copper alloy, Sn plated)	
螺丝 (Screws)	钢, 镀锌 (Steel, Zn plated)	
方盒 (Cage)	铜合金, 镀镍 (Copper alloy, Ni plated)	

产品命名编码:

(Product Number Code):

GS009S-5.08-XXP-1Y-00A (H)

产品型号 (Series No.)

客户需求

(Customer Request)

极数 (No. of poles)

塑体颜色 (Housing Color)

1: 单倍间距
(Single Pitch)
2: 双倍间距
(Double Pitch)

1: 绿色 (Green) 7: 透明色
2: 蓝色 (Blue) (Transparent)
3: 黑色 (Black) 8: 白色 (White)
4: 灰色 (Grey) 9: 黄色 (Yellow)
5: 橙色 (Orange) Y: 多种颜色
6: 红色 (Red) (Mixed Color)

P=5.08mm, N为孔位数 (N for hole digits), 有效位数为 (Significant Digits): 02P~XXP												
N	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P	13P
L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
N	14P	15P	16P	17P	18P	19P	20P	21P	22P	23P	24P	...
L	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	

 宁波高胜电子有限公司 NINGBO GOOSVN ELECTRONIC CO.,LTD			公差范围 (Tolerance Range)	
型号 (Type): GS009S-5.08-XXP-1Y-00A (H)			150~	±1.50
核准 (Approval):			60~150	±1.00
图号 (Drawing NO.):			30~60	±0.60
审核 (Audit):			6~30	±0.40
单位 (Units): mm			0~6	±0.25
页码 (Page): 1/1			角度 (Angle)	X ±2° XX ±1°
设计 (Design):			比例 (Scale): FULL	版次 (Version): T0