

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-15-016505	11NOV2015	DL	CW
	B2	ECR-16-009730	06JUL2016	BS	CW
	B3	ECR-16-018198	13FEB2017	QY	CW
	C	ECR-21-117384	09NOV2021	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-4.0 mm² (26-12 AWG)
CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20300X20XX000)

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-4.0 mm² (26-12 AWG)
接线类型: 冷压接
2. 端子需要单独订购.
(订货号参考图面: T20300X20XX000)

M3 SCREW
RECOMMENDED
TIGHTENING
TORQUE 0.2Nm
M3螺丝 推荐锁紧力矩0.2Nm

40.1

31.4

M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.2Nm
M3螺丝 推荐锁紧力矩0.2Nm

21

21






TYPE-1:T2080052201-000 TE LOGO
类 型-1:T2080052201-000 TE LOGO

TYPE-2:T2080052201-001 STAINLESS STEEL SCREW,TE LOGO
类 型-2:T2080052201-001 不锈钢螺丝,TE LOGO

GROUNDING CONTACT TYPE: SCREW CONTACT
GROUNDING CONTACT FINISH: SILVER PLATED
WIRE RANGE: 2.5mm (AWG14)
接地端子类型: 螺丝连接端子 / 接地端子表面处理: 镀银 / 接线范围: 2.5mm² (AWG14)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	10JAN2015	 TE Connectivity		
		CHK	10JAN2015			
		APVD	10JAN2015	NAME HQ-005-F		
		PRODUCT SPEC	108-137054			
		APPLICATION SPEC	114-137054	SIZE A300779		
		WEIGHT	-			
		Customer Drawing		SCALE	2:1	SHEET
				1 OF 2		REV
						C


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




NOTES:
SEE SHEET 1
注释:
见页 1

TYPE-3:T2080052201-002 STAINLESS STEEL SCREW,NO LOGO
类 型-3:T2080052201-002 不锈钢螺丝,无LOGO

ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外,其它尺寸同类型1



T2080052201-002	HQ-005-F	HQ-005 FEMALE INSERT, STAINLESS STEEL SCREW,NO LOGO HQ-005 母插,不锈钢螺丝,无LOGO	TYPE-3 类 型-3
T2080052201-001	HQ-005-F	HQ-005 FEMALE INSERT, STAINLESS STEEL SCREW HQ-005 母插,不锈钢螺丝	TYPE-2 类 型-2
T2080052201-000	HQ-005-F	HQ-005 FEMALE INSERT HQ-005 母插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 10JAN2015	 TE Connectivity					
DIMENSIONS: mm		CHK Chris Wang 10JAN2015	NAME HQ-005-F					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Xiang Xu 10JAN2015						
		PRODUCT SPEC 108-137054	SIZE CAGE CODE DRAWING NO RESTRICTED TO					
		APPLICATION SPEC 114-137054						
MATERIAL - -		WEIGHT -	A300779		C-T2080052201000		-	
FINISH - -								
Customer Drawing			SCALE 2:1		SHEET 2 OF 2		REV C	