



$$A = 2.54 * \frac{n^p}{2} \pm 0.50$$

$$B = 2.54 * \frac{n^p}{2} - 2.54 \pm 0.20$$

PCB Layout

Technical Data

Material:  
 Contact material: Brass  
 Plating: Gold Flash  
 Insulator material: Black polyester UL94V-0  
 Standard: PA6T+30%G. F

Electrical:

Current rating: 3amps/contact max.  
 Contact resistance:  $\leq 20m \Omega$ /contact  
 Insulation resistance:  $\geq 1000M \Omega$  at V=100V  
 Withstanding voltage: 550V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE:  $\pm 0.20$

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D/2254S-22-XX-75	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			CONNECTOR	
TOLERANCES ARE		30 <sup>+0.15</sup> <sub>-0.10</sub>	±0.30	ANGLE
		10 <sup>+0.30</sup> <sub>-0.10</sub>	±0.20	UNIT: mm
		5 <sup>+0.10</sup> <sub>-0.10</sub>	±0.15	SCALE: 1:1
				SHEET 1 OF 1
				PROJ

  

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			