

## 100V Trench MOS Barrier Schottky

**Ultra Low VF 0.57V@15A, 25 °C**



### Features

- Trench MOS schottky technology
- Low stored charge Majority Carrier Conduction
- Ultra low forward voltage drop
- Low leakage current
- Low power loss and high efficiency
- High surge capacity
- ESD rating:>20K volts

### Typical Application

Schottky rectifier design for high frequency switched mode power supplies, such as adaptors and on board DC/DC converters.

**15 Amperes, 100 Volts**



**TO-277**

### Device Summary

Symbol	Value
I <sub>F(AV)</sub>	15 A
V <sub>RRM</sub>	100V
V <sub>F(Typical)</sub>	0.57V
T <sub>j(max)</sub>	150 °C

### Mechanical Data

Case: JEDEC TO-277 , molded plastic body

Terminals: Plated leads, solderable per  
MIL-STD-750, Method 2026

Mounting Position: Any

Note: Pins 2 & 3 must be electrically connected at the printed circuit board.

<b>Major Rating and Characteristics(per diode)</b>					
<b>Symbol</b>	<b>Parameter</b>			<b>Values</b>	<b>Units</b>
V <sub>RRM</sub>	Repetitive peak reverse voltage			100	V
T <sub>J</sub>	Storage temperature range			-55 to 150	°C
I <sub>FSM</sub>	Surge non repetitive forward current	10 ms sine or 6 ms rect. pulse		350	A
I <sub>F(AV)</sub>	Maximum average forward current 50 % duty cycle, rectangular waveform		T <sub>c</sub> =25°C	15	

<b>Electrical Characteristics(T<sub>A</sub>=25 °C unless otherwise noted)</b>							
Parameter	Test condition		Symbol	TYP	MAX	UNITS	
Forward Voltage drop	I <sub>F</sub> =5A	T <sub>A</sub> =25 °C	V <sub>F</sub> <sup>(1)</sup>	0.45	-	V	
	I <sub>F</sub> =10A			0.51			
	I <sub>F</sub> =15A			0.57	0.65		
	I <sub>F</sub> =5A	T <sub>A</sub> =125 °C		0.41	-		
	I <sub>F</sub> =10A			0.56			
	I <sub>F</sub> =15A			0.52	0.60		
Reverse leakage current	V <sub>R</sub> =100V	T <sub>A</sub> =25 °C	I <sub>R</sub> <sup>(2)</sup>	-	50	uA	
		T <sub>A</sub> =125 °C		15	70	mA	
Junction capacitance	V <sub>R</sub> =5V <sub>DC</sub> , 25 °C(1MHz)		C <sub>j</sub>	1000		pF	

Notes (1) Pulse test: 300us pulse width,2% duty cycle (2) Pulse test: 300us pulse width,2% duty cycle

<b>Thermal Characteristics(T<sub>A</sub>=25 °C unless otherwise noted)</b>				
Parameter	Symbol	SK15U100AAPU		UNIT
Typical thermal resistance	R <sub>JA</sub> <sup>(1)</sup>	75		°C /W
	R <sub>JM</sub> <sup>(2)</sup>	34		

#### Notes

- (1) Free air, mounted on recommended PCB, 2oz.pad area; thermal resistance R<sub>JA</sub>-junction to ambient
- (2) Cathode pad dimensions 18.8mm x 14.4mm. Anode pad dimensions 5.6mm x 14.4mm; RJM-junction to mount

## Characteristics Curves ( $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Fig.1 Typical Forward Voltage Characteristics






Fig.2 Typical Reverse Leakage Characteristics



## Package Outline Dimensions in Millimeters

UNIT:MM		
Dim	Min	Max
A	1.05	1.25
A2	0.33	0.43
b1	0.80	0.99
b2	1.70	1.88
D	3.90	4.05
D2	3.054Typ	
E	6.40	6.60
e	1.84Typ	
E1	5.30	5.50
E2	3.549Typ	
L	0.75	0.95
L1	0.45	0.65
W	1.10	1.41



Pin: 1 → 2 → 3

TQ-277