

# APPROVAL SHEET

## (RoHS Compliant & Halogen Free)

**CUSTOMER** : 富為電子  
**CUSTOMER'S PART NO.** :  
**DESCRIPTION** : Multi-layer Band Pass Filter  
**PART NO.** : LTB-2012-2G4H6-A29  
**DATE** :  
**AUTHORIZED BY** : *Derek Wei*

	FULLY APPROVED	PARTIALLY APPROVED	REJECTED
SIGN			
SUGGESTION			

美磊科技股份有限公司

**MAG. LAYERS SCIENTIFIC-TECHNICS CO., LTD**

HEAD OFFICE / PINGZHEN PLANT

270, Nan-Feng Road, Pingzhen District, Taoyuan City, Taiwan

TEL : 886-3-4159111 FAX : 886-3-4192255

[http : //www.maglayers.com.tw](http://www.maglayers.com.tw)

[E-mail : info@maglayers.com.tw](mailto:info@maglayers.com.tw)



## Revision History

Version	Date	Description	Approved by	Prepared by
1	2018/10/17	Initial specification.	CF	Carol
2	2018/11/16	Updated electrical requirements.	CF	Carol
3	2019/08/22	Updated electrical requirements & electrical characteristics.	CF	JC
4	2020/06/05	Update storage condition. Add MSL rating.	CF	JC
5	2020/11/18	Update Reliability test.	CF	Melody



## APPLICATION

WLAN, Bluetooth, Home RF.

## FEATURES

- Compact Size**  
Miniaturized SMD packaged in low profile and lightweight.
- Low loss**  
Low insertion loss, high attenuation.
- High Soldering Heat Resistance**  
High quality termination allows both flow and re-flow soldering methods to be applied.
- Characteristics**  
Eliminate noise over a wide frequency range. Ideal for high frequency and space limited designs.
- Available in tape and reel packaging for automatic mounting**

## PRODUCT IDENTIFICATION

L T B - 2 0 1 2 - ### x x - A 2 9 - □ □  
①                      ②                      ③                      ④                      ⑤

- ① Product Code
- ② Dimension Code
- ③ Series Type (### represents center frequency and xx represents material type)
- ④ Design Code
- ⑤ Pattern Code

## ELECTRICAL REQUIREMENTS


Part No.	Pass Band	Insertion Loss in BW	VSWR In BW	Attenuation
LTB-2012-2G4H6-A29-RW	2400~2500 MHz	1.1 dB max. 0.83 dB typ.	2 max.	30 dB min. at 500~960 MHz 43 dB typ. at 500~960 MHz 26 dB min. at 1500~1650 MHz 33 dB typ. at 1500~1650 MHz 22 dB min. at 3200~3300 MHz 32 dB typ. at 3200~3300 MHz 35 dB min. at 4800~5000 MHz 44 dB typ. at 4800~5000 MHz 20 dB min. at 7200~7500 MHz 28 dB typ. at 7200~7500 MHz

Operating Temperature Range : -40~85°C

Power Capacity : 3W max.



## PRODUCT DIMENSION




L	W	T	a1
2.00±0.15	1.25±0.10	1 max.	0.175±0.10
a2	c1	c2	e1
0.25±0.10	0.325±0.10	0.275±0.10	0.25±0.05
e2	e3		
0.25±0.05	0.25±0.05		

NOTE : Dimensions in mm.


## TERMINAL CONFIGURATION

Top View




- ① IN
- ② GND
- ③ GND
- ④ OUT
- ⑤ GND

## MEASURING DIAGRAM



Test Instrument :  
Agilent E5071C Network Analyzer.


## RECOMMENDED PCB LAYOUT AND LAND PATTERN



Unit : mm


⊙ Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

## ELECTRICAL CHARACTERISTICS ( T=25°C)



## RELIABILITY TEST

### Mechanical Test

Item	Test Condition	Specification
<b>Vibration</b>	10 Hz/min~55 Hz/min~10 Hz/min vibration frequency with 1.5 mm amplitude for two hours in x, y, z directions	No apparent damage
<b>Drop shock</b>	Dropped onto printed circuit board from 100cm height three times in x, y, z directions. The terminals shall be protected.	No apparent damage
<b>Soldering heat resistance</b>	Preheating temperature : $150\pm 10^{\circ}\text{C}$ Preheating time : 1 to 2 minutes Solder bath temperature : $260\pm 5^{\circ}\text{C}$ Bathing time : $10\pm 1$ seconds	Loss of metallization on the edges of each electrode shall not exceed 25%.
<b>Bending test onto printed circuit board</b>	Solder specimen LTCC components on the test printed circuit board (L: 100 x W: 40 x T: 1.6mm) in appended recommended PCB pattern. Apply the load in direction of the arrow until bending reaches 2 mm. 60sec holding time.  Unit: mm	No apparent damage
<b>Solderability</b>	*Solder bath temperature : $245\pm 5^{\circ}\text{C}$ *Immersion time : $3\pm 1$ seconds. Solder : Sn3Ag0.5Cu for lead-free	At least 95% of a surface of each terminal electrode must be covered by fresh solder.
<b>Adhesive strength</b>	Standard is as follows 0605~1005 $>0.1\text{KgF}$ 1109~2016 $>0.5\text{KgF}$ 2520~ $>1\text{KgF}$	No apparent damage


### Environment Test

<b>Thermal shock</b>	$-40^{\circ}\text{C}$ ~ $85^{\circ}\text{C}$ for 100 cycles each cycle being 30 min	No apparent damage Fulfill the electrical spec. after test
<b>Humidity resistance</b>	$85\pm 2^{\circ}\text{C}$ , 80~90% R.H. for 1000 hours	No apparent damage Fulfill the electrical spec. after test
<b>High temperature resistance</b>	$85\pm 2^{\circ}\text{C}$ for 1000 hours	No apparent damage Fulfill the electrical spec. after test
<b>Low temperature resistance</b>	$-40\pm 3^{\circ}\text{C}$ for 1000 hours	No apparent damage Fulfill the electrical spec. after test




# PACKAGING FOR SMC

## Peel-off force



The force for peeling off cover tape is 10 grams in the arrow direction.


## Dimension (Unit: mm)



TYPE	A	B	C	D	E	F
8 mm	178±1	60+0.5 -0	-	13±0.2	9±0.5	12±0.5
12 mm	178±0.3	60±0.2	19.3±0.1	13.5±0.1	13.6±0.1	-


## Taping quantity

SERIES	5824 5724	5320 5220	4532	4516	3225	3216 2520	2012 1608	1005
PCS/Reel	5000	3000	1000	2000	2500	3000	4000	10000



## TAPE PACKING CASE

Unit:cm



No. of Reels	W	L	H
2	18±0.5	18±0.5	2.4±0.2
3	18±0.5	18±0.5	3.6±0.2
4	18±0.5	18±0.5	4.8±0.2
5	18±0.5	18±0.5	6.0±0.2

## MSL RATING

Level 1

## OPERATION TEMPERATURE


-40°C~85°C

## STORAGE CONDITION

The temperature should be within -40~85°C and humidity should be less than 75% RH. The product should be used within 6 months from the time of delivery.


## ATTENTION REGARDING PCB BENDING

- (a) PCB shall be designed so that products are not subjected to the mechanical stress for board warpage. Product shall be located in the sideways direction to the mechanical stress.




(Poor example)

Length:  $a > b$




(Good example)

- (b) Products (A,B,C,D) shall be located carefully so that products are not subjected to the mechanical stress due to warping the board. Because they may be subjected to the mechanical stress in order of  $A > C > B \approx D$ .





## RECOMMENDED REFLOW SOLDERING PROFILE



Profile Feature		Sn-Pb	Pb-Free
Preheat	ts	60~120 seconds	60~180 seconds
	Tsmin	100°C	150°C
	Tsmax	150°C	200°C
Average ramp-up rate (Tsmax to Tp)		3°C/second max.	3°C/second max.
Time main above	Temperature (TL)	183°C	217°C
	Time (tL)	60~150 seconds	60~150 seconds
Peak temperature (Tp)		230°C	250~260°C
Time within 5°C of actual peak temperature (tP)		10 seconds	10 seconds
Ramp-down rate		6°C/sec max.	6°C/sec max.
Time 25°C to peak temperature		6 minutes max.	8 minutes max.

## NOTES

The contents of this data sheet are subject to change without notice. Please confirm the specifications and delivery conditions when placing your order.