


## PRODUCT CHARACTERISTICS

VR(@IC=0.5mA)	45V
VF(@IF=30A)	0.6V
IR(@VR=45V)	50uA
ID	60A

## Symbol




## MECHANICAL CHARACTERISTICS


- \* Case: Epoxy, Molded
- \* Finish: All External Surfaces Corrosion Resistant and Terminal
- \* Leads are Readily Solderable
- \* Lead Temperature for Soldering Purposes:  
260 °C Max. for 10 Seconds

## FEATURES


- \* Guard Ring for Stress Protection
- \* Low Forward Voltage
- \* Low Power Loss/High Efficiency
- \* High Surge Capacity
- \* Low Stored Charge Majority Carrier Conduction
- \* Pb Free Packages are Available\*



TO-220



TO-220F



TO-263

## ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MBR6045F	TO-220F	50 pieces/Tube
N/A	MBR6045A	TO-220	50 pieces/Tube
N/A	MBR6045E	TO-263	800 pieces/reel

## MAIMUM RATINGS (Each Diode Leg)

Parameter	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	$V_{RRM}$	45	V
Average Rectified Output Current	(Total)	60	A
	(per Leg)	30	A
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Reate Load	$I_{FSM}$	500	A
Operating and Storage Temperature Range	$T_J, T_{STG}$	-55 to + 175	°C

## ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	Test Conditions	Min	Typ.	Max	Unit
Peak Repetitive Reverse Voltage	$B_V$	$I_C=0.5mA, T_J=25^\circ C$	—	47	—	V
Forward Voltage Drop	$V_F$	$I_F=30A, T_J=25^\circ C$	—	0.58	0.6	V
Leakage Current	$I_R$	$V_R=45V, T_J=25^\circ C$	—	—	0.05	mA
		$V_R=45V, T_J=125^\circ C$	—	—	6	




Figure 1. Typical Forward Voltage Per Diode






Figure 2. Typical Reverse Current Per Diode




$T_C$ , CASE TEMPERATURE ( $^\circ\text{C}$ )  
Fig.3 Forward Current Derating Curve



NUMBER OF CYCLES AT 60HZ  
Fig.4 Max Non-Repetitive Surge Current



■ TO-220-2L PACKAGE OUTLINE DIMENSIONS



■ TO-263-2L PACKAGE OUTLINE DIMENSIONS

