

4






3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	17APR07	L.L	K.O



NOTE:
 1. GENERAL TOLERANCE: $\pm 0.5, \pm 3^\circ$
 2. SHALL BE FREE FROM FUNCTION AND CONFIGURE DEFECTS
 3. WARPAGE MAX 4MM

- 1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN L.LIU 16APR07	tyco Tyco Electronics Shanghai, China	
DIMENSIONS: mm		CHK L.YIN 16APR07	NAME ECU 90P SLIDER	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm 1 PLC ± 0.5 2 PLC ± 0.3 3 PLC ± 0.13 4 PLC ± 0.0001 ANGLES $\pm 2^\circ$		APVD K.ODA 17APR07	SIZE A200779	
MATERIAL PA66-GF30		PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	DRAWING NO. C-1813263	RESTRICTED TO -
AMP 1471-9 REV 31MAR2000		SCALE		SHEET OF REV 1 1 A