

Product Summary

| $V_{(BR)DSS}$ | $R_{DS(on)TYP}$ | I_D |
|---------------|-----------------|-------|
| 20V | 32mΩ@4.5V | 2.1A |
| | 43mΩ@2.5V | |


Feature

- TrenchFET Power MOSFET
- Excellent $R_{DS(on)}$ and Low Gate Charge

Application

- DC/DC Converter
- Load Switch for Portable Devices
- Battery Switch

MARKING:



ABSOLUTE MAXIMUM RATINGS ($T_a=25^\circ C$ unless otherwise noted)

| Parameter | | Symbol | Value | Unit |
|---|------------------|-----------------|----------|------|
| Drain-Source Voltage | | V_{DS} | 20 | V |
| Gate-Source Voltage | | V_{GS} | ± 8 | V |
| Continuous Drain Current ^{1,5} | $T_A=25^\circ C$ | I_D | 2.1 | A |
| Plused Drain Current ² | | I_{DM} | 10 | A |
| Power Dissipation ^{4,5} | $T_A=25^\circ C$ | P_D | 1.4 | W |
| Thermal Resistance from Junction to Ambient | | $R_{\theta JA}$ | 89 | °C/W |
| Junction and Storage Temperature Range | | T_{STG} | -55~+150 | °C |



SALLTECH

SR2302

MOSFET ELECTRICAL CHARACTERISTICS($T_a=25^\circ\text{C}$ unless otherwise noted)


| Parameter | Symbol | Test Condition | Min | Type | Max | Unit |
|---|-----------------------------|--|------|------|-----------|------------------|
| Static Characteristics | | | | | | |
| Drain-source breakdown voltage | $V_{(\text{BR})\text{DSS}}$ | $V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$ | 20 | | | V |
| Zero gate voltage drain current | I_{DSS} | $V_{\text{DS}} = 20\text{V}, V_{\text{GS}} = 0\text{V}$ | | | 1 | μA |
| Gate-body leakage current | I_{GSS} | $V_{\text{GS}} = \pm 8\text{V}, V_{\text{DS}} = 0\text{V}$ | | | ± 0.1 | μA |
| Gate threshold voltage ³ | $V_{\text{GS}(\text{th})}$ | $V_{\text{DS}} = V_{\text{GS}}, I_D = 250\mu\text{A}$ | 0.65 | 0.95 | 1.2 | V |
| Drain-source on-resistance ³ | $R_{\text{DS}(\text{on})}$ | $V_{\text{GS}} = 4.5\text{V}, I_D = 3.6\text{A}$ | | 32 | 42 | $\text{m}\Omega$ |
| | | $V_{\text{GS}} = 2.5\text{V}, I_D = 3.1\text{A}$ | | 43 | 65 | |
| Forward transconductance ³ | g_{FS} | $V_{\text{DS}} = 5\text{V}, I_D = 3.6\text{A}$ | 8 | | | S |
| Dynamic characteristics | | | | | | |
| Input Capacitance | C_{iss} | $V_{\text{DS}} = 10\text{V}, V_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$ | | 260 | | pF |
| Output Capacitance | C_{oss} | | | 48 | | pF |
| Reverse Transfer Capacitance | C_{rss} | | | 27 | | pF |
| Total gate charge | Q_g | $V_{\text{DS}} = 10\text{V}, V_{\text{GS}} = 4.5\text{V}, I_D = 3.0\text{A}$ | | 2.9 | 5 | nC |
| Gate-source charge | Q_{gs} | | | 0.4 | | nC |
| Gate-drain charge | Q_{gd} | | | 0.6 | | nC |
| Switching Characteristics | | | | | | |
| Turn-on delay time | $t_{\text{d}(\text{on})}$ | $V_{\text{DD}} = 10\text{V}, R_L = 3.3\Omega, V_{\text{GEN}} = 4.5\text{V}, R_g = 6\Omega$ | | 2.5 | | ns |
| Turn-on rise time | t_r | | | 3.2 | | ns |
| Turn-off delay time | $t_{\text{d}(\text{off})}$ | | | 21 | | ns |
| Turn-off fall time | t_f | | | 3 | | ns |
| Source-Drain Diode characteristics | | | | | | |
| Diode Forward voltage ³ | V_{DS} | $V_{\text{GS}} = 0\text{V}, I_S = 0.94\text{A}$ | | 0.7 | 1.2 | V |

Notes :


- 1.The maximum current rating is limited by package.
- 2.Pulse Test : Pulse Width $\leq 10\mu\text{s}$, duty cycle $\leq 1\%$.
- 3.Pulse Test : Pulse Width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$.
- 4.The power dissipation P_D is limited by $T_{\text{J}(\text{MAX})} = 150^\circ\text{C}$.
- 5.Device mounted on 1in² FR-4 board with 2oz. Copper, in a still air environment with $T_A = 25^\circ\text{C}$.

Typical Electrical and Thermal Characteristics


Output Characteristics





Transfer Characteristics




$R_{DS(ON)} - I_D$






$R_{DS(ON)} - V_{GS}$



Threshold Voltage



SOT-23 Package Information




| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 0.900 | 1.150 | 0.035 | 0.045 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 0.900 | 1.050 | 0.035 | 0.041 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 2.800 | 3.000 | 0.110 | 0.118 |
| E | 1.200 | 1.400 | 0.047 | 0.055 |
| E1 | 2.250 | 2.550 | 0.089 | 0.100 |
| e | 0.950 TYP | | 0.037 TYP | |
| e1 | 1.800 | 2.000 | 0.071 | 0.079 |
| L | 0.550 REF | | 0.022 REF | |
| L1 | 0.300 | 0.500 | 0.012 | 0.020 |
| θ | 0° | 8° | 0° | 8° |

SOT-23 Tape and Reel


SOT-23 Tape and reel

SOT-23 Embossed Carrier Tape




| Dimensions are in millimeter | | | | | | | | | | |
|------------------------------|------|------|------|-------|------|------|------|------|------|------|
| Pkg type | A | B | C | d | E | F | P0 | P | P1 | W |
| SOT-23 | 3.15 | 2.77 | 1.22 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |

SOT-23 Tape Leader and Trailer



SOT-23 Reel



| Dimensions are in millimeter | | | | | | | | |
|------------------------------|---------|-------|-------|--------|--------|-------|------|-------|
| Reel Option | D | D1 | D2 | G | H | I | W1 | W2 |
| 7" Dia | Ø178.00 | 54.40 | 13.00 | R78.00 | R25.60 | R6.50 | 9.50 | 12.30 |

| REEL | Reel Size | Box | Box Size(mm) | Carton | Carton Size(mm) | G.W.(kg) |
|----------|-----------|------------|--------------|-------------|-----------------|----------|
| 3000 pcs | 7 inch | 30,000 pcs | 203×203×195 | 120,000 pcs | 438×438×220 | |