

PRODUCT CHARACTERISTICS

VDSS	650V
$R_{DS(on)max}(V_{GS}=10V)$	1.1Ω
Qg@type	28nC
ID	8A

APPLICATIONS

- High efficiency switch mode power supplies
- Electronic lamp ballasts based on half bridge
- LED power supplies

FEATURES

- * $R_{DS(ON)} = 1.1\Omega @ V_{GS} = 10V$
- * Ultra low gate charge
- * Low reverse transfer capacitance
- * Fast switching capability
- * Avalanche energy specified
- * Improved dv/dt capability, high ruggedness

ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT8N65F	TO-220F	50 pieces/Tube
N/A	MOT8N65A	TO-220	50 pieces/Tube

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V_{DSS}	650	V
Gate-Source Voltage		V_{GSS}	±30	V
Avalanche Current (Note 2)		I_{AR}	8	A
Drain Current	Continuous	I_D	8	A
	Pulsed (Note 2)	I_{DM}	32	A
Avalanche Energy	Single Pulsed (Note 3)	E_{AS}	230	mJ
	Repetitive (Note 2)	E_{AR}	14.7	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	4.5	V/ns
Power Dissipation	TO-220	P_D	147	W
	TO-220F		48	W
Junction Temperature		T_J	+150	°C
Operating Temperature		T_{OPR}	-55 ~ +150	°C
Storage Temperature		T_{STG}	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.



Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Repetitive Rating : Pulse width limited by T_J


3. $L = 7.1\text{mH}$, $I_{AS} = 8\text{A}$, $V_{DD} = 50\text{V}$, $R_G = 25\Omega$, Starting $T_J = 25^\circ\text{C}$

4. $I_{SD} \leq 8\text{A}$, $di/dt \leq 200\text{A}/\mu\text{s}$, $V_{DD} \leq BV_{DSS}$, Starting $T_J = 25^\circ\text{C}$

Symbol



TO-220



TO-220F




■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)


PARAMETER		SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage		BV _{DSS}	V _{GS} = 0 V, I _D = 250 μA	650			V
Drain-Source Leakage Current		I _{DSS}	V _{DS} = 650 V, V _{GS} = 0 V			10	μA
Gate-Source Leakage Current	Forward	I _{GSS}	V _{GS} = 30 V, V _{DS} = 0 V			100	nA
	Reverse		V _{GS} = -30 V, V _{DS} = 0 V			-100	nA
Breakdown Voltage Temperature Coefficient		ΔBV _{DSS} /ΔT _J	I _D =250μA,Referenced to 25°C		0.7		V/°C
ON CHARACTERISTICS							
Gate Threshold Voltage		V _{GS(TH)}	V _{DS} = V _{GS} , I _D = 250 μA	2.0		4.0	V
Static Drain-Source On-State Resistance		R _{DS(ON)}	V _{GS} = 10 V, I _D = 4A		0.95	1.1	Ω
DYNAMIC CHARACTERISTICS							
Input Capacitance		C _{ISS}	V _{DS} = 25 V, V _{GS} = 0V, f = 1MHz		965	1255	pF
Output Capacitance		C _{OSS}			105	135	pF
Reverse Transfer Capacitance		C _{RSS}			12	16	pF
SWITCHING CHARACTERISTICS							
Turn-On Delay Time		t _{D(ON)}	V _{DD} = 325V, I _D =8A, R _G = 25Ω (Note 1, 2)		16.5	45	ns
Turn-On Rise Time		t _R			60.5	130	ns
Turn-Off Delay Time		t _{D(OFF)}			81	170	ns
Turn-Off Fall Time		t _F			64.5	140	ns
Total Gate Charge		Q _G	V _{DS} = 520V,I _D =8A, V _{GS} = 10 V (Note 1, 2)		28	36	nC
Gate-Source Charge		Q _{GS}			4.5		nC
Gate-Drain Charge		Q _{GD}			12		nC
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS							
Drain-Source Diode Forward Voltage		V _{SD}	V _{GS} = 0 V, I _S =8A			1.4	V
Maximum Continuous Drain-Source Diode Forward Current		I _S				8	A
Maximum Pulsed Drain-Source Diode Forward Current		I _{SM}				32	A
Reverse Recovery Time		t _{RR}	V _{GS} = 0 V, I _S =8A,		365		ns
Reverse Recovery Charge		Q _{RR}	dl _F /dt = 100 A/μs (Note 2)		3.4		μC

Notes: 1. Pulse Test: Pulse width $\leq 300\mu\text{s}$, Duty cycle $\leq 2\%$
2. Essentially independent of operating temperature

■ TEST CIRCUITS AND WAVEFORMS




Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms


TEST CIRCUITS AND WAVEFORMS(Cont.)




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform









Unclamped Inductive Switching Test Circuit








Unclamped Inductive Switching Waveforms

■ TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS(Cont.)



Technical drawing of a mechanical part, showing three views: front, side, and top. The drawing includes dimensions and tolerances in millimeters.

Front View Dimensions:

- Overall width: 10.06 ± 0.15
- Overall height: 15.87 ± 0.15
- Top section width: 7.00 ± 0.15
- Top section height: 3.30
- Bottom section height: 4.90
- Central circular feature diameter: $3 \times \varnothing 1.50$
- Vertical slot width: 8.0
- Vertical slot depth: 12.93 ± 0.3
- Vertical slot width: $3 \times 1.38 \pm 0.1$
- Vertical slot depth: (9.75)
- Vertical slot width: 0.80
- Vertical slot depth: (3.18)
- Vertical slot width: 2.54
- Vertical slot depth: 2.54

Side View Dimensions:

- Overall width: 4.70 ± 0.1
- Overall height: 6.68 ± 0.1
- Top section width: 2.54 ± 0.15
- Top section height: 5°
- Bottom section height: $1.00 \times 45^\circ$
- Bottom section width: 0.50
- Bottom section height: 2.82 ± 0.1
- Bottom section width: 5°

Top View Dimensions:

- Overall width: 10.60 ± 0.15
- Overall height: 15.87 ± 0.15
- Top section width: $3 \times \varnothing 1.50$
- Top section height: 1.80
- Bottom section height: 10.60 ± 0.15
- Bottom section width: 0.50

■ TO-220-3L PACKAGE OUTLINE DIMENSIONS

