

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

C O N T E N T S

	Sheet
1. Application	3
2. Part Number System	3
3. Characteristics	4~10
3.1 Rated voltage & Surge voltage	
3.2 Capacitance (Tolerance)	
3.3 ESR	
3.4 Leakage current	
3.5 Temperature characteristic	
3.6 Load life test	
3.7 Damp heat test	
3.8 Terminal strength	
3.9 Resistance to vibration	
3.10 Solderability	
3.11 Resistance to soldering heat	
4. Product Dimensions	11
5. Notice item	12

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	2
STANDARD MANUAL				


ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

1. Application

The specification applies to electric double layer capacitors used in electronic equipment.

2. Part Number System



2.1 Capacitance code

Code	127
Capacitance (F)	120

2.2 Rated voltage code

Code	0T
Voltage (W.V.)	2.7

2.3 Type

Code	SZ
Type	Z-TYPE

2.4 Capacitance tolerance

“O” stands for 0% ~ +30%

2.5 Diameter

Code	O
Diameter	25

2.6 Case length

45=45mm

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	3
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

3. Characteristics

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature: 15°C to 35°C

Relative humidity : 25% to 75%

Air Pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature: 20°C ± 2°C

Relative humidity : 60% to 70%

Air Pressure : 86kPa to 106kPa


Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is -40°C to 60°C.

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	4
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

ITEM		PERFORMANCE				
3.1	Rated voltage (WV)	<table><tr><td>WV (V.DC)</td><td>2.7</td></tr><tr><td>SV (V.DC)</td><td>2.8</td></tr></table>	WV (V.DC)	2.7	SV (V.DC)	2.8
	WV (V.DC)	2.7				
SV (V.DC)	2.8					
	Surge voltage (SV)					
3.2	Nominal capacitance (Tolerance)	<Condition> Constant current discharge method: Measuring circuit: Constant current / constant voltage power supply  Constant Current Discharger Key $\textcircled{A}$ d.c. ammeter $\textcircled{V}$ d.c. voltmeter - S changeover switch - Cx capacitor under test Figure 1- Circuit for constant current discharge method Measuring method - Set the d.c.voltage at the rated voltage (U_R) - Set the constant current value of the constant current discharger to the discharge current specified in Table 1. - Turn the switch S to the d.c.power supply ,apply voltage and charge for 30 min after the constant current / constant voltage power supply has achieved the rated voltage. - After a charge for 30 min has finished ,change over the switch S to the constant current discharger ,and discharge with a constant current. - Measure the time t_1 and t_2 where the voltage between capacitor terminals at the time of discharge reduces from U_1 to U_2 as shown in Figure 2 ,and calculate the capacitance value by the following formula:				

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	5
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

<Condition>




Figure 2- Voltage characteristic between capacitor terminals

$$C = \frac{I \times (t_2 - t_1)}{U_1 - U_2}$$

Where

- C is the capacitance(F);
- I is the discharge current (A);
- U_1 is the measurement starting voltage (V);
- U_2 is the measurement end voltage (V);
- t_1 is the time from discharge start to reach U_1 (s);
- t_2 is the time from discharge start to reach U_2 (s).

f) The discharge current I and the voltages U_1 and U_2 at the time of discharge voltage drop shall be as per Table 1 .The method classification shall be in accordance with the individual standards.

Table 1 – Discharge conditions

Charge time	30 min
I (mA)	$4 \times C U_R$
U_1	The value to be 80% of the charging voltage ($0.8 \times U_R$)
U_2	The value to be 40% of the charging voltage ($0.4 \times U_R$)
NOTE C_R is the rated capacitance in F(Farad),and U_R is the rated voltage in V (Volt)	

3.2

Nominal
capacitance
(Tolerance)

Issue Date : 2017-07-07

Name

Specification Sheet – DRL

Version

01

Page

6

STANDARD MANUAL

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

3.3	ESR	<Condition> Measuring frequency :1kHz Measuring temperature:20±2℃ Measuring point : 2mm max from the surface of a sealing resin on the lead wire. <Criteria> (20℃)Less than the initial limit: <table><tr><td>Rated Voltage (V)</td><td>Capacitance (F)</td><td>Dimension (D×L, mm)</td><td>ESR, AC (mΩ) (max) at 1kHz/20℃</td></tr><tr><td>2.7</td><td>120</td><td>25X45</td><td>18</td></tr></table>	Rated Voltage (V)	Capacitance (F)	Dimension (D×L, mm)	ESR, AC (mΩ) (max) at 1kHz/20℃	2.7	120	25X45	18																
Rated Voltage (V)	Capacitance (F)	Dimension (D×L, mm)	ESR, AC (mΩ) (max) at 1kHz/20℃																							
2.7	120	25X45	18																							
3.4	Leakage current	<Condition> 1. Ambient temperature: 25℃±2℃. 2.The electrification time:72H 3. Desistance value of protective resistor less than 1Ω. <Criteria> Less than the initial limit(25℃±2℃): I≤0.550mA I is the Leakage current																								
3.5	Temperature characteristic	<Condition> <table><tr><td>STEP</td><td>Temperature(℃)</td><td>Item</td><td>Characteristics</td></tr><tr><td>1</td><td>20±2</td><td>Capacitance、 ESR</td><td>-----</td></tr><tr><td rowspan="2">2</td><td rowspan="2">-40+3</td><td>ΔC/C</td><td>Within ±30% of initial capacitance</td></tr><tr><td>ESR</td><td>Less than or equal to 4 times of the value of item 3.3</td></tr><tr><td>3</td><td>Keep at 15 to 35℃ for 15 minutes or more</td><td>-----</td><td>-----</td></tr><tr><td rowspan="2">4</td><td rowspan="2">60±2</td><td>ΔC/C</td><td>Within ±30% of initial capacitance</td></tr><tr><td>ESR</td><td>The limit specified in 3.3</td></tr></table> a. ESR -40℃/ ESR 20℃: ESR ratio at 1kHz; b. ΔC/C 20℃: Capacitance change ;	STEP	Temperature(℃)	Item	Characteristics	1	20±2	Capacitance、 ESR	-----	2	-40+3	ΔC/C	Within ±30% of initial capacitance	ESR	Less than or equal to 4 times of the value of item 3.3	3	Keep at 15 to 35℃ for 15 minutes or more	-----	-----	4	60±2	ΔC/C	Within ±30% of initial capacitance	ESR	The limit specified in 3.3
STEP	Temperature(℃)	Item	Characteristics																							
1	20±2	Capacitance、 ESR	-----																							
2	-40+3	ΔC/C	Within ±30% of initial capacitance																							
		ESR	Less than or equal to 4 times of the value of item 3.3																							
3	Keep at 15 to 35℃ for 15 minutes or more	-----	-----																							
4	60±2	ΔC/C	Within ±30% of initial capacitance																							
		ESR	The limit specified in 3.3																							

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	7
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS


DRL SERIES

3.6	Load life test	<Condition> The Capacitor is stored at a temperature of 60 ±2 °C with rated voltage for 1000 +48/0 hours .The result should meet the following table: <Criteria> <table><tr><td>Item</td><td>Performance</td></tr><tr><td>Capacitance Change</td><td>Within ±30% of initial capacitance</td></tr><tr><td>ESR</td><td>Less than or equal to 4 times of the value of item 3.3</td></tr><tr><td>Appearance</td><td>No visible damage and no leakage of electrolyte</td></tr></table>	Item	Performance	Capacitance Change	Within ±30% of initial capacitance	ESR	Less than or equal to 4 times of the value of item 3.3	Appearance	No visible damage and no leakage of electrolyte
Item	Performance									
Capacitance Change	Within ±30% of initial capacitance									
ESR	Less than or equal to 4 times of the value of item 3.3									
Appearance	No visible damage and no leakage of electrolyte									
3.7	Damp heat test	<Condition> Humidity Test: The capacitor shall be exposed for 240±48 hours in an atmosphere of 90~95%RH at 40±2°C, the characteristic change shall meet the following requirement. <Criteria> <table><tr><td>Item</td><td>Performance</td></tr><tr><td>Capacitance Change</td><td>Within ±30% of initial capacitance</td></tr><tr><td>ESR</td><td>Less than or equal to 4 times of the value of item 3.3</td></tr><tr><td>Appearance</td><td>No visible damage and no leakage of electrolyte</td></tr></table>	Item	Performance	Capacitance Change	Within ±30% of initial capacitance	ESR	Less than or equal to 4 times of the value of item 3.3	Appearance	No visible damage and no leakage of electrolyte
Item	Performance									
Capacitance Change	Within ±30% of initial capacitance									
ESR	Less than or equal to 4 times of the value of item 3.3									
Appearance	No visible damage and no leakage of electrolyte									

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	8
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

3.8	Terminal strength	<Condition> A static load of 25N (2.5kgf) shall be applied to the lead wire terminal in the axial direction away from the capacitor body for 30s. <Criteria> There shall be no intermittent contacts, open or short circuit and there shall be no mechanical damage such as terminal damage.				
3.9	Vibration test	<Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range : 10Hz ~ 55Hz Peak to peak amplitude : 1.5mm Sweep rate : 10Hz ~ 55Hz ~ 10Hz in about 1 minute <Criteria> After the test, the following items shall be tested: <table><tr><td>Appearance</td><td>No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.</td></tr><tr><td>Inner construction</td><td>No intermittent contact, open or short circuit. No damage of tab terminals or electrodes.</td></tr></table> Mounting method: The capacitor must be fixed in place with a bracket. 	Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.	Inner construction	No intermittent contact, open or short circuit. No damage of tab terminals or electrodes.
Appearance	No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.					
Inner construction	No intermittent contact, open or short circuit. No damage of tab terminals or electrodes.					

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	9
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

3.10	Solderability	The capacitor shall be tested under the following conditions: Solder : Sn-3Ag-0.5Cu Soldering temperature: 245±3°C Immersing time : 2.0±0.5s Immersing depth : 1.5~ 2.0mm from the root. Flux : Approx .25% rosin in ETHANOL Performance: At least 75% of the dipped portion of the terminal shall be covered with new solder.						
3.11	Resistance to soldering heat	A) Solder bath method Lead terminals of a capacitor are placed on the heat isolation board with thickness of 1.6±0.5mm. It will dip into the flux of isopropylalcohol solution of colophony. Then it will be immersed at the surface of the solder with the following condition: Solder : Sn-3Ag-0.5Cu Soldering temperature : 260 ±5°C Immersing time : 5±0.5s Heat protector: t=1.6mm glass –epoxy board B) Soldering iron method Bit temperature : 350 ±10°C Application time : 3.5 ±0.5 s Heat protector: t=1.6mm glass –epoxy board For both methods, after the capacitor at thermal stability, the following items shall be measured: <table><tr><td>Item</td><td>Performance</td></tr><tr><td>Capacitance Change</td><td>Within ±10% of initial capacitance</td></tr><tr><td>Appearance</td><td>No visible damage legible marking and no leakage of electrolyte</td></tr></table>	Item	Performance	Capacitance Change	Within ±10% of initial capacitance	Appearance	No visible damage legible marking and no leakage of electrolyte
Item	Performance							
Capacitance Change	Within ±10% of initial capacitance							
Appearance	No visible damage legible marking and no leakage of electrolyte							

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	10
STANDARD MANUAL				


ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

4. Product Dimensions

Unit: mm

Z-TYPE



Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	11
STANDARD MANUAL				

ELECTRIC DOUBLE LAYER CAPACITORS SPECIFICATIONS

DRL SERIES

5 . Notice item

- (1) The capacitor has fixed polarity.
- (2) The capacitor should be used under rated voltage.
- (3) The capacitor should not be used in the charge and discharge circuit with high frequency.
- (4) The ambient temperature affects the super capacitor life.
- (5) Voltage reduction $\Delta V=IR$ will happen at the moment of discharge.
- (6) The capacitor cannot be stored on the place with humidity over 85%RH or place with toxic gas.
- (7) The capacitor should stored in the environment within $-30^{\circ}\text{C}\sim 50^{\circ}\text{C}$ temperature and less than 60% relative humidity.
- (8) If the capacitor is applied on the double-side PCB, the connection should not be around the place on which the super capacitor can contact.
- (9) Don't twist capacitor or make it slanting after installing.
- (10) Need avoid over heat on the capacitor during soldering (The temperature should be 260°C with the time less than 5s during soldering on 1.6mm printed PCB.)
- (11) There is voltage balance problem between each capacitor unit during series connection between super capacitor.

Issue Date : 2017-07-07	Name	Specification Sheet – DRL		
Version	01		Page	12
STANDARD MANUAL				