




FRONT VIEW




RIGHT SIDE VIEW



BOTTOM VIEW



RECOMMENDED PCB LAYOUT VIEWED FROM COMPONENT SIDE



XKB Connectivity

**MATERIAL 材料:**

HOUSING 外壳: PBT,UL94V-0,BLACK.  
 TERMINALS BRACKET 端子支架: PBT,UL94V-0,RED.  
 TERMINAL 端子: PHOSPHOR BRONZE T=0.30MM  
 GOLD PLATING ON CONTACT AREA.

**MECHANICAL 机械:**

DURABILITY 耐用性: 750 CYCLES MIN,12.5MM/MINUTE.  
 INSERTION FORCE 插入力:2.2KG.F MAX  
 RETENTION STRENGTH 保持力:7.7KG.F BETWEEN JACK AND PLUG.  
 OPERATING TEMPERATURE 工作温度: -40°C~+85°C.  
 STORAGE TEMPERATURE 储存温度: -40°C~+85°C.  
 ALL CRITICAL DIMENSIONS WITH "\*"

**ELECTRICAL 电气:**

VOLTAGE 电压: 125 VOLTS AC.  
 CURRENT RATING 电流额定值: 1.5AMP.  
 DIELECTRIC STRENGTH 介电强度: 1000 VAC RMS 50HZ OR 60HZ,1 MIN  
 INSULATION RESISTANCE 绝缘电阻: 500 MEGA OHMS MIN.INITIAL  
 AFTER 500V DC FOR 1 MINUTE.  
 CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX.  
 INITIAL 50 MILLIOHMS MAX. AFTER  
 DURABILITY TEST.

广东星坤科技股份有限公司

△X	日期
△X	日期
△X	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	DESCRIPTION

UNSPECIFIED TOLERANCES

DSND	SCALE: N/A	MODEL TYPE: RJ JACK
DWN	VIEW:	PART NO.:
CHKD	UNIT: mm/in	DWG NO.: X02AKIWA1DB4134
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO.,LIMITED		SHEET 1/1
		REVISION: A0