



Surface Mount Schottky Barrier Rectifier

Reverse Voltage - 40 to 200 V

Forward Current - 1.0A

FEATURES

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case: SOD-323HE
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 5.4mg/0.00019oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Simplified outline SOD-323HE and symbol







Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SS14HS	SS16HS	SS110HS	SS115HS	SS120HS	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	40	60	100	150	200	V
Maximum RMS voltage	V_{RMS}	28	42	70	105	140	V
Maximum DC Blocking Voltage	V_{DC}	40	60	100	150	200	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$			1.0			A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}			25			A
Max Instantaneous Forward Voltage at 1 A	V_F	0.55	0.70	0.85	0.95		V
Maximum DC Reverse Current $T_a = 25^\circ C$ at Rated DC Reverse Voltage $T_a = 100^\circ C$	I_R	0.5 20		0.3 15			mA
Typical Junction Capacitance ⁽¹⁾	C_j	60		40			pF
Typical Thermal Resistance ⁽²⁾	$R_{\theta JA}$			150			°C/W
Operating Junction Temperature Range	T_j			-55 ~ +125			°C
Storage Temperature Range	T_{stg}			-55 ~ +150			°C

(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C.

(2) P.C.B. mounted with 8X 8 mm copper pad areas.






PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-323HE




Top View

Bottom View

UNIT		A	b	B	C	D	E	H _E	g	L	∠
mm	max	0.77	0.75	0.95	0.20	1.45	2.3	2.7	1.55	0.8	12°
	min	0.57	0.45	0.65	0.10	1.25	2.1	2.3	1.1	0.4	
mil	max	30	30	37	8	57	91	106	61	31	12°
	min	22	18	26	4	49	83	91	43	16	

The recommended mounting pad size



Marking

Type number	Marking code
SS14HS	K4
SS16HS	K6
SS110HS	K10
SS115HS	K15
SS120HS	K20



Important Notice and Disclaimer

Jingdao Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Jingdao Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Jingdao Microelectronics assume any liability for application assistance or customer product design.

Jingdao Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Jingdao Microelectronics.

Jingdao Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of Jingdao Microelectronics.