



上海立凯电控科技有限公司
Shanghai LineKey Technology Co., Ltd.



Specification For Approval

规格书

客户名称:

部件名称:

叠层射频电感

客户料号:

立凯料号:

HFM0603CQ-3N9S

供方确认			客户确认
制作	审核	核准	
吴子晗	薄双燕	陈余想	

Spec 变更记录:

版本	序号	更改描述	更改原因	备注
A0	01	Released		

地址: 上海市浦东新区商城路800号斯米克大厦1102室

电话: 021-61993616

邮箱: Sales@linekey.cn

网址: www.linekey.cn

Add: No.1101, Pudong South Road, Shanghai, China

Tel: 021-61993616

E-mail: Sales@linekey.cn

Website: www.linekey.cn

客户/CLIENT:
承制方/MANUFACTURER: 上海立凯电控科技有限公司

型号/MODEL: HFM0603CQ-3N9S
版本/REV.: A0 页数: 2/4

1. Scope

This specification applies to HFM0603CQ-3N9S SMD multilayer RF inductor.

2. Product Description and Identification (Part Number)

HFM 0603CQ - 3N9 S
① ② ③ ④

- ① Product Series: HFM Series
- ② Size: 0.6mm×0.3mm×0.3mm
- ③ Inductance: 3N9 = 3.9nH
- ④ Tolerance: S=±0.3nH





3. Operating & Storage Temperature

- 1) Operating temperature range : -55℃ ~ +125℃ (Including Self-heating) .

4. Shape and Dimensions (Unit: mm)

Dimensions and recommended PCB pattern for reflow soldering



Series	L(mm)	W(mm)	T(mm)	D(mm)	E(mm)	F(mm)	G(mm) .
HFW0603	0.6±0.03	0.3±0.03	0.3±0.03	0.15±0.05	0.3 Typ.	0.3 Typ	0.8 Typ.

5. Electrical Characteristics

Part Number	Inductance (nH)	Tolerance	Q Value (Min)	Test Freq. L/Q (MHz)	SRF Min. (GHz)	DCR Max(Ω)	Rated Current Max (mA)
HFM0603CQ-3N9S	3.9	±0.3nH	14	500	6.5	0.48	320

拟制/PREPARED BY:
吴子哈

审核/CHECKED BY:
薄双燕

批准/APPROVED BY:
陈余想

客户/CLIENT:

型号/MODEL: HFM0603CQ-3N9S

承制方/MANUFACTURER: 上海立凯电控科技有限公司

版本/REV.: A0


页数: 3/4

Note*

- 1) Rated Current: Max. DC current which causes 20K temperature rise from 20° C ambient;
- 2) Measuring Instrument: L/Q:CH-1062, DCR: HIOKI-3540, Rated Current:CH-1062

6. Typical Characteristic Chart

L/Q Vs. Frequency



拟制/PREPARED BY:

吴子晗

审核/CHECKED BY:

薄双燕

批准/APPROVED BY:

陈余想




客户/CLIENT:

型号/MODEL: HFM0603CQ-3N9S

承制方/MANUFACTURER: 上海立凯电控科技有限公司

版本/REV.: A0 页数: 4/4

6. Reliability Test

Items	Requirements	Test Methods and Remarks
6.1 Terminal Strength		1) Solder the inductor to the testing jig using eutectic solder. Then apply a force in the direction of the arrow. 2) No removal or split of the termination or other defects shall occur. 3) 10N force. 4) Keep time: 5±2s.
6.2 High Temperature	1) No visible mechanical damage. 2) Inductance change: Within ±10%	1) Storage Temperature :125+/-5°C. 2) Duration: 96 ±4 Hours. 3) Recovery: then measured at room ambient temperature after placing 24 hours.
6.3 Low Temperature	1) No visible mechanical damage. 2) Inductance change: Within ±10%	1) Storage Temperature :125+/-5°C 2) Duration: 96 ±4 Hour. 3) Recovery: then measured at room ambient temperature after placing 24 hours.
6.4 Vibration test	1) No visible mechanical damage. 2) Inductance change: Within ±10%	1) Frequency range:10HZ~55HZ~10HZ. 2) Amplitude:1.5mm p-p. 3) Direction: X, Y, Z. 4) Time:1 minute/cycle,2hours per axis
6.5 High Temperature Storage Tested	1) No visible mechanical damage. 2) Inductance change: Within ±10%	1) Storage Temperature :60+/-2°C. 2) Relative Humidity:90-95% RH. 3) Duration: 96 ±4 Hours. 4) Recovery: then measured at room ambient temperature after placing 24 hours.
6.6 Resistance to Soldering Heat	1) No visible mechanical damage. 2) Inductance change: Within ±10% 	1) Re-flowing Profile: Please refer to the left graph. 2) Test board thickness: 1.0mm. 3) Test board material: glass epoxy resin. 4) The chip shall be stabilized at normal condition for 1~2 hours before measuring.
6.7 Thermal Shock	1) No visible mechanical damage. 2) Inductance change: Within ±10% 	1) Temperature and time: -40±3°C for 30±3 min→105°C for 30±3min, please refer to the left graph. 2) Transforming interval: Max, 3 minutes 3) Tested cycle: 100 cycles. 4) The chip shall be stabilized at normal condition for 1~2 hours before measuring.

拟制/PREPARED BY:

吴子晗

审核/CHECKED BY:

薄双燕

批准/APPROVED BY:

陈余想