

NOTES1:

- UL Standard
1.Rated voltage/current : 300V / 15A
2.Withstanding voltage : AC1600V/1Min.

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
2.Pitch : 5.08mm, Poles : N=04~48P
3.Operating temperature: -40°C~+105°C
4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm			
Over	TO	Over	TO	Over	TO
6	10	30	60	100	150
TO	24	TO	100	TO	150
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00
				±1.30	±2

5.RoHS Compliance

Ordering Information






JL2EDGVT - 508 XX G 0 1

Pitch
508=5.08PH

No.of pins
4P~48P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
E=Grey

Packing
0=Pe bag
T=Tube
A=Tray



REVISION RECORD			
REV	ECN	DESCRIPTION	DATE

DRAW	SHUANGPING ZHENG		SCALE		FIT	PART NO.	
	UNIT	mm					
CHECK	LICHAD LIU		SIZE	A4	SHEET	1/1	JL2EDGVT-508XXG01
APPROVE	YONGLIANG GAO		PRD.		TITLE:	JL2EDGVT-5-08-2xNP插拔式公座/直脚/开口绿色	

jiln® 东莞市锦凌电子有限公司
DONGGUAN JINLING ELECTRONIC CO., LTD