

## Data sheet

US2:11CD3BF

Class 11, manual starter, 0.18-0.25 Amps, NEMA 1,



Figure similar

product brand name	Class 11
design of the product	Manual Starter
<strong>General technical data</strong>	
ambient temperature [°F]	
• during storage	122 ... 176 °F
• during operation	68 ... 140 °F
ambient temperature	
• during storage	50 ... 80 °C
• during operation	20 ... 60 °C
number of poles for main current circuit	3
<strong>Contactor</strong>	
mechanical service life (switching cycles) of the main contacts typical	100000
<strong>Coil</strong>	
type of voltage of the control supply voltage	n.a.
<strong>Overload relay</strong>	
adjustable current response value current of the current-dependent overload release	0.25 A
<strong>Mounting/wiring</strong>	
fastening method	wall mounting
<strong>Short-circuit current rating</strong>	
design of the short-circuit trip	magnetic
<strong>Certificates/ approvals</strong>	
certificate of suitability	UL
<strong>Further information</strong>	
Industrial Controls - Product Overview (Catalogs, Brochures,...)	
<a href="http://www.usa.siemens.com/iccatalog">www.usa.siemens.com/iccatalog</a>	
Industry Mall (Online ordering system)	
<a href="https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:11CD3BF">https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:11CD3BF</a>	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
<a href="https://support.industry.siemens.com/cs/US/en/ps/US2:11CD3BF">https://support.industry.siemens.com/cs/US/en/ps/US2:11CD3BF</a>	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	
<a href="http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:11CD3BF&amp;lang=en">http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:11CD3BF&amp;lang=en</a>	
Certificates/approvals	
<a href="https://support.industry.siemens.com/cs/US/en/ps/US2:11CD3BF/certificate">https://support.industry.siemens.com/cs/US/en/ps/US2:11CD3BF/certificate</a>	