




Product Summary

- 60V/ 5A
- $R_{DS(ON)} = 25m\Omega$ (Typ) @ $V_{GS} = -10V$
- $R_{DS(ON)} = 30m\Omega$ (Typ) @ $V_{GS} = -4.5V$
- Reliable and Rugged
- Lead Free and Green Devices Available
(RoHS Compliant)


Application

- DC-DC Converters.
- Load Switch.
- Power Management.


Package and Pin Configuration



Circuit diagram



Marking:



“P” is TECHPUBLIC LOGO

“4N” is Part Number,fixed

“xx” is internal code

Absolute Maximum Ratings ($T_A=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	5	A
Pulsed Drain Current (note 1)	I_{DM}	30	A
Power Dissipation	P_D	1.7	A
Thermal Resistance from Junction to Ambient (note 2)	$R_{\theta JA}$	106	°C/W
Junction Temperature	T_J	150	°C
Storage Temperature	T_{STG}	-55~+150	°C




Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}}=0\text{V}, I_D=250\mu\text{A}$	60			V
Gate-Threshold Voltage ^(Note3)	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}}=V_{\text{GS}}, I_D=250\mu\text{A}$	1.0		3.0	V
Gate-Body Leakage Current	I_{GSS}	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}}=60\text{V}, V_{\text{GS}}=0\text{V}$			1	μA
Drain-Source On-Resistance ^(Note3)	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}}=10\text{V}, I_D=3\text{A}$ $V_{\text{GS}}=4.5\text{V}, I_D=3\text{A}$		25	29	$\text{m}\Omega$
Forward Transconductance ^(Note3)	g_{fs}	$V_{\text{DS}}=5\text{V}, I_D=4.5\text{A}$		30	35	
Dynamic Characteristics^(Note4)						
Input Capacitance	C_{iss}	$V_{\text{DS}}=30\text{V}, V_{\text{GS}}=0\text{V}, f=1\text{MHz}$		500		pF
Output Capacitance	C_{oss}			60		
Reverse Transfer Capacitance	C_{rss}			25		
Switching Characteristics^(Note4)						
Total Gate Charge	Q_g	$V_{\text{DS}}=48\text{V}, V_{\text{GS}}=10\text{V}, I_D=15\text{A}$		12		nC
Gate-Source Charge	Q_{gs}			4.1		
Gate-Drain Charge	Q_{gd}			4.5		
Turn-on Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{DD}}=30\text{V}, V_{\text{GS}}=10\text{V}, I_D=2\text{A}, R_G=3\Omega, R_L=6.7\Omega$		5.0		ns
Turn-on Rise Time	t_r			2.6		
Turn-off Delay Time	$t_{\text{d}(\text{off})}$			16.1		
Turn-off Fall Time	t_f			2.3		
Drain-Source Diode Characteristics						
Diode Forward Voltage ^(Note3)	V_{SD}	$V_{\text{GS}}=0\text{V}, I_s=20\text{A}$			1.2	V
Diode Forward Current ^(Note2)	I_s				20	A
Reverse Recovery Time	t_{rr}	$I_F=20\text{A}, di/dt=100\text{A}/\mu\text{s}$ ^(Note4)		35		μC
Reverse Recovery Charge	Q_{rr}			53		
Forward Turn-On Time	t_{on}	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)				



SOT23-6 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°