



HIGH-SIDE AND LOW-SIDE GATE DRIVERS IN SO-16

Description


The DGD2110 and DGD2113 are high-voltage/high-speed MOSFET and IGBT drivers with independent high-side and low-side outputs. The high-side driver features floating supply for operation at up to 500V/600V. The 10ns (max)/20ns (max) propagation delay matching between the high- and the low side drivers allows high-frequency operation.

The DGD2110 and DGD2113 logic inputs are compatible with standard CMOS levels (as low as 3.3V) while driver outputs feature high-pulse current buffers designed for minimum driver cross conduction.

The DGD2110 and DGD2113 are offered in a SO-16 package. They operate over an extended -40°C to +125°C temperature range.

Applications

- DC-DC Converters
- DC-AC Inverters
- AC-DC Power Supplies
- Motor Controls
- Class D Power Amplifiers



Features

- Drives two N-Channel MOSFETs or IGBTs in High-Side/Low-Side Configuration
- Floating High-Side Operates to 600V
- 2.5A Sink/2.5A Source Typical Output Currents
- Outputs Tolerant To Negative Transients
- Wide Gate Driver Supply Voltage Range: 10V to 20V
- Wide Logic Input Supply Voltage Range: 3.3V to 20V
- Wide Logic Supply Offset Voltage Range: -5V to 5V
- 15ns (typ) Rise/13ns (typ) Fall Times with 1000pF load
- 105ns (typ) Turn-On/94ns (typ) Turn-Off Delay Times
- Cycle-by-Cycle Edge-Triggered Shutdown Circuitry
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Case: SO-16 (Type TH)
- Case Material: Molded Plastic. "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish—Matte Tin Plated Leads,
 Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.130 grams (Approximate)



Top View

Ordering Information (Note 4)

Product	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
DGD2110S16-13	DGD2110	13	16	1500
DGD2113S16-13	DGD2113	13	16	1500

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.


Marking Information



J;| = Manufacturer's Marking
DGD211x = Product Type Marking Code (See Table Above)
YY = Year (ex: 19 = 2019)
WW = Week (01 - 53)



Pin Diagrams




Top view: SO-16

Pin Descriptions

Pin Number	Pin Name	Function
1	LO	Low-side gate driver output pin
2	COM	Low-side gate driver power supply return pin
3	Vcc	Low-side gate driver power supply pin
4,5,9,10,16	NC	No connect pin (No Internal Connection)
6	Vs	High-side gate driver floating power supply return pin
7	V _B	High-side gate driver floating power supply pin
8	НО	High-side gate drive output pin
11	V_{DD}	Logic power supply pin
12	HIN	Logic input pin for high-side gate driver output. HIN and HO are in phase
13	SD	Logic input shutdown pin
14	LIN	Logic input pin for low-side gate driver output. LIN and LO are in phase
15	V_{SS}	Logic ground pin

Functional Block Diagram





Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
High-Side Floating Supply Voltage (DGD2110)	V _B	-0.3 to +524	V
High-Side Floating Supply Voltage (DGD2113)	V _B	-0.3 to +624	V
High-Side Floating Supply Offset Voltage	Vs	V _B -24 to V _B +0.3	V
High-Side Floating Output Voltage	V_{HO}	V _S -0.3 to V _S +0.3	V
Offset Supply Voltage Transient	dV _S / dt	50	V/ns
Low-Side Fixed Supply Voltage	Vcc	-0.3 to +24	V
Low-Side Output Voltage	V_{LO}	-0.3 to V _{CC} +0.3	V
Logic Supply Voltage	V_{DD}	-0.3 to V _{SS} +24	V
Logic Supply Offset Voltage	V _{SS}	V _{CC} -24 to V _{CC} +0.3	V
Logic Input Voltage (HIN, LIN, and SD)	V _{IN}	V _{SS} -0.3 to V _{DD} +0.3	V

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation Linear Derating Factor (Note 5)	P _D	1.25	W
Thermal Resistance, Junction to Ambient (Note 5)	R _{0JA}	90	°C/W
Thermal Resistance, Junction to Case (Note 5)	ReJC	45	°C/W
Operating Temperature	T_J	+150	
Lead Temperature (Soldering, 10 seconds)	TL	+300	°C
Storage Temperature Range	T _{STG}	-55 to +150	

Note: 5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit	
High-Side Floating Supply Absolute Voltage	V _B	V _S + 10	V _S + 20	V	
High-Side Floating Supply Offset Voltage	DGD2110	Vs	(Note 6)	500	V
High-Side Floating Supply Offset Voltage	DGD2113	Vs	(Note 6)	600	V
High-Side Floating Output Voltage	V _{HO}	Vs	V _B	V	
Low-Side Fixed Supply Voltage		Vcc	10	20	V
Low-Side Output Voltage	V_{LO}	0	V _{CC}	V	
Logic Supply Voltage	V_{DD}	V _{SS} + 3	V _{SS} + 20	V	
Logic Supply Offset Voltage	V _{SS}	-5 (Note 7)	5	V	
Logic Input Voltage (HIN, LIN, and SD)	V _{IN}	V _{SS}	V_{DD}	V	
Ambient Temperature	T _A	-40	+125	°C	

Notes:

^{6.} Logic operation for $V_S = -4V$ to +500V.

^{7.} When V_{DD} <5V, the minumum V_{SS} offset is limited to - V_{DD} .



DC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}, V_{DD}) = 15V, V_{SS} = COM, @T_A = +25°C unless otherwise specified.) (Note 8)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Logic "1" Input Voltage (Note 9)	V _{IH}	9.5	_	_	V	_
Logic "0" Input Voltage (Note 9)	V_{IL}	_	_	6.0	V	_
High Level Output Voltage, V _{BIAS} - V _O	VoH	_	_	1.4	V	$I_O = 0mA$
Low Level Output Voltage, V _O	V_{OL}	_	_	0.15	V	I _O = 20mA
Offset Supply Leakage Current	I_{LK}	_	_	50	μΑ	$V_B = V_S = 500V/600V$
Quiescent V _{BS} Supply Current	I _{BSQ}	_	55	230	μA	V_{IN} = 0V or V_{DD}
Quiescent V _{CC} Supply Current	Iccq	_	56	340	μΑ	V_{IN} = 0V or V_{DD}
Quiescent V _{DD} Supply Current	I_{DDQ}	_	0.6	30	μA	V_{IN} = 0V or V_{DD}
Logic "1" Input Bias Current	I _{IN+}	_	20	40	μΑ	$V_{IN} = V_{DD}$
Logic "0" Input Bias Current	I _{IN-}	_	_	5.0	μΑ	$V_{IN} = 0V$
V _{BS} Supply Undervoltage Positive Going Threshold	V_{BSUV+}	7.5	8.6	9.7	V	_
V _{BS} Supply Undervoltage Negative Going Threshold	V_{BSUV-}	7.0	8.2	9.4	V	_
V _{CC} Supply Undervoltage Positive Going Threshold	V _{CCUV+}	7.4	8.5	9.6	V	_
V _{CC} Supply Undervoltage Negative Going Threshold	V _{CCUV} -	7.0	8.2	9.4	V	_
Output High Short Circuit Pulsed Current	I _{O+}	2.0	2.5	_	Α	$V_O = 0V$, $V_{IN} = V_{DD}$, PW $\leq 10\mu s$
Output Low Short Circuit Pulsed Current	I _{O-}	2.0	2.5	_	Α	V _O = 15V, V _{IN} = 0V, PW ≤ 10µs

Note:

AC Electrical Characteristics (V_{BIAS} (V_{CC}, V_{BS}, V_{DD}) = 15V, C_L = 1000pF, V_{SS} = COM, @T_A = +25°C, unless otherwise specified.)

Parameter		Symbol	Min	Тур	Max	Unit	Conditions
Turn-On Propagation Delay		t _{ON}	_	105	150	ns	$V_S = 0V$
Turn-Off Propagation Delay		toff	_	94	125	ns	V _S = 500V/600V
Shut Down Propagation Delay		t _{SD}	_	70	140	ns	V _S = 500V/600V
Turn-On Rise Time		t _r	_	15	35	ns	_
Turn-Off Fall Time		t _f	_	13	25	ns	_
Delay Matching	DGD2110	t _{DM}	_	_	10	_	_
Delay Matching	DGD2113	t _{DM}	_	_	20	_	_

^{8.} The V_{IN} and I_{IN} parameters are referenced to V_{SS} and are applicable to all three logic input pins: HIN, LIN, and SD. The V_O and I_O parameters are referenced to COM and are applicable to the respective output pins: HO and LO.

^{9.} For optimal operation, it is recommended that the input pulses (HIN and LIN) should have a minimum amplitude of 9.5V (VDD = 15V) with a minimum pulse width of 200ns.



Timing Waveforms




Figure 1. Input / Output Timing Diagram




Figure 2. Switching Time Waveform Definitions




Figure 3. Shutdown Waveform Definitions




Figure 4. Delay Matching Waveform Definitions



Typical Performance Characteristics (Vcc=15V, @TA = +25°C, unless otherwise specified.)




Figure 5. Turn-on Propogation Delay vs. Supply Voltage




Figure 6. Turn-on Propogation Delay vs. Temperature




Figure 7. Turn-off Propogation Delay vs. Supply Voltage




Figure 8. Turn-off Propogation Delay vs. Temperature




Figure 9. Rise Time vs. Supply Voltage




Figure 10. Rise Time vs. Temperature



Typical Performance Characteristics (continued)




Figure 11. Fall Time vs. Supply Voltage




Figure 13. Quiescent Current vs. Supply Voltage




Figure 15. Delay Matching vs. Supply Voltage




Figure 12. Fall Time vs. Temperature




Figure 14. Quiescent Current vs. Temperature




Figure 16. Delay Matching vs. Temperature



Typical Performance Characteristics (cont.)




Figure 17. Output Source Current vs. Supply Voltage




Figure 19. Output Sink Current vs. Supply Voltage Note: graphs overlap one another




Figure 21. Logic 1 Input Voltage vs. Supply Voltage




Figure 18. Output Source Current vs. Temperature




Figure 20. Output Sink Current vs. Temperature




Figure 22. Logic 1 Input Voltage vs. Temperature



Typical Performance Characteristics (cont.)




Figure 23. Logic 0 Input Voltage vs. Supply Voltage




Figure 25. V_{cc} UVLO vs. Temperature




Figure 27. Offset Supply Leakage Current vs. Temperature




Figure 24. Logic 0 Input Voltage vs. Temperature




Figure 26. V_{BS} UVLO vs. Temperature




Figure 28. V_s Maximum Offset vs. Supply Voltage



Typical Performance Characteristics (cont.)




Figure 29. Input Bias Current vs. Temperature




Figure 31. Turn-On Propagation Delay vs. Logic Supply Voltage




Figure 30. Input Voltage vs. Logic Supply Voltage




Figure 32. Turn-Off Propagation Delay vs. Logic Supply Voltage





Figure 33. Shutdown Propagation Delay vs. Logic Supply Voltage




Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-16 (Type TH)






SO-16 (Type TH)					
Dim	Min	Max	Тур		
Α	2.36	2.64			
A1	0.10	0.30			
b	0.33	0.51			
С	0.229	0.318			
D	10.11	10.46	10.29		
Е	10.01	10.64	10.33		
E1	7.42	7.59	7.52		
е			1.27		
h	-		0.48		
L	0.41	1.27			
θ	0°	8°			
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-16 (Type TH)



Dimensions	Value (in mm)
С	1.27
C1	8.46
Х	0.60
Υ	2.20

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com