





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2010.06.15	馮代勇
02	△	變更新圖號	2010.12.08	黃明霞



RECOMMENDED P.C.B LAYOUT
(Tolerance:±0.05)

Specifications
 Current Rating: 1.0Amp
 Insulation Resistance: 1000MΩ Min.
 Dielectric Withstanding: 300V AC
 Contact Resistance: 20mΩ Max.
 Operating Temperature: -40°C to +105°C
Materials
 Contact Material: Phosphor Bronze
 Insulator Material: Polyester UL94V-0
 LCP Or Equivalent material
 All materials must meet Greenconn requirement for environment protection.



Ordering Information

GPCC101 - XX XX A005 C 1 A X

No. of Pins per Row: 02~40
 Standard Plating: 02=Gold Flash, Selective plating: 01=Tin
 Standard: A=Box, Selective: C=Tube, D=Tape & Reel

格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X. ± 5.0°	X. ± 0.30
.X ± 3.0°	.X ± 0.25
.XX ± 2.0°	.XX ± 0.15
.XXX ± 1.0°	.XXX ± 0.10

DESIGN: 黃明霞	DATE: 2010.12.08
CHECKED: 李新華	DATE: 2010.12.08
AUDITED: LEAR	DATE: 2010.12.08
APPROVED: LINK	DATE: 2010.12.08

DWG. NO. △ GPCC101-CA5CA
PART NO. GPCC101-XXXXA005C1AX

TITLE:
 1.00 PIN HEADER
 SINGLE ROW SMT TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.	⊕
02	mm	6:1	1/1	⊕