




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2013.11.20	郭丙建



Recommended P.C.Board
Layout
(Tolerance: ± 0.05)



Specifications

Current Rating: 1.0Amp
 Insulation Resistance: 1000M Ω Min.
 Dielectric Withstanding: 300V AC
 Contact Resistance: 20m Ω Max.
 Operating Temperature: -40°C to +105°C
Materials
 Contact Material: Phosphor Bronze
 Insulator Material: Polyester UL94V-0
 LCP Or Equivalent material
 All materials must meet Greenconn
 requirement for environment protection.

Ordering Information

G PCA101-XX XX A 001 C 1 A X
 No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin
 05=Gold Flash /Tin
 Color 1=Black
 Standard Packing A=Box
 Selective Packing C=Tube

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGN:	郭丙建	DATE:	2013.11.20	DWG. NO.	TITLE. PITCH 1.00 HEADER SIGLE ROW DIP TYPE
X.* $\pm 5.0^\circ$	X. ± 0.30	CHECKED:	劉 蟬	DATE:	2013.11.20	GPCA101-CA1CA	
.X* $\pm 3.0^\circ$.X ± 0.25	AUDITED:	吳柏昌	DATE:	2013.11.20	PART NO. GPCA101-XX XX A001C1AX	
.XX* $\pm 2.0^\circ$.XX ± 0.15	APPROVED:	陳義昌	DATE:	2013.11.20		
.XXX* $\pm 1.0^\circ$.XXX ± 0.10						