

**MICROCHIP****HV809**

Offline High-Voltage EL Lamp Driver

Features

- Up to 200V DC Input Voltage
- 400V Peak-to-Peak Output Voltage
- Up to 350 nF Output Load
(100 in² for 3.5 nF/in² Lamp)
- Adjustable Output Lamp Frequency
- Adjustable On/Off Pulsing Frequency

Applications

- Electronic Organizers
- Handheld Portable Computers
- Display Signs
- Portable Instrumentation Equipment

General Description


The HV809 is an offline high-voltage EL lamp driver integrated circuit designed for driving EL lamps of up to 350 nF at 400 Hz. The input supply voltage can be a rectified nominal 120V AC source or any other DC source up to 200V. The HV809 supplies the EL lamp with an AC square wave with a peak-to-peak voltage of twice the input DC voltage.

The HV809 has two internal oscillators, a low-voltage output linear regulator, and a high-voltage output H-bridge. The high-voltage output H-bridge frequency is set by an external resistor connected between the REL-Osc and GND pins. The EL lamp is connected between the V_A and V_B pins. For the HV809 in the 8-pin package, an external RC network can be connected between the oscillator's Osc1 and Osc2 pins to pulse the EL lamp on and off.


For detailed circuit and application information, please refer to Application Note, *AN-H36*.

Package Types

**8-lead SOIC (Narrow Body)
(Top view)**




**8-lead SOIC (with Heat Slug)
(Top view)**



See [Table 2-1](#) for pin information.

HV809

Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings^t

High-Voltage Input, HV _{IN}	+210V
Internal Supply Voltage, V _{DD}	+15V
Maximum Junction Temperature, T _{JMAX}	+125°C
Storage Temperature, T _S	-55°C to +150°C
Power Dissipation:	
8-lead SOIC	500 mW
8-lead SOIC (with Heat Slug)	1.5 Watts

^t Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

RECOMMENDED OPERATING CONDITIONS

Parameter	Sym.	Min.	Typ.	Max.	Unit	Conditions
High-Voltage Input	HV _{IN}	50	—	200	V	
Load Capacitance	C _L	—	—	350	nF	R _{EL} = 1 MΩ, HV _{IN} = 170V
		—	—	150	nF	R _{EL} = 390 kΩ, HV _{IN} = 170V
Operating Temperature	T _A	-25	—	+85	°C	

DC ELECTRICAL CHARACTERISTICS

Electrical Specifications: Over recommended operating conditions unless otherwise indicated; T_A = 25°C

Parameter	Sym.	Min.	Typ.	Max.	Unit	Conditions
High-Voltage Supply Current	I _{IN}	—	—	70	mA	HV _{IN} = 170V, R _{EL} = 1 MΩ, CL = 350 nF
		—	—	9	mA	HV _{IN} = 170V, R _{EL} = 1 MΩ, CL = 50 nF
Quiescent Supply Current	I _{INQ}	—	—	400	μA	HV _{IN} = 170V, R _{EL} = 1 MΩ, Osc1 = GND, No load
		—	—	100	μA	HV _{IN} = 170V, R _{EL} = 1 MΩ, Osc1 = V _{DD} , No load
Osc2 Sink Current	I _{SINK}	—	300	—	μA	V _{Osc2} = 1V
Osc2 Source Current	I _{SOURCE}	—	100	—	μA	V _{Osc2} = V _{DD} –1V
Osc1 Logic Input Leakage Current	I _{Osc1}	—	±10	—	μA	V _{Osc1} = GND and V _{DD}
Osc1 Hysteresis Voltage	V _{Osc1(HYST)}	—	2.5	—	V	
Minimum Differential Output Voltage across Lamp	V _{A-B}	—	—	400	V	HV _{IN} = 200V
Internal Supply Voltage	V _{DD}	8	10	12	V	No load on V _{DD}

AC ELECTRICAL CHARACTERISTICS

Electrical Specifications: Over recommended operating conditions unless otherwise indicated; T_A = 25°C

Parameter	Sym.	Min.	Typ.	Max.	Unit	Conditions
V _{A-B} Output Drive Frequency	f _{EL}	320	400	480	Hz	R _{EL} = 1 MΩ, Osc1 = GND, C _L = 350 nF
		0.8	1	1.2	kHz	R _{EL} = 390 kΩ, Osc1 = GND, C _L = 150 nF
Output Rise Time	t _r	—	180	250	μs	C _L = 150 nF, HV _{IN} = 170V
Output Fall Time	t _f	—	50	100	μs	C _L = 150 nF, HV _{IN} = 170V

HV809

TEMPERATURE SPECIFICATIONS

Parameter	Sym.	Min.	Typ.	Max.	Unit	Conditions
TEMPERATURE RANGE						
Operating Ambient Temperature	T _A	-25	—	+85	°C	
Maximum Junction Temperature	T _{JMAX}	—	—	+125	°C	
Storage Temperature	T _S	-55	—	+150	°C	
PACKAGE THERMAL RESISTANCE						
8-lead SOIC	θ _{JA}	—	101	—	°C/W	
8-lead SOIC (with Heat Slug)	θ _{JA}	—	84	—	°C/W	

2.0 PIN DESCRIPTION

The details on the pins of HV809 8-lead SOIC (narrow body) and 8-lead SOIC (narrow body with heat slug) are listed on [Table 2-1](#). See [Package Types](#) for the location of pins.

TABLE 2-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Description
1	HVIN	High-voltage input supply pin
2	VDD	Internal supply voltage
3	Osc2	The RC network can be connected between the oscillator's Osc1 and Osc2 pins to pulse the EL lamp on and off.
4	Osc1	The Output H-bridge can be enabled and disabled by connecting the Osc1 pin to the GND and VDD pins. The output can be left enabled by connecting the Osc1 pin to GND.
5	REL-Osc	EL lamp frequency is controlled via an external REL resistor connected between the REL-Osc and GND pins of the device.
6	GND	Ground pin
7	VB	VB side of the EL lamp driver H-bridge. Connection for one of the EL lamp terminals.
8	VA	VA side of the EL lamp driver H-bridge. Connection for one of the EL lamp terminals.

Note 1: Heat slug is at ground potential.

HV809

3.0 FUNCTIONAL DESCRIPTION




FIGURE 3-1: Pulsing EL Lamp.




FIGURE 3-2: Push-button, Delayed Turn-off.




FIGURE 3-3: Typical Waveform on V_A and V_B and Differential Waveform V_A-V_B .


TABLE 3-1: FUNCTION TABLE

Inputs	Outputs	
Osc1	V_A	V_B
GND	Enabled	Enabled
V_{DD}	Disabled	Disabled


4.0 PACKAGING INFORMATION

4.1 Package Marking Information


8-lead SOIC




Example



8-lead SOIC




Example



Legend:	XX...X Product Code or Customer-specific information
Y	Year code (last digit of calendar year)
YY	Year code (last 2 digits of calendar year)
WW	Week code (week of January 1 is week '01')
NNN	Alphanumeric traceability code
(e3)	Pb-free JEDEC® designator for Matte Tin (Sn)
*	This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.

Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for product code or customer-specific information. Package may or not include the corporate logo.

8-Lead SOIC (Narrow Body) Package Outline (LG/TG)**4.90x3.90mm body, 1.75mm height (max), 1.27mm pitch**

Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Note:

1. This chamfer feature is optional. A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symbol	A	A1	A2	b	D	E	E1	e	h	L	L1	L2	θ	θ1
Dimension (mm)	MIN	1.35*	0.10	1.25	0.31	4.80*	5.80*	3.80*	1.27	0.25	0.40	1.04 REF	0°	5°
	NOM	-	-	-	-	4.90	6.00	3.90	BSC	-	-		-	-
	MAX	1.75	0.25	1.65*	0.51	5.00*	6.20*	4.00*		0.50	1.27	BSC	8°	15°


JEDEC Registration MS-012, Variation AA, Issue E, Sept. 2005.

* This dimension is not specified in the JEDEC drawing.

Drawings are not to scale.

8-Lead SOIC (Narrow Body w/Heat Slug) Package Outline (SG)

4.90x3.90mm body, 1.70mm height (max), 1.27mm pitch



Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Note:

1. If optional chamfer feature is not present, a Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symbol	A	A1	A2	b	D	D1	E	E1	E2	e	h	L	L1	L2	θ	θ_1	
Dimension (mm)	MIN	1.25*	0.00	1.25	0.31	4.80*	3.30†	5.80*	3.80*	2.29†	1.27 BSC	0.25	0.40	1.04	0.25 BSC	0°	5°
	NOM	-	-	-	-	4.90	-	6.00	3.90	-		-	-			-	-
	MAX	1.70	0.15	1.55*	0.51	5.00*	3.81†	6.20*	4.00*	2.79†		0.50	1.27	REF	BSC	8°	15°

JEDEC Registration MS-012, Variation BA, Issue E, Sept. 2005.

* This dimension is not specified in the JEDEC drawing.

† This dimension differs from the JEDEC drawing.

Drawings not to scale.

APPENDIX A: REVISION HISTORY

Revision A (August 2018)

- Converted Supertex Doc# DSFP-HV908 to Microchip DS20005630A
- Removed “Processed with HVCMOS® Technology” from the Features section
- Removed the “Output VDD Current” parameter from the DC Electrical Characteristics table
- Removed the 7-lead TO-220 package option
- Changed the quantity of the LG and SG packages from 2500/Reel to 3300/Reel
- Made minor text changes throughout the document

HV809

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO. Device	XX Package Options	-	X Environmental	-	X Media Type	Examples:
Device:	HV809	=	Offline High-Voltage EL Lamp Driver			a) HV809LG-G: Offline High-Voltage EL Lamp Driver, 8-lead SOIC Package, 3300/Reel
Packages:	LG	=	8-lead SOIC			b) HV809SG-G: Offline High-Voltage EL Lamp Driver, 8-lead SOIC Package (with Heat Slug), 3300/Reel
	SG	=	8-lead SOIC (with Heat Slug)			
Environmental:	G	=	Lead (Pb)-free/RoHS-compliant Package			
Media Type:	(blank)	=	3300/Reel for an LG Package			
	(blank)	=	3300/Reel for an SG Package			

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. **MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE.** Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMS, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949 =

Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, AVR, AVR logo, AVR Freaks, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, Kleer, LANCheck, LINK MD, maXStylus, maXTouch, MediaLB, megaAVR, MOST, MOST logo, MPLAB, OptoLynx, PIC, picoPower, PICSTART, PIC32 logo, Prochip Designer, QTouch, SAM-BA, SpyNIC, SST, SST Logo, SuperFlash, tinyAVR, UNI/O, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, EtherSynch, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and Quiet-Wire are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2018, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-3381-1



MICROCHIP

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta

Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX

Tel: 512-257-3370

Boston

Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago

Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas

Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit

Novi, MI
Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983

Indianapolis

Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles

Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC

Tel: 919-844-7510

New York, NY

Tel: 631-435-6000

San Jose, CA

Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto

Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733
China - Beijing
Tel: 86-10-8569-7000
China - Chengdu
Tel: 86-28-8665-5511
China - Chongqing
Tel: 86-23-8980-9588
China - Dongguan
Tel: 86-769-8702-9880
China - Guangzhou
Tel: 86-20-8755-8029
China - Hangzhou
Tel: 86-571-8792-8115
China - Hong Kong SAR
Tel: 852-2943-5100
China - Nanjing
Tel: 86-25-8473-2460
China - Qingdao
Tel: 86-532-8502-7355
China - Shanghai
Tel: 86-21-3326-8000
China - Shenyang
Tel: 86-24-2334-2829
China - Shenzhen
Tel: 86-755-8864-2200
China - Suzhou
Tel: 86-186-6233-1526
China - Wuhan
Tel: 86-27-5980-5300
China - Xian
Tel: 86-29-8833-7252
China - Xiamen
Tel: 86-592-2388138
China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444
India - New Delhi
Tel: 91-11-4160-8631
India - Pune
Tel: 91-20-4121-0141
Japan - Osaka
Tel: 81-6-6152-7160
Japan - Tokyo
Tel: 81-3-6880- 3770
Korea - Daegu
Tel: 82-53-744-4301
Korea - Seoul
Tel: 82-2-554-7200
Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906
Malaysia - Penang
Tel: 60-4-227-8870
Philippines - Manila
Tel: 63-2-634-9065
Singapore
Tel: 65-6334-8870
Taiwan - Hsin Chu
Tel: 886-3-577-8366
Taiwan - Kaohsiung
Tel: 886-7-213-7830
Taiwan - Taipei
Tel: 886-2-2508-8600
Thailand - Bangkok
Tel: 66-2-694-1351
Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393
Denmark - Copenhagen
Tel: 45-4450-2828
Fax: 45-4485-2829
Finland - Espoo
Tel: 358-9-4520-820
France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79
Germany - Garching
Tel: 49-8931-9700
Germany - Haan
Tel: 49-2129-3766400
Germany - Heilbronn
Tel: 49-7131-67-3636
Germany - Karlsruhe
Tel: 49-721-625370
Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44
Germany - Rosenheim
Tel: 49-8031-354-560
Israel - Ra'anana
Tel: 972-9-744-7705
Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781
Italy - Padova
Tel: 39-049-7625286
Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340
Norway - Trondheim
Tel: 47-7289-7561
Poland - Warsaw
Tel: 48-22-3325737
Romania - Bucharest
Tel: 40-21-407-87-50
Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91
Sweden - Gothenberg
Tel: 46-31-704-60-40
Sweden - Stockholm
Tel: 46-8-5090-4654
UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820