








REV	LOCAS	DESCRIPTION	DRAW	DATE
A1	NEW	INITIAL RELEASE	Long	2016.11.16
A2			LIU	2021.09.09



RECOMMENDED P.C.BOARD LAYOUT (TOP VIEW)
TOLERANCES UNLESS OTHERWISE SPEC.±0.05


PAD AREA KEEP OUT AREA



NOTES:

- MATERIAL:
 - HOUSING: THERMOPLASTIC UL 94V-0; COLOR: BLACK .
 - TERMINAL: COPPER ALLOY T=0.15mm;
 - SHELL: STAINLESS STEEL T=0.30mm;
- FINISH:
 - TERMINAL: GOLD FLASH PLATING ON CONTACT AREA, MATTE Sn 100u"Min PLATING ON SOLDER TAILS, NICKEL 50u"Min UNDERPLATING OVERALL.
 - SHELL: MATTE Sn 80u"Min OVERALL, NICKEL 50u"Min UNDERPLATING OVERALL.
- SPECIFICATIONS:
 - VOLTAGE RATING : 100VAC;
 - CURRENT RATING: 1.0A;
 - INSULATION RESISTANCE: 100MEG.OHM MIN.
 - CONTACT RESISTANCE: 50MILL.OHM MAX.
 - OPERATION TEMPERATURE: -20° TO +65°.
 - MATING FORCE: 35N MAX.
 - UNMATING FORCE: 8N MIN.
 - DURABILITY: 10000 CYCLES:

Ordering Information



MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)	DESIGN	Long	DATE	2016.11.16	TITLE:	MICRO USB 5PIN PH: 0.65mm H: 2.45mm DIP TYPE INSERT 0.80MM	
	CHECKED		DATE				
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	APPROVED		DATE				
	PART NO:	UA0507065245-56-08			REV: A2	SCALE: 1:1	UNIT: mm
	DRAWING NO:				SIZE: A4	SHEET: 1/1	



DongGuan D-CHAIN Precision Components CO, Ltd