









REV.	LOCALS.	DESCRIPTION	DRWN.	DATE.
01	NEW	INITIAL RELEASE.	LUU	2019.03.20
02		UPDATED	LUU	2021.06.29
03		UPDATED	Andy	2022.06.14

- NOTES:
- MATERIAL:
    - HOUSING: THERMOPLASTIC; UL 94V-0; COLOR: BLACK
    - CANTACT TERMINAL: COPPER ALLOY
  - FINISH:
    - CONTACT: Au PLATING ON CONTACT AREA AND ON SOLDER TAILS, 50µ" NICKEL UNDERPLATING OVER ALL.
  - SPECIALITY:
    - CURRENT RATING: 1.0A
    - VOLTAGE RATING: 50V
    - CONTACT RESISTANCE: 100 MILL OHM MAX
    - WITHSTANDING VOLTAGE: AC250V R.M.S
    - INSULATION RESISTANCE: 1000MEG.OHM MIN AT DC 250V
    - DURABILITY: 1000 CYCLES
    - OPERATION TEMPERATURE: -25°C~+85°C



PACKAGE:  
Q'TY: 3500PCS/REEL



SMT SOLDER AREA  
OPEN WIRE RESTRICTED AREA  
OPEN WIRE & COPPER RESTRICTED AREA  
1. TOUCH AREA OF CONTACT TIPS, NO ELECTRICAL FUNCTION  
2. NO FIRST PGB-LAYER CIRCUITS IN THE AREA  
RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

Pin No.	NAME	TYPE	DESCRIPTION
1	DAT 2	I/O/PP	Date Line(bit2)
2	CD/DAT 3	I/O/PP	Card Detecty/Date Line(bit3)
3	CMD	PP	Command Response
4	VDD	S	Supply Voltage
5	CLK	I	Clcok
6	VSS	S	Supply Voltage Ground
7	DATO	I/O/PP	Date Line(bit0)
8	DATI	I/O/PP	Date Line(bit1)

MEASURE POINT:	DESCRIPTION
QUADRANT POINT	(QP)
TANGENCY POINT	(TP)
INTERSECTION POINT	(IP)

DESIGN	DATE	TITLE:
LUU	2019.03.20	1.35H 分体式 三端二卡座(卡半密)

CHECKED	DATE	REV	SCALE	UNIT:
		03	1:1	mm

DESIGN	DATE	REV	SCALE	UNIT:
LUU	2019.03.20	03	1:1	mm

APPROVED	DATE	REV	SCALE	UNIT:
		03	1:1	mm

PART NO:	REV	SIZE	SHEET
TA0801110033-147	03	A4	5/5

DRAWING NO:	REV	SIZE	SHEET
	03	A4	5/5



Dongguan D-CHAIN Precision Components CO, Ltd