



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	14MAY2019	H.X	I.Y




1 MATERIAL:
TYPE: COPPER ALLOY

2 FINISH:
UNDERPLATE TYPE: NICKEL
TOP PLATE TYPE: TIN

3. PARTS MUST BE FREE OF BURRS, CRACKS, OR OTHER
VISUAL IMPERFECTIONS THAT MAY AFFECT FIT FORM OR FUNCTION

© 2019 TE Connectivity. All Rights Reserved.

5.41	6.10	7.70	2350478-3
4.76	5.41	7.00	2350478-2
4.11	4.76	6.40	2350478-1
MIN	MAX	E	PART NO
WIRE O.D.			

DIMENSIONS:		DWN H.XIA	14MAY2019	MATERIAL		1		FINISH		2	
mm		CHK E.JIANG	15MAY2019	TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD I.YIN	15MAY2019								
0 PLC ±-		PRODUCT SPEC		NAME OUTER FERRULE, HVA280							
1 PLC ±0.2		108-2394									
2 PLC ±0.10		APPLICATION SPEC		SIZE A 4							
3 PLC ±0.013		114-13259									
4 PLC ±0.0001		WEIGHT		CAGE CODE		DRAWING NO		RESTRICTED TO			
ANGLES ±-		-		00779		C-2350478		-			
		CUSTOMER DRAWING				SCALE		SHEET		REV	
				4:1		1 OF 1		A			