



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

APPLICATION AS SHOWN



SCALE 1:1



NOTES:

8 .48POS.TAB AND PLUG HSG ASSY MATES WITH BULKHEAD BRACKET.


48POS. HSG ASSY P/N: MALE SIDE:2366066-*,FEMALE SIDE:2366036-*,

BULKHEAD BRACKET P/N: 2050752-1 OR FOLLOW DIMENSIONS ON INTERFACE.

IF THERE ARE ANY OTHER APPLICATIONS FOR THIS BRACKET, PLEASE CONFIRM WITH TE PRODUCT ENGINEER FIRST.



BULKHEAD BRACKET INTERFACE



SECTION X-X

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TANG 03JAN2020	 TE Connectivity			
DIMENSIONS: mm		CHK E. JIANG 03JAN2020				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. YIN 03JAN2020	NAME 48POS, MCON 1.2 LL, TAB HSG ASSY UNSEALED, CONNECTOR			
0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±0.100 4 PLC ±0.0500 ANGLES ±5°		PRODUCT SPEC 108-32618 APPLICATION SPEC 114-32365	SIZE A2			
MATERIAL -		WEIGHT -	CAGE CODE 00779			
FINISH -		RESTRICTED CUSTOMER	DRAWING NO C-2366066			
		SCALE 2:1	SHEET 2 OF 2			
			REV B			