

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese

December 2002

Revised August 2005

FSA3357 Low Voltage SP3T Analog Switch (3:1 Multiplexer/Demultiplexer)

General Description

The FSA3357 is a high performance, single-pole/triple-throw (SP3T) Analog Switch or 3:1 Multiplexer/Demultiplexer. The device is fabricated with advanced sub-micron CMOS technology to achieve high speed enable and disable times and low On Resistance. The break before make select circuitry prevents disruption of signals on the B₀, B₁, or B₂ Ports due to the switches temporarily being enabled during select pin switching. The device is specified to operate over the 1.65 to 5.5V V_{CC} operating range. The control input tolerates voltages up to 5.5V independent of the V_{CC} operating range.

Features

- Useful in both analog and digital applications
- Space saving US8 8-lead surface mount package
- Low On Resistance; < 9 Ω on typ @ 3.3V V_{CC}
- Broad V_{CC} operating range; 1.65V to 5.5V
- Rail-to-Rail signal handling
- Power down high impedance control input
- Overvoltage tolerance of control input to 7.0V
- Break before make enable circuitry
- 250 MHz 3dB bandwidth
- Space saving Pb-Free MicroPak[™] packaging

Applications

- Cell Phone
- PDA
- Video

Ordering Code:

Product Order Number	Package Number	Code	Package Description	Supplied As
FSA3357K8X		Top Mark A357	8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide	3k Units on Tape and Reel
FSA3357L8X	MAC08A	FE	Pb-Free 8-Lead MicroPak, 1.6 mm Wide	5k Units on Tape and Reel

Pb-Free package per JEDEC J-STD-020B.

FAIRCHILD

SEMICONDUCTOR

Analog Symbols



Pin Assignments for MicroPak



(Top Through View)

Connection Diagram



Pin Descriptions

Pin Names	Description
A ₁ , B ₀ , B ₁ , B ₂	Data Ports
S ₁ , S ₂	Control Input
	•

Function Table

S ₁	S ₂	Function
0	0	No Connection
1	0	B ₀ Connected to A
0	1	B ₁ Connected to A
1	1	B ₂ Connected to A

Absolute Maximum Ratings(Note 1)

Supply Voltage (V _{CC})	-0.5V to +7.0V
DC Switch Voltage (V_S) (Note 2)	-0.5V to V _{CC}
	+0.5V
DC Input Voltage (VIN) (Note 2)	-0.5V to +7.0V
DC Input Diode Current (I _{IK})	
@ $(I_{IK}) V_{IN} < 0V$	–50 mA
DC Output Current (I _{OUT})	128 mA
DC V _{CC} or Ground Current (I_{CC}/I_{GND})	±100 mA
Storage Temperature Range (T _{STG})	$-65^{\circ}C$ to $+150^{\circ}C$
Junction Temperature under Bias (T_J)	150°C
Junction Lead Temperature (T_L)	
(Soldering, 10 seconds)	260°C
Power Dissipation (P _D) @ +85°C	180 mW

Recommended Operating Conditions

(Note 3)

1.65V to 5.5V
0V to V_{CC}
0V to V_{CC}
0V to V_{CC}
$-40^{\circ}C$ to $+85^{\circ}C$
0 ns/V to 10 ns/V
0 ns/V to 5 ns/V
250°C/W
224°C/W

Note 1: Absolute maximum ratings are DC values beyond which the device may be damaged or have its useful life impaired. The datasheet specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation outside datasheet specifications.

Note 2: The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

Note 3: Control inputs must be held HIGH or LOW, they must not float.

DC Electrical	Characteristics
----------------------	-----------------

Symbol	Devementer	Vcc		$T_A = +25^{\circ}C$		$T_A = -40^{\circ}C \text{ to } +85^{\circ}C$		Units	Conditions
Symbol	Parameter	(V)	Min	Тур	Max	Min	Max	Units	Conditions
V _{IH}	HIGH Level	1.65 – 1.95	0.75 V _{CC}			0.75 V _{CC}			
	Input Voltage	2.3 - 5.5	0.7 V _{CC}			0.7 V _{CC}		V	
V _{IL}	LOW Level	1.65 – 1.95			0.25 V _{CC}		0.25 V _{CC}	V	
	Input Voltage	2.3 – 5.5			0.3 V _{CC}		0.3 V _{CC}	v	
I _{IN}	Input Leakage Current	0 - 5.5			±0.1		±1.0	μA	$0 \leq V_{IN} \leq 5.5 V$
I _{OFF}	OFF State Leakage Current	1.65 - 5.5			±0.1		±1.0	μA	$0 \leq A, \ B_n \leq V_{CC}$
R _{ON}	Switch On Resistance	4.5		5.0	7.0		7.0		$V_{IN} = 0V, I_{O} = 30 \text{ mA}$
	(Note 4)			6.0	12.0		12.0		$V_{IN} = 2.4 V, I_{O} = -30 \text{ mA}$
				7.0	15.0		15.0		$V_{IN} = 4.5 V, I_O = -30 \text{ mA}$
		3.0		6.5	9.0		9.0		$V_{IN} = 0V, I_{O} = 24 \text{ mA}$
				9.0	20.0		20.0	Ω	$V_{IN} = 3V, I_{O} = -24 \text{ mA}$
		2.3		8.0	12.0		12.0		$V_{IN} = 0V, I_{O} = 8 \text{ mA}$
				11.0	30.0		30.0		$V_{IN} = 2.3V$, $I_O = -8$ mA
		1.65		10.0	20.0		20.0		$V_{IN} = 0V, I_{O} = 4 \text{ mA}$
				17.0	50.0		50.0		$V_{IN} = 1.65V, I_{O} = -4 \text{ mA}$
I _{CC}	Quiescent Supply Current	5.5			1.0		10.0	μA	$V_{IN} = V_{CC}$ or GND
	All Channels ON or OFF	5.5			1.0		10.0	μΑ	I _{OUT} = 0
ASR	Analog Signal Range	V _{CC}	0.0		V _{CC}	0.0	V _{CC}	V	
ΔR_{ON}	On Resistance Match	4.5		0.15					I _A = -30 mA, V _{Bn} = 3.15
	Between Channels	3.0		0.22				Ω	I _A = -24 mA, V _{Bn} = 2.1
	(Note 4)(Note 5)(Note 6)	2.3		0.31				12	I _A = -8 mA, V _{Bn} = 1.6
		1.65		0.62					$I_A = -4 \text{ mA}, V_{Bn} = 1.15$
R _{flat}	On Resistance Flatness	5.0		6.0					$I_A = -30 \text{ mA}, \ 0 \leq V_{Bn} \leq V_{CC}$
	(Note 4)(Note 5)(Note 7)	3.3		12.0				Ω	$I_A = -24 \text{ mA}, \ 0 \leq V_{Bn} \leq V_{CC}$
		2.5		40.0				22	$I_A = -8 \ mA, \ 0 \leq V_{Bn} \leq V_{CC}$
		1.8		140.0					$I_A = -4 \text{ mA}, 0 \le V_{Bn} \le V_{CC}$

DC Electrical Characteristics (Continued)

Note 4: Measured by the voltage drop between A and B_n pins at the indicated current through the switch. On Resistance is determined by the lower of the voltages on the two (A or B_n Ports).

Note 5: Parameter is characterized but not tested in production.

Note 6: $\Delta R_{ON} = R_{ON} \text{ max} - R_{ON} \text{ min measured at identical V}_{CC}$, temperature and voltage levels.

Note 7: Flatness is defined as the difference between the maximum and minimum value of On Resistance over the specified range of conditions.

AC Electrical Characteristics

0	Description	V _{cc}		$T_A = +25^{\circ}C$		T _A = -40°	C to +85°C	l la la	Conditions	Figure
Symbol	Parameter	(V)	Min	Тур	Max	Min	Max	Units	Conditions	Number
t _{PHL}	Propagation Delay	1.65 - 1.95		2.0						
t _{PLH}	Bus to Bus	2.3 - 2.7		1.1						Figures
	(Note 8)	3.0 - 3.6		0.7				ns	V _I = OPEN	1, 2
		4.5 - 5.5		0.4						
t _{PZL}	Output Enable Time	1.65 - 1.95	5.0		32.0	5.0	34.0			
t _{PZH}	Turn on Time	2.3 - 2.7	3.0		15.0	3.0	16.5		$V_I = 2 \times V_{CC}$ for t_{PZL}	Figures
	(A to B _n)	3.0 - 3.6	2.0		9.5	2.0	11.0	ns	$V_I = 0V$ for t_{PZH}	1, 2
		4.5 - 5.5	1.5		6.5	1.5	7.0			
t _{PLZ}	Output Disable Time	1.65 - 1.95	3.0		14.0	3.0	14.5			Figures 1, 2
t _{PHZ}	Turn Off Time	2.3 - 2.7	2.0		7.2	2.0	7.8		$V_I = 2 \times V_{CC}$ for t_{PLZ}	
	(A Port to B _n Port)	3.0 - 3.6	1.5		5.1	1.5	5.5	ns	$V_I = 0V$ for t_{PHZ}	
		4.5 - 5.5	0.8		3.7	0.8	4.0			
t _{B-M}	Break Before Make Time	1.65 - 1.95	0.5			0.5				Figure 3
	(Note 9)	2.3 - 2.7	0.5			0.5				
		3.0 - 3.6	0.5			0.5		ns		
		4.5 - 5.5	0.5			0.5				
Q	Charge Injection (Note 9)	5.0		3.0					C _L = 0.1 nF, V _{GEN} = 0V	
		3.3		2.0				pC	$R_{GEN} = 0\Omega$	Figure 4
OIRR	Off Isolation (Note 10)	1.65 - 5.5		-58.0				9	$R_L = 50\Omega$	Figure 5
								dB	f = 10MHz	Figure 5
Xtalk	Crosstalk	1.65 - 5.5		-60.0				-iD	$R_L = 50\Omega$	Figure 0
								dB f = 10MHz		Figure 6
BW	-3dB Bandwidth	1.65 - 5.5		250.0				MHz	$R_L = 50\Omega$	Figure 9
THD	Total Harmonic Distortion	İ							R _L = 600Ω	1
	(Note 9)	5.0		.01				%	0.5 V _{P-P}	
									f = 600 Hz to 20 KHz	

Note 8: This parameter is guaranteed by design but not tested. The bus switch contributes no propagation delay other than the RC delay of the On Resistance of the switch and the 50 pF load capacitance, when driven by an ideal voltage source (zero output impedance).

Note 9: Guaranteed by Design.

Note 10: Off Isolation = 20 $\log_{10} [V_A / V_{Bn}]$

Capacitance (Note 11)

Symbol	Parameter	Тур	Max	Units	Conditions	Figure Number
C _{IN}	Control Pin Input Capacitance	2.0		pF	$V_{CC} = 0V$	
C _{IO-B}	B Port Off Capacitance	3.6		pF	$V_{CC} = 5.0V$	Figure 7
C _{IOA-ON}	A Port Capacitance When Switch Is Enabled	14.5		pF	$V_{CC} = 5.0V$	Figure 8

Note 11: $T_A = +25$ °C, f = 1 MHz, Capacitance is characterized but not tested in production.

FSA3357

AC Loading and Waveforms **\$** 500Ω FROM • OUTPUT **ξ**^{500Ω} UNDER 50pl TEST Note: Input driven by 50Ω source terminated in 50Ω Note: \mathbf{C}_{L} includes load and stray capacitance Note: Input PRR = 1.0 MHz; t_W = 500 ns FIGURE 1. AC Test Circuit t_f = 2.5 ns - t, = 2.5 ns $v_{\rm CC}$ 90% t_r= 2.5 ns→ • t_f = 2.5 ns 90 CONTROL INPUT V_{CC} 50% 50% 90% 909 SWITCH INPUT 10% 10% 50% GND 50% t_{PZL} 10% 10% V_{TRI} GND t_{PLH} t_{PHL} OUTPUT 50% V_{OL}+0.3V V_{он} VOL OUTPUT 50% 50% t_{PZH} -- t_{PHZ} √он V_{OL} V_{OH}-0.3V OUTPUT 50% V_{tri} FIGURE 2. AC Waveforms VIN Vout Logic Input 35 pF \$500Ω VOUT Logic Input 0.9 x V_{OUT} tD FIGURE 3. Break Before Make Interval Timing





Tape and Reel Specification



Package	Таре	Number	Cavity	Cover Tape
Designator	Section	Cavities	Status	Status
	Leader (Start End)	125 (typ)	Empty	Sealed
K8X	Carrier	250	Filled	Sealed
	Trailer (Hub End)	75 (typ)	Empty	Sealed





REEL DIMENSIONS inches (millimeters)



→ →	₩ ₃ ₩ ₂

W₁

Tape Size	Α	В	С	D	Ν	W1	W2	W3
8 mm	7.0	0.059	0.512	0.795	2.165	0.331 + 0.059/- 0.000	0.567	W1 + 0.078/-0.039
	(177.8)	(1.50)	(13.00)	(20.20)	(55.00)	(8.40 + 1.50/-0.00)	(14.40)	(W1 + 2.00/-1.00)

FSA3357



Physical Dimensions inches (millimeters) unless otherwise noted





LAND PATTERN RECOMMENDATION



A. CONFORMS TO JEDEC REGISTRATION MO-187 B. DIMENSIONS ARE IN MILLIMETERS.

AND TIE BAR EXTRUSIONS.

C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH,

D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.







MAB08AREVC

NOTES:

8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide Package Number MAB08A

FSA3357



DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use

provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product develop- ment. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been dis- continued by Fairchild Semiconductor. The datasheet is printed for ref- erence information only.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC