

N-Channel Enhancement Mode Field Effect Transistor


2N7000, 2N7002, **NDS7002A**


Description

These N-channel enhancement mode field effect transistors are produced using onsemi's proprietary, high cell density, DMOS technology. These products have been designed to minimize on-state resistance while providing rugged, reliable, and fast switching performance. They can be used in most applications requiring up to 400 mAdc and can deliver pulsed currents up to 2 A. These products are particularly suited for low-voltage, low-current applications, such as small servo motor control, power MOSFET gate drivers, and other switching applications.

Features

- High Density Cell Design for Low R_{DS(on)}
- Voltage Controlled Small Signal Switch
- Rugged and Reliable
- High Saturation Current Capability
- This Device is Pb-Free and Halogen Free





MARKING DIAGRAM



\$Y = Logo

&Z = Assembly Plant Code

= Date Code

2N7000 = Specific Device Code



1 - Gate

2 - Source

3 - Drain

SOT-23 **CASE 318-08**

MARKING DIAGRAM



&E = Designates Space

&Y = Binary Calendar Year Coding Scheme

7x2 = Specific Device Code

x= 0, 1

&G = Date Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 7 of this data sheet.

ABSOLUTE MAXIMUM RATINGS Values are at T_C = 25°C unless otherwise noted.

		Value			
Symbol	Parameter	2N7000	2N7002	NDS7002A	Unit
V _{DSS}	Drain-to-Source Voltage		60		
V _{DGR}	Drain-Gate Voltage (R _{GS} ≤ 1 MW)		60		V
V _{GSS}	Gate-Source Voltage - Continuous	±20			V
	Gate-Source Voltage - Non Repetitive (tp < 50 ms)	±40			
I _D	Maximum Drain Current - Continuous	200	115	280	mA
	Maximum Drain Current - Pulsed	500	800	1500	
P _D	Maximum Power Dissipation Derated above 25°C	400	200	300	mW
		3.2	1.6	2.4	mW/°C
T _J , T _{STG}	Operating and Storage Temperature Range	-55 to 150 -65 to 150		°C	
TL	Maximum Lead Temperature for Soldering Purposes, 1/16-inch from Case for 10 s		300		°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS Values are at $T_C = 25$ °C unless otherwise noted.

		Value			
Symbol	Parameter	2N7000	2N7002	NDS7002A	Unit
$R_{ heta JA}$	Thermal Resistance, Junction to Ambient	312.5	625	417	°C/W

ELECTRICAL CHARACTERISTICS

Values are at T_C = 25°C unless otherwise noted.

Symbol	Parameter	Conditions	Туре	Min	Тур	Max	Unit
FF CHARA	CTERISTICS						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0 V, I _D = 10 μA	All	60	-	-	٧
I _{DSS}	Zero Gate Voltage Drain	V _{DS} = 48 V, V _{GS} = 0 V	2N7000	-	-	1	μΑ
	103 1, 103 - 1	, ac ,		-	-	1	mA
		2N7002	-	-	1	μΑ	
		$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V},$ $T_C = 125^{\circ}\text{C}$	NDS7002A	-	-	0.5	mA
I _{GSSF}	Gate – Body Leakage,	V _{GS} = 15 V, V _{DS} = 0 V	2N7000	-	-	10	nA
	Forward	V _{GS} = 20 V, V _{DS} = 0 V	2N7002 NDS7002A	-	-	100	
I _{GSSR}	Gate – Body Leakage,	$V_{GS} = -15 \text{ V}, V_{DS} = 0 \text{ V}$	2N7000	-	-	-10	nA
	Reverse	$V_{GS} = -20 \text{ V}, V_{DS} = 0 \text{ V}$	2N7002 NDS7002A	-	-	-100	1
N CHARAC	CTERISTICS		-				-
V _{GS(th)}	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 1 \text{ mA}$	2N7000	0.8	2.1	3	V
		$V_{DS} = V_{GS}$, $I_D = 250 \mu A$	2N7002 NDS7002A	1	2.1	2.5	

ELECTRICAL CHARACTERISTICS (continued)

Values are at $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Conditions	Туре	Min	Тур	Max	Unit
ON CHARAC	CTERISTICS						
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} = 10 V, I _D = 500 mA	2N7000	-	1.2	5	Ω
	OII-nesistance	$V_{GS} = 10 \text{ V}, I_D = 500 \text{ mA}, T_C = 125^{\circ}\text{C}$		-	1.9	9	
		$V_{GS} = 4.5 \text{ V}, I_D = 75 \text{ mA}$	1	_	1.8	5.3	
		V _{GS} = 10 V, I _D = 500 mA	2N7002	_	1.2	7.5	
		$V_{GS} = 10 \text{ V}, I_D = 500 \text{ mA}, T_C = 100^{\circ}\text{C}$		-	1.7	13.5	
		$V_{GS} = 5 \text{ V}, I_D = 50 \text{ mA}$		-	1.7	7.5	
		$V_{GS} = 5 \text{ V}, I_D = 50 \text{ mA}, $ $T_C = 100^{\circ}\text{C}$		-	2.4	13.5	
		V _{GS} = 10 V, I _D = 500 mA	NDS7002A	_	1.2	2	
		$V_{GS} = 10 \text{ V}, I_D = 500 \text{ mA}, T_C = 125^{\circ}\text{C}$		-	2	3.5	
		$V_{GS} = 5 \text{ V}, I_D = 50 \text{ mA}$	1 I	_	1.7	3	
		$V_{GS} = 5 \text{ V}, I_D = 50 \text{ mA},$ $T_C = 125^{\circ}\text{C}$		-	2.8	5	
V _{DS(on)}	Drain-Source On-Voltage	V _{GS} = 10 V, I _D = 500 mA	2N7000	-	0.6	2.5	V
		$V_{GS} = 4.5 \text{ V}, I_D = 75 \text{ mA}$		_	0.14	0.4	
		V _{GS} = 10 V, I _D = 500 mA	2N7002	-	0.6	3.75	
		$V_{GS} = 5.0 \text{ V}, I_D = 50 \text{ mA}$	1	_	0.09	1.5	
		$V_{GS} = 10 \text{ V}, I_D = 500 \text{ mA}$	NDS7002A	-	0.6	1	
		$V_{GS} = 5.0 \text{ V}, I_D = 50 \text{ mA}$		-	0.09	0.15	
$I_{D(on)}$	On-State Drain Current	$V_{GS} = 4.5 \text{ V}, V_{DS} = 10 \text{ V}$	2N7000	75	600	-	mA
		V_{GS} = 10 V, $V_{DS} \ge 2 V_{DS(on)}$	2N7002	500	2700	_	
		V_{GS} = 10 V, $V_{DS} \ge 2 V_{DS(on)}$	NDS7002A	500	2700	_	
g _F s	Forward Transconductance	$V_{DS} = 10 \text{ V}, I_D = 200 \text{ mA}$	2N7000	100	320	_	mS
		$V_{DS} \ge 2 V_{DS(on)}, I_D = 200 \text{ mA}$	2N7002	80	320	-	
		$V_{DS} \ge 2 V_{DS(on)}, I_D = 200 \text{ mA}$	NDS7002A	80	320	-	
YNAMIC CI	HARACTERISTICS					_	
C _{iss}	Input Capacitance	$V_{DS} = 25 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1.0 MHz	All	_	20	50	pF
C _{oss}	Output Capacitance		All	_	11	25	
C _{rss}	Reverse Transfer Capacitance		All	-	4	5	
t _{on}	Turn-On Time	$\begin{aligned} &V_{DD}=15\text{ V, R}_{L}=25\ \Omega,\\ &I_{D}=500\text{ mA, V}_{GS}=10\text{ V,}\\ &R_{GEN}=25\ \Omega \end{aligned}$	2N7000	-	_	10	ns
		$\begin{split} &V_{DD}=30 \text{ V, R}_{L}=150 \ \Omega, \\ &I_{D}=200 \text{ mA, V}_{GS}=10 \text{ V,} \\ &R_{GEN}=25 \ \Omega \end{split}$	2N7002 NDS7002A	-	-	20	
t _{off}	Turn-Off Time	V_{DD} = 15 V, R_{L} = 25 Ω , I_{D} = 500 mA, V_{GS} = 10 V, R_{GEN} = 25 Ω	2N7000	-	_	10	ns
		$\begin{aligned} &V_{DD}=30 \text{ V, R}_{L}=150 \ \Omega, \\ &I_{D}=200 \text{ mA, V}_{GS}=10 \text{ V,} \\ &R_{GEN}=25 \ \Omega \end{aligned}$	2N7002 NDS7002A	-	_	20	

ELECTRICAL CHARACTERISTICS (continued)

Values are at $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Conditions	Туре	Min	Тур	Max	Unit
DRAIN-SOU	RCE DIODE CHARACTERISTICS						
I _S	Maximum Continuous Drain-Sou	2N7002	-	_	115	mA	
			NDS7002A	-	-	280	
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current		2N7002	-	-	0.8	Α
			NDS7002A	-	-	1.5	
V _{SD}	$ \begin{array}{ll} \mbox{Drain-Source Diode} & \mbox{V}_{\mbox{GS}} = 0 \mbox{ V, I}_{\mbox{S}} = 115 \mbox{ mA} \\ \mbox{Forward Voltage} & (\mbox{Note 1}) \end{array} $		2N7002	-	0.88	1.5	V
		V _{GS} = 0 V, I _S = 400 mA (Note 1)	NDS7002A	ı	0.88	1.2	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. On-Region Characteristics

2

1.75

1.5

1.25

1

0.75

0.5

-25

 $V_{GS} = 10^{'}V$

I_D = 500 mA

Drain-Source On-Resistance

R_{DS(on)}, Normalized

 V_{GS} 2.5 T_J = 125°0 25°C -55°C

Gate Voltage and Drain Current

Figure 3. On-Resistance Variation with **Temperature**

T_J, Junction Temperature (°C)

50

75

100

125




Figure 4. On-Resistance Variation with **Drain Current and Temperature**

150

R_{DS(on)}, Normalized

^{1.} Pulse test: Pulse Width ≤ 300 μs, Duty Cycel ≤ 2 %

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 5. Transfer Characteristics

Figure 6. Gate Threshold Variation with Temperature




Figure 7. Breakdown Voltage Variation with Temperature

Figure 8. Body Diode Forward Voltage Variation with




Figure 9. Capacitance Characteristics

Figure 10. Gate Charge Characteristics

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 11. Switching Test Circuit

Figure 12. Switching Waveforms




Figure 13. 2N7000 Maximum Safe Operating Area

Figure 14. 2N7002 Maximum Safe Operating Area




Figure 15. NDS7000A Maximum Safe Operating Area

TYPICAL PERFORMANCE CHARACTERISTICS (Continued)




Figure 16. TO-92, 2N7000 Transient Thermal Response Curve




Figure 17. SOT-23, 2N7002 / NDS7002A Transient Thermal Response Curve


ORDERING INFORMATION


Part Number	Marking	Package	Packing Method [†]	Min Order Qty / Immediate Pack Qty
2N7000	2N7000	TO-92 3L	Bulk	10000 / 1000
2N7000-D74Z		(Pb-Free)	Ammo	2000 / 2000
2N7000-D75Z			Tape and Reel	2000 / 2000
2N7000-D26Z				2000 / 2000
2N7002	702	SOT-23 3L	Tape and Reel	3000 / 3000
NDS7002A	712	(Pb-Free)		3000 / 3000

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

TO-92 3 4.825x4.76 CASE 135AN ISSUE O


DATE 31 JUL 2016





NOTES: UNLESS OTHERWISE SPECIFIED

- DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS. A)
- ALL DIMENSIONS ARE IN MILLIMETERS.
 DRAWING CONFORMS TO ASME Y14.5M—2009.




DOCUMENT NUMBER:	98AON13880G	Electronic versions are uncontrolled except when accessed directly from the Document Repos Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TO-92 3 4.825X4.76		PAGE 1 OF 1	


ON Semiconductor and at a trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

TO-92 3 4.83x4.76 LEADFORMED

CASE 135AR ISSUE O


DATE 30 SEP 2016





NOTES: UNLESS OTHERWISE SPECIFIED

- A) DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DRAWING CONFORMS TO ASME Y14.5M-1994



DOCUMENT NUMBER:	Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED	, ,	
DESCRIPTION:	TO-92 3 4.83X4.76 LEADF	ORMED	PAGE 1 OF 1

ON Semiconductor and at a trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



SOT-23 (TO-236) CASE 318-08 **ISSUE AS**

DATE 30 JAN 2018

0.017

0.021

0.094


0.022


0.027


0.104

10°


SCALE 4:1 D Ε – 3X h **TOP VIEW**







RECOMMENDED SOLDERING FOOTPRINT



DIMENSIONS: MILLIMETERS

PIN 1. RETURN

3. INPUT

3. ANODE

STYLE 28: PIN 1. ANODE 2. ANODE

2. OUTPUT

NOTES:

0.43

0.54

2.40

0.30

0.35

2.10

0°

ΗE

- NOTES:
 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: MILLIMETERS.
 3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH.
 MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL
- 4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

	MILLIMETERS				INCHES	
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.039	0.044
A1	0.01	0.06	0.10	0.000	0.002	0.004
b	0.37	0.44	0.50	0.015	0.017	0.020
С	0.08	0.14	0.20	0.003	0.006	0.008
D	2.80	2.90	3.04	0.110	0.114	0.120
Е	1.20	1.30	1.40	0.047	0.051	0.055
٩	1 78	1 90	2 04	0.070	0.075	0.080

0.55

0.69


2.64

10° 0° **GENERIC MARKING DIAGRAM***

0.012

0.014

0.083



XXX = Specific Device Code

= Date Code

PIN 1. ANODE 2. CATHODE

3. GATE

= Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present.

STYLE 1 THRU 5: CANCELLED	STYLE 6: PIN 1. BASE 2. EMITTER 3. COLLECTOR	STYLE 7: PIN 1. EMITTER 2. BASE 3. COLLECTOR	STYLE 8: PIN 1. ANODE 2. NO CONNECTION 3. CATHODE	N	
STYLE 9:	STYLE 10:	STYLE 11:	STYLE 12: PIN 1. CATHODE 2. CATHODE 3. ANODE	STYLE 13:	STYLE 14:
PIN 1. ANODE	PIN 1. DRAIN	PIN 1. ANODE		PIN 1. SOURCE	PIN 1. CATHODE
2. ANODE	2. SOURCE	2. CATHODE		2. DRAIN	2. GATE
3. CATHODE	3. GATE	3. CATHODE-ANODE		3. GATE	3. ANODE
STYLE 15:	STYLE 16:	STYLE 17:	STYLE 18:	STYLE 19:	STYLE 20:
PIN 1. GATE	PIN 1. ANODE	PIN 1. NO CONNECTION	PIN 1. NO CONNECTION	N PIN 1. CATHODE	PIN 1. CATHODE
2. CATHODE	2. CATHODE	2. ANODE	2. CATHODE	2. ANODE	2. ANODE
3. ANODE	3. CATHODE	3. CATHODE	3. ANODE	3. CATHODE-ANODI	3. GATE
STYLE 21:	STYLE 22:	STYLE 23:	STYLE 24:	STYLE 25:	STYLE 26:

PIN 1. ANODE

ANODE

CATHODE

DOCUMENT NUMBER:	98ASB42226B	Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED (
DESCRIPTION:	SOT-23 (TO-236)		PAGE 1 OF 1

PIN 1. GATE 2. DRAIN

3. SOURCE

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

PIN 1. GATE

2. SOURCE

3. CATHODE

DRAIN

STYLE 27: PIN 1. CATHODE 2. CATHODE

PIN 1. CATHODE 2. ANODE

3. NO CONNECTION

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative