





- Right angle design Right angle design allows ease of harness routing in tight places. Available in one circuit to twelve circuits.
- Easy insertion, positive locking

The combination of terminal and housing allows easy mating to a male tab. Un-mating is equally easy. Simply hold the housing and pull. The contact locking spring is depressed by the taper inside the housing. The locking mechanism prevents accidental disengagement of the contact from the mating tab.

• Ultra low insertion force

The contact is designed as a low insertion force with a large contact area to give stable performance, even when high current is applied.

- Contact back out preventive design Innovative contact and housing design eliminates contact back out caused due to damaged locking lances during termination and harness assembly.
- Keying options

Selective removal of built-in keys and blocking housing cavities, allows for an infinite number of keying possibilities. The cover can be molded in various colors.

#### Contact



## Specifications -

- Current rating: 15A AC, DC max.(AWG #14) (20A Contact under develoment)
- Voltage rating: 250V AC, DC max.
- Temperature range: -40°C to +105°C (including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 3m  $\Omega$  max. After environmental testing/ 6m  $\Omega$  max.
- Insulation resistance: 1,000M  $\Omega$  min.
- Withstanding voltage: 2,000V AC/minute
- Applicable wire: AWG #18 to #14
- \* Refer to "General Instruction and Notice when using
- Terminals and Connectors" at the end of this catalog.
- \* Contact JST for details.

## Standards -

Recognized E60389

Model No.		Q'ty /			
	mm <sup>2</sup>	AWG# UL1015	Insulation O.D. (mm)	reel	
RASRSF-61-250A	0.00.000	18~14, 18+18~20+20	3.0~3.9	5,000	
RASRSF-61T-250A	0.82~2.08	18+18~20+20			
Material and Finish					
RASRSF-61T-250A: Brass, tin-plated					
	RASRSF-61	-250A: Brass			

Contact	Applicator			
Contact	Crimp applicator	Dies set		
RASRSF-61()-250A	CMKS-L	CDSRASRSF61250		

# **RARSF CONNECTOR**

### Housing



## Different keying and blocked configurations available upon request

Circuits I	Model No	Dimensions (mm)		Q'ty	Appliable Contact
	NOUEI NO	A	В	/box	Applicable Contact
1	RARSFP-1V-00	7.9	5.0	5,000	
2	RARSFP-2V-00	12.9	10.0	3,000	
3	RARSFP-3V-00	17.9	15.0	2,000	
4	RARSFP-4V-00	22.9	20.0	2,000	
5	RARSFP-5V-00	27.9	25.0	1,500	
6	RARSFP-6V-00	32.9	30.0	1,000	RASRSF-61-250A
7	RARSFP-7V-00	37.9	35.0	1,000	RASRSF-61T-250A
8	RARSFP-8V-00	42.9	40.0	1,000	
9	RARSFP-9V-00	47.9	45.0	800	
10	RARSFP-10V-00	52.9	50.0	500	
11	RARSFP-11V-00	57.9	55.0	500	
12	RARSFP-12V-00	62.9	60.0	500	
		Mate			

Glass-filled PBT, UL94V-0, natural (white)

### Applicable tab



Note: Make Sure there are no unneeded ribs or other protuberances on the tab surfaces.

## Cover



Circuits	Model No	Dimensions (mm)	Q'ty / box	Applicable Contact
		A		
1	RARSFC-1V	7.9	10,000	
2	RARSFC-2V	12.9	6,000	
3	RARSFC-3V	17.9	5,000	
4	RARSFC-4V	22.9	4,000	
5	RARSFC-5V	27.9	3,000	
6	RARSFC-6V	32.9	2,000	RASRSF-61-250A
7	RARSFC-7V	37.9	2,000	RASRSF-61T-250A
8	RARSFC-8V	42.9	2,000	
9	RARSFC-9V	47.9	1,600	
10	RARSFC-10V	52.9	1,000	
11	RARSFC-11V	57.9	1,000	
12	RARSFC-12V	62.9	1,000	
		Material		_

Glass-filled PBT, UL94V-0, natural (white)