

Class 11, manual switch, 25 Amps, NEMA 1,



Figure similar

product brand name
design of the product

Class 11
Manual Switch

General technical data

ambient temperature [°F]	
• during storage	122 ... 176 °F
• during operation	68 ... 140 °F
ambient temperature	
• during storage	50 ... 80 °C
• during operation	20 ... 60 °C
number of poles for main current circuit	3

Horsepower ratings

yielded mechanical performance [hp] for 3-phase AC motor	
• at 115 V rated value	2 hp
• at 200/208 V rated value	7.5 hp
• at 220/230 V rated value	7.5 hp
• at 460/480 V rated value	15 hp
• at 575/600 V rated value	20 hp

Contactor

mechanical service life (switching cycles) of the main contacts typical	100000
---	--------

Overload relay

adjustable current response value current of the current-dependent overload release	25 A
---	------

Mounting/wiring

fastening method	wall mounting
type of electrical connection for supply voltage line-side	Screw-type terminals

Short-circuit current rating

design of the short-circuit trip	magnetic
----------------------------------	----------

Certificates/ approvals

certificate of suitability	UL
----------------------------	----

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:115D3BF>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:115D3BF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:115D3BF&lang=en

Certificates/approvals

last modified:

5/31/2021 