



Figure similar

Class 11, manual switch, 1 Amps, NEMA 1,

product brand name	Class 11
design of the product	Manual Switch
General technical data	
ambient temperature [°F]	
• during storage	122 ... 176 °F
• during operation	68 ... 140 °F
ambient temperature	
• during storage	50 ... 80 °C
• during operation	20 ... 60 °C
number of poles for main current circuit	3
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 460/480 V rated value	0.5 hp
• at 575/600 V rated value	0.5 hp
Contactor	
mechanical service life (switching cycles) of the main contacts typical	100000
Overload relay	
adjustable current response value current of the current-dependent overload release	1 A
Mounting/wiring	
fastening method	wall mounting
type of electrical connection for supply voltage line-side	Screw-type terminals
Short-circuit current rating	
design of the short-circuit trip	magnetic
Certificates/ approvals	
certificate of suitability	UL
Further information	
Industrial Controls - Product Overview (Catalogs, Brochures,...)	
www.usa.siemens.com/iccatalog	
Industry Mall (Online ordering system)	
https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:111D3BG	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
https://support.industry.siemens.com/cs/US/en/ps/US2:111D3BG	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:111D3BG&lang=en	
Certificates/approvals	
https://support.industry.siemens.com/cs/US/en/ps/US2:111D3BG/certificate	

last modified:

5/31/2021 