

A

B

C

D

E

A

B

C

D

E

版次 (Vension)	变更内容 (Rev. Content)	变更者 (Change Person)

技术参数 (Technical Data)		
项 目 (Item)	UL	IEC
额定电气参数 (Rated Electrical Parameters)	300V/8A	250V/7A
压线范围 (Wire Range)	/	/
工频耐压 (Frequency Voltage)	AC 2000V	
冲击耐压 (Rated Surge Voltage)	4000V	
绝缘阻抗 (Insulation Resistance)	DC500V 500MΩ above	
接触电阻 (Contact Resistance)	≤8mΩ	
剥线长度 (Stripping Length)	/	
工作温度 (Temperature)	-40℃~+105℃	
材质和电镀 (Material and plating)		
绝缘材质 (Housing)	PA66 (UL94 V-0)	
触点材料 (Contact)	铜合金, 镀锡 (Copper alloy, Sn plated)	
/	/	

产品命名编码:

(Product Number Code):

GSP002RC-3.5-XXP-1Y-00A (H)

产品型号 (Series No.)

极数 (No. of poles)

客户需求

(Customer Request)

塑体颜色 (Housing Color)

1: 单倍间距
(Single Pitch)
2: 双倍间距
(Double Pitch)

1: 绿色 (Green) 7: 透明色
(Transparent)
2: 蓝色 (Blue)
3: 黑色 (Black) 8: 白色 (White)
4: 灰色 (Grey) 9: 黄色 (Yellow)
5: 橙色 (Orange) Y: 多种颜色
6: 红色 (Red) (Mixed Color)

P=3.50mm, N为孔位数 (N for hole digits), 有效位数为 (Significant Digits): 02P~24P

N	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P	13P
L	8.10	11.60	15.10	18.60	22.10	25.60	29.10	32.60	36.10	39.60	43.10	46.60
B	3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00
N	14P	15P	16P	17P	18P	19P	20P	21P	22P	23P	24P	
L	50.10	53.60	57.10	60.60	64.10	67.60	71.10	74.60	78.10	81.60	85.10	
B	45.50	49.00	52.50	56.00	59.50	62.50	66.50	70.00	73.50	77.00	80.50	



宁波高胜电子有限公司
NINGBO GOOSVN ELECTRONIC CO.,LTD

型号 (Type): GSP002RC-3.5-XXP-1Y-00A (H)

核准 (Approval):

图号 (Drawing NO.):

审核 (Audit):

单位 (Units): mm

页码 (Page): 1/1

设计 (Design):

比例 (Scale): FULL

版次 (Version): T0

公差范围 (Tolerance Range)

150~ ±1.50

60~150 ±1.00

30~60 ±0.60

6~30 ±0.40

0~6 ±0.25

角度 (Angle) X ±2°

XX ±1°

版次 (Version): T0