

Class 11, manual starter, 0.11-0.16 Amps, NEMA 1,



Figure similar

product brand name  
design of the product

Class 11  
Manual Starter

### General technical data

ambient temperature [°F]

- during storage 122 ... 176 °F
- during operation 68 ... 140 °F

ambient temperature

- during storage 50 ... 80 °C
- during operation 20 ... 60 °C

number of poles for main current circuit

3

### Contactor

mechanical service life (switching cycles) of the main contacts typical

100000

### Coil

type of voltage of the control supply voltage

n.a.

### Overload relay

adjustable current response value current of the current-dependent overload release

0.16 A

### Mounting/wiring

fastening method

wall mounting

### Short-circuit current rating

design of the short-circuit trip

magnetic

### Certificates/ approvals

certificate of suitability

UL

### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:11AD3BG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:11AD3BG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:11AD3BG&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:11AD3BG&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:11AD3BG/certificate>