

HER301G thru HER308G

Glass Passivated Junction High Efficiency Rectifiers
Reverse Voltage 50 to 1000V Forward Current3.0A

FEATURES

- * Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- * Ideally suited for use in very high frequency switching power supplies, inverters and as free wheeling diodes
- * Ultrafast recovery time for high efficiency
- * Excellent high temperature switching
- * Soft recovery characteristics
- * Cavity-free glass passivated junction
- * High temperature soldering guaranteed:
260°C/10 seconds, 0.375" (9.5mm) lead length,
5 lbs. (2.3kg) tension

Mechanical Data

Case: JEDEC DO-201AD, molded plastic over glass DIE


Terminals: Plated axial leads, solderable per
MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.038 oz., 1.03 g

Handling precaution:None



We declare that the material of product compliance
with ROHS requirements

1.Electrical Characteristic

Maximum & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	HER 301G	HER 302G	HER 303G	HER 304G	HER 305G	HER 306G	HER 307G	HER 308G	Unit
Marking		HER 301G	HER 302G	HER 303G	HER 304G	HER 305G	HER 306G	HER 307G	HER 308G	
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	300	400	600	800	1000	V
Maximum RSM voltage	V _{RSM}	35	70	140	210	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	300	400	600	800	1000	V
Maximum average forward rectified current 0.375" (9.5mm) lead length at T _A = 55°C	IF(AV)	3.0								A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	150				125				A
Maximum full load reverse current, full cycle average,0.375"(9.5mm) lead lengths at T _A = 55°C	IR(AV)	100								μA
Typical thermal resistance (Note 2)	R _{θJA}	55								°C/W
Operating junction and storage temperature range	T _J , T _{TSG}	-50 to +150								°C

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter Symbol	symbol	HER 301G	HER 302G	HER 303G	HER 304G	HER 305G	HER 306G	HER 307G	HER 308G	Unit		
Maximum instantaneous forward voltage at 3.0A	V _F	1.00		1.30		1.85				V		
Maximum DC reverse current TA = 25°C at rated DC blocking voltage TA = 125°C	IR	10 200								μA		
Typical reverse recovery time (Note 1)	trr	50				75				ns		
Typical junction capacitance at 4.0V, 1MHz	C _J	50				40				PF		

NOTES:

1. IF = 0.5A, IR = 1.0A, IRR = 0.25A
2. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

HER301G thru HER308G

2. Ratings and Characteristic Curves (TA = 25°C unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig. 3. - Typical Instantaneous Forward Characteristics




Fig 5. - typical transient thermal impedance




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig 4. - Typical Reverse Characteristics





Fig 6. - Typical Junction Capacitance



HER301G thru HER308G


3. dimension:

Package outline						
Dimensions					Note:	
	inches		mm			
L	Min.	Max.	Min.	Max.	DO-201AD	
L1	0.335	0.375	8.5	9.5	molded plastic case	
ΦD	1.0	-	25.4	-	The marking band indicates the	
Φd	0.197	0.220	5.0	5.6	cathode	
	0.048	0.052	1.2	1.3		

标题:	文件编号: WI-250
塑封生产线轴向产品包装规范	第 4 版 第 0 次修改
	第 1 页

1 弹带盒装 ammo and box


1.1. 弹带盒规格 ammo spec.



单位: mm

	L	W	H
T52	262±2	76±2	90±2
T42	262±2	64±2	90±2
T26	250±3	45±3	95±3

1.2 弹带内盒要求 inner box spec.



标题:	文件编号: WI-250
塑封生产线轴向产品包装规范	第 4 版 第 0 次修改
	第 2 页

1.4 标签要求 label spec.


1.4.1 LRC标签 LRC label

成 型	*****	成型规格 forming spec.
FORMING		
型 号	*****	LRC产品型号 type
TYPE		
重复峰压 (V)	****	产品重复峰压值 peak repetitive voltage
PRV (V)		
额定电流 (A)	**	产品额定电流值 average output current
I _o (A)		
数量 (只)	****	产品数量 quantity
Q'TY (pcs)		
QC章		
检验员	****	
CHECKER	02	
日期:	*****	产品生产日期 date
DATE:		

1.4.2 环保标签 environmental protection label



2.外箱规格 cartoon spec.




3 按以上包装方式, 编带数量和外包装箱产品数量: typing and cartoon spec.

	塑封外型			
	A-405 & DO-41 & R-1	R-3	DO-15	DO-201AD
每根编带数量 quantity/ammo	3K	1.8K	2K(T52) 1.8K(T26)	0.8K
外箱数量 (T52编带) quantity/cartoon	30K	18K	20K	8.0K
外箱数量 (T26编带) quantity/cartoon	60K	36K	36K	-
外箱数量 (T42编带) quantity/cartoon	54K	32.4K	36K	-

标题:	文件编号: WI-250
塑封生产线轴向产品包装规范	第 4 版 第 0 次修改
	第 3 页

4 编带规格 brede spec



尺寸代号	编带尺寸 typing dimension					
	26/tape	35/tape	40/tape	42/tape	52/tape	52/tape#
W	26 0.0/+1.6	35 -1.0/+0.5	40 -1.0/+0.5	42 -1.0/+1.0	52 -1.0/+2.0	52 -1.0/+2.0
P	5±0.5	5±0.5	5±0.5	5±0.5	5±0.5	10±0.5
L1-L2	<1.0	<1.0	<1.0	<1.0	<1.0	<1.0
H	6±1.0	6±1.0	6±1.0	6±1.0	6±1.0	6±1.0
Z	<1.0	<1.0	<1.0	<1.0	<1.0	<1.0
R	<1.0	<1.0	<1.0	<1.0	<1.0	<1.0
T	>3.5	>3.5	>3.5	>3.5	>3.5	>3.5

注: 52编带# 为DO-201AD编带规格 "52编带#" just for D0-201AD

1. 红白编带厚度为0.05mm; 两种胶带各自之间无明显色差; 编带要求均为胶带。

The typing thickness is 0.05mm and color is obvious difference

2. 两端引带20~40cm. Typing lead over 20~40cm

3. 红色编带一端为二极管“负极” ; 白色编带一端为二极管“正极”。

red color is cathode ,white color is anode

4. 无卤 green epoxy compound (无卤产品才贴HF only)


 Green



乐山无线电股份有限公司
Leshan Radio Company, Ltd

HER301G thru HER308G

4. Update Record

版次	更新记录	更新作者	更新日期
1	第一版	周杰	2010-6-22
2	1. 取消HER308HG; 2. 增加包装规范	周杰	2012-8-3