


LPB8233DT0AG

P-Channel 20-V (D-S) MOSFET

1. FEATURES

- Low RDS(on) trench technology
- Low thermal impedance.
- Fast switching speed.
- We declare that the material of product compliance with RoHS requirements and Halogen Free.




DFN3333-8A

2. APPLICATIONS

- Load Switches
- DC/DC Conversion
- Motor Drives

3. DEVICE MARKING AND RESISTOR VALUES

Device	Marking	Shipping
LPB8233DT0AG	N2A	2000/Tape&Reel



4. MAXIMUM RATINGS(Ta = 25°C unless otherwise stated)

Parameter		Symbol	Limits	Unit
Drain-to-Source Voltage		VDS	-20	V
Gate-to-Source Voltage		VGS	± 10	V
Continuous Drain Current(Note 1)	TA =25°C	ID	-18	A
	TA =70°C		-14	
Continuous Drain Current(Note 3)	TA =25°C		-7	
	TA =70°C		-5	
Pulsed Drain Current (Note 2)		IDM	-70	
Pulsed Drain Current (Note 3)			-28	
Avalanche Current		IAS	43	A
Avalanche Energy L=0.1mH		EAS	93	mJ
Power Dissipation(Note 1)	TA =25°C	PD	2.5	W
	TA =70°C		2	
Power Dissipation(Note 3)	TA =25°C		0.7	
	TA =70°C		0.4	
Operating Junction and Storage Temperature Range		TJ,TSTG	-55 ~+150	°C

5. THERMAL CHARACTERISTICS

Parameter	Symbol	Limits	Unit
Maximum Junction-to-Ambient(Note 1)	RθJA	50	°C/W
Maximum Junction-to-Ambient(Note 3)	RθJA	174	
Maximum Junction-to-Case	RθJC	2.7	

- 1.Surface mounted on "1.5 x 1.5" FR4 board using 1 sq in pad, 2 oz Cu
- 2.Pulse width limited by maximum junction temperature.
- 3.Surface mounted on FR4 board using the minimum recommended pad size.





6. ELECTRICAL CHARACTERISTICS (Ta= 25°C)

Characteristic		Symbol	Min.	Typ.	Max.	Unit
Static						
Drain-Source Breakdown Voltage (VGS = 0 V, ID = -250 μ A)		V(BR)DSS	-20	-	-	V
Gate-Source Threshold Voltage (VDS = VGS, ID = -250 μ A)		VGS(TH)	-0.5	-0.7	-1.3	V
Gate-Body leakage current (VDS = 0 V, VGS = $\pm$ 10V)		IGSS	-	-	$\pm$ 100	nA
Zero Gate Voltage Drain Current (VDS = -16 V, VGS = 0 V) (VDS = -16 V, VGS = 0 V, TJ = 55°C)		IDSS	-	-	-1 -10	μ A
Drain-to-Source On-Resistance(Note 4) (VGS = -4.5 V, ID = -14 A) (VGS = -2.5 V, ID = -11 A)		RDS(ON)	-	7.5 10	9.5 13.8	m Ω
Diode Forward Voltage(Note 4) (IS = -2.5 A, VGS = 0 V)		VSD	-	-0.69	-1.2	V
Dynamic(Note 5)						
Total Gate Charge	(VDS = -10 V, VGS = -4.5 V, ID = -14.6 A)	Qg	-	61	-	nC
Gate to Source Charge		Qgs	-	11.4	-	
Gate to Drain Charge		Qgd	-	14.7	-	
Turn-on Delay Time	(VDS=-10 V, RL=0.7 Ω , ID=- 14.6A, VGEN=- 4.5 V, RGEN=6 Ω)	td(ON)	-	29	-	nS
Rise Time		tr	-	180	-	
Turn-Off Delay Time		td(OFF)	-	415	-	
Fall Time		tf	-	270	-	
Input Capacitance	(VDS=-15 V, VGS=0 V, f=1MHz)	Ciss	-	5147	-	pF
Output Capacitance		Coss	-	661	-	
Reverse Transfer Capacitance		Crss	-	616	-	
Gate-Resistance (VDS = 0 V, VGS = 0 V, f = 1 MHz)		Rg	-	2.5	10	Ω
Source-Drain DIODE Ratings and Characteristics(Tc= 25° C)						
Continuous Current(Note 3)		IS	-	-	-20	A
Plused Current(Note 3)		ISM	-	-	-70	
Reverse Recovery Time (IF=IS, dIf/dt=100A/us)		trr	-	-	200	nS
Reverse Recovery Charge (IF=IS, dIf/dt=100A/us)		Qrr	-	-	96	nC





4.Pulse test: PW $\leq$ 300us duty cycle $\leq$ 2%.

5.Guaranteed by design, not subject to production testing.




7.ELECTRICAL CHARACTERISTICS CURVES



7.ELECTRICAL CHARACTERISTICS CURVES(Con.)




7.ELECTRICAL CHARACTERISTICS CURVES(Con.)



8.OUTLINE AND DIMENSIONS


DFN3333-8A



DFN3333-8A			
DIM	MIN	NOR	MAX
A	0.60	0.65	0.70
A1	0.00	0.03	0.05
b	0.27	0.32	0.37
D	3.25	3.30	3.35
E	3.25	3.30	3.35
D1	2.22	2.27	2.32
E1	1.60	1.65	1.70
e	0.65BSC		
L	0.40	0.45	0.50
L1	0.30	0.35	0.40
A3	0.152REF.		
All Dimensions in mm			

9.SOLDERING FOOTPRINT

DFN3333-8A



DFN3333-8A	
DIM	(mm)
C	0.65
X	0.42
X1	0.42
X2	0.23
X3	2.37
Y	0.70
Y1	1.85
Y2	3.70
Y3	2.25

DISCLAIMER

- Curve guarantee in the specification. The curve of test items with electric parameter is used as quality guarantee. The curve of test items without electric parameter is used as reference only.
- Before you use our Products for new Project, you are requested to carefully read this document and fully understand its contents. LRC shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any LRC's Products against warning, caution or note contained in this document.
- All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using LRC's Products, please confirm the latest information with a LRC sales representative.