







N=PIN数



P.C.B LAYOUT

Material 材料

Insulator 塑胶: PBT PA9T (UL 94V-0)

Contact 端子: Brass 黄铜

Surface Coating 表面镀层: Gold Over Nickel 里镍外金

Electrical Characteristics 电气特性

Current rating 额定电流: 2.5Amps

Dielectric Withstanding Voltage 耐压:

AC 500V for 1 Minute.

Insulator Resistance 绝缘电阻: 1000MΩ Min.

Contact Resistance 接触电阻: 20mΩ Max.

Operating Temperature 工作温度: -40°C ~ +105°C

Max. Processing Temp 瞬时温度:

240° C for 30-60 seconds

(260° C for 10 seconds)

| 未注尺寸公差 | | | PZ2.54-2*N-wz | | 上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD 上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD | | | |
|--------|-------|-----------|---------------|----------------|---|----|----|----|
| 尺寸 | 公差 | | | | | | | |
| X. | ±0.3 | ±5° | 版本编号 | 20171018 A/0 | TEL:86-21-34975176/51571121 | | | |
| X.X | ±0.2 | ±3° | 图纸编号 | ZR20171018-260 | | | | |
| X.XX | ±0.15 | | 物料编号 | | 1:1 | mm | 图幅 | A4 |
| 制图 | 周元金 | 201171018 | 第三视角 | | | | | |
| 审核 | 张海娜 | 201171018 | | | | | | |
| 核准 | 章妹 | 201171018 | | | | | | |