



NOTES:

- Rating: 10A 125/250VAC CUL;CCC
- CONTACT RESISTANCE: 50mΩ Max
- INSULATION RESISTANCE: 100MΩ Min, at 500VDC
- WITHSTAND VOLTAGE: 2000VAC 0.5mA 1 minute

电话: 0769-82310511-867
 邮箱: hooya89@hooya.hk

8	本体	PA66	1
7	盖子	PA66	1
6	3#端子	C2680 1/2H Ag-plating	2
5	3#PIN	C1100 1/2H Ag-plating	2
4	连接片	C2680 1/2H Tin-plating	1
3	2#PIN	C2680 1/2H Ni-plating	2
2	1#PIN	C2680 1/2H Ni-plating	1
1	1#端子	C2680 1/2H Tin-plating	3
NO.	PART NAME	MATERIAL	Q'TY

A	5	→	10	→	DIMENSIONAL TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	
	4	→	9	→								
	3	→	8	→	X	±0.30	2019.05.20	MAT'L	***			
	2	→	7	→	X.X	±0.20				MATERIAL NO.	DRAWING NO.	
	1	→	6	→	X.XX	±0.10	RT-C14B-H00-13-R	WIF119108	AO			
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LECLION ELECTRONIC & HARDWARE CO., LTD.						