





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
A	NEW	INTERIM INITIAL RELEASE.	2021.06.16	郭康



Specifications
 Current Rating:1.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:300VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Copper alloy
 High Temperature Thermoplastic: Suitable for Reflow Soldering Process (LCP, Nylon HTN, Nylon9T)
 All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PEA230 - XX XX A 045 X X X X

No. of Pins per Row: 02~50
 Standard Plating: 02=Gold Flash
 Selective Plating: 01=Tin, 05=Gold Flash/Tin
 Insulator Material: R=NYLON-HTN, C=LCP, J=NYLON-9T
 Color: 1=Black, 5=Natural
 Contact Material: A=Phosphor Bronze, B=Brass
 Standard Packing: C=Tube(03~50PIN)
 Selective Packing: A=Box, E=CAP+Tube(04~50PIN), F=CAP+Tape&Reel

 Website:www.greenconn.com E-mail:sales@greenconn.com	3RD.ANG PROJ. 	GENERAL TOLERANCE		DESIGNED: 郭康	DATE: 2021.06.16	DWG. NO.	TITLE.
		X'±5.0'	X±0.30			GPEA230-CA045	
REV. A UNIT. mm SCALE. 4:1 PAGE. 1/1		.X'±3.0'	.X±0.25	CHECKED:	DATE:	PART NO.	
		.XX'±2.0'	.XX±0.15			GPEA230-XXXX A045XXXX	
		.XXX'±1.0'	.XXX±0.10	APPROVED:	DATE:		