




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2021.06.04	郭康



Specifications
 Current Rating:1Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:300VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Copper alloy
 High Temperture Thermoplastic: Suitable for Reflow Soldering Process (LCP, Nylon HTN, Nylon9T)
 Regular Thermoplastic: Only Suitable for Wave Soldering Process (PBT).
 All materials must meet GREENCONN hazardous substances control standards.




Ordering Information

G PEB212 - XX XX A 052 X X X X

No. of Pins per Row 02~40	Standard Plating 02=Gold Flash Selective Plating 01=Tin 05=Gold Flash/Tin	Insulator Material A=PBT (Halogen) K=PBT (Halogen Free) R=NYLON-HTN C=LCP J=NYLON-9T	Color 1=Black 5=Natural	Contact Material A=Phosphor Bronze B=Brass	Standard Packing C=Tube(04~40PIN) Selective Packing A=Box H=Acetate tape+T&R
------------------------------	---	---	-------------------------------	--	--

Recommended P.C.Board Layout
 (Tolerance:±0.05)



3RD.ANG PROJ.
 PAGE. 1/1

GENERAL TOLERANCE	
X'±5.0'	X.±0.30
.X'±3.0'	.X±0.25
.XX'±2.0'	.XX±0.15
.XXX'±1.0'	.XXX±0.10

DESIGNED: 郭康
 CHECKED:
 APPROVED:

DATE: 2021.06.04
 DATE:
 DATE:

DWG. NO.
 GPEB212-CA052
 PART NO.
 GPEB212-XXXX A052XXXX

TITLE.
 1.27 PIN HEADER
 DUAL ROWS R/A TYPE
 CONNECTOR