





MAPX	MODIFICATION	DATE
------	--------------	------



- NOTES:
- HOUSING: SEE NOTES.
TERMINAL: SEE NOTES.
SHELL: SEE NOTES.
 - MECHANICAL CHARACTERISTIC:
INSERTION FORCE: 35N(3.57KGF) MAX
EXTRACTION FORCE: 10~35N(1.02~3.57KGF) MIN
DURABILITY: 1500 CYCLES EXTRACTION FORCE: 10~35N
5000 CYCLES MIN
5000 CYCLES EXTRACTION FORCE: 3~35N
 - ENVIRONMENTAL:
OPERATING TEMPERATURE: -55°C+85°C
 - Contact finish:
01: Selective Gold Flash
02: Selective Gold 3U"
03: Selective Gold 5U"
04: Selective Gold 15U"
05: Selective Gold 30U"

深圳市精拓金电子有限公司

产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

X	±0.15	X	±5°
X	±0.10	X	±2°
XX	±0.05	XX	±1°
XXX	±0.03	XXX	±0.5°

单位 UNITS	MM	制图 DRAWING	许榕强	制料号 PRODUCT PART NO.	914-122B1011D10200
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AF/10.0苹果款/沉板反向四脚插板/铜壳露面/FBT白胶防火
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW	版本 VER
					AD