


HVCW-3535MGS



3535 系列产品 / Products Series

具有高发光效率、高一致性、高稳定性、高可靠性，主要用于汽车应用

High luminous efficiency, consistency, stability and reliability, it is mainly used in automobile applications.

特征

- 外观：白色EMC塑料，荧光硅胶封装
- 50% I_v 视角：120°
- 颜色：Cx=0.325,Cy=0.335 (CIE1931)
- 资格：可靠性测试符合AEC Q102和 IEC 60810标准
- 潮湿敏感等级-2

Features

- Package: Colored diffused silicone in white EMC cup
- Viewing angle at 50% I_v : 120°
- Color: Cx=0.325,Cy=0.335 (acc. to CIE1931)
- Qualifications: Reliability test compliance with AEC Q102 and IEC 60810
- MSL-2

应用

- 信号灯
- 汽车内外部照明应用

Applications

- Signaling
- Interior and exterior lighting for automotive

订购信息 / Ordering Information

型号 Type	光通量 Luminous Flux $\Phi_v @ I_f=350mA$	订单编号 Ordering Code
HVCW-3535MGS-XXXX-XXXX-XX 亮度档 Brightness 色度坐标 Chromaticity Coordinate 电压档 Forward Voltage	112 -180 lm	XXXXXX

备注

■ 亮度档

单个最小包装只装有同一个亮度档次的产品，具体分档信息请见第4页

例如：HVCW-3535MGS-5L8L-XXXX-XX，单个卷盘中的产品只有5L、6L、7L、8L中的某一档

■ 色度坐标档

单个最小包装只装有同一个色度坐标档次的产品，具体分档信息请见第5页

例如：HVCW-3535MGS-XXXX-ebvF46fcbB46-XX，单个卷盘中的产品只有ebvF46、ebxD46、ebzB46、fcbB46中的某一档

■ 正向电压档

单个最小包装只装有同一个正向电压档次的产品，具体分档信息请见第4页

例如：HVCW-3535MGS-XXXX-XXXX-8F8H，单个卷盘中的产品只有8F、8G、8H中的某一档

Note

■ Brightness Grouping

Only one brightness group will be packed in each reel. Please refer to page #4 for details.

E.g.: HVCW-3535MGS-5L8L-XXXX-XX, means only one bin of 5L、6L、7L or 8L is in each reel.

■ Chromaticity Coordinate Groups

Only one Chromaticity Coordinate group will be packed in each reel. Please refer to page #5 for details.

E.g.: HVCW-3535MGS-XXXX-ebvF46fcbB46-XX, means only one bin of ebvF46、ebxD46、ebzB46 or fcbB46 is in each reel.

■ Forward Voltage Groups

Only one forward voltage group will be packed in each reel. Please refer to page #4 for details.

E.g.: HVCW-3535MGS-XXXX-XXXX-8F8H, means only one bin of 8F、8G or 8H is in each reel.

极限参数 / Maximum Ratings

参数 Parameters	符号 Symbol	数值 Rating	单位 Unit
结温 / Junction Temperature	T_j	150	°C
正向电流 / Forward Current ($T_s=25^{\circ}\text{C}$)	I_f	500	mA
峰值正向电流 Peak Forward Current ($t \leq 10\mu\text{s}$; $D=0.005$; $T_s=25^{\circ}\text{C}$)	I_{fp}	1000	mA
反向电压 / Reverse Voltage ($T_s=25^{\circ}\text{C}$)	V_r	不可施加反向电压 / not designed for reverse operation	V
抗静电能力 Electrostatic Discharge (HBM)	V_{ESD}	2000	V
操作温度 / Operating Temperature	T_{opr}	-40 ~ +125	°C
储存温度 / Storage Temperature	T_{stg}	-40 ~ +125	°C

特性 / Characteristics ($T_s = 25^{\circ}\text{C}$; $I_f = 350\text{ mA}$)


参数 Parameters		符号 Symbol	数值 Rating	单位 Unit
色坐标 / Chromaticity coordinates acc. to CIE 1931	typ.	Cx	0.325	—
		Cy	0.335	—
50 % I_v 下的视角 / Viewing Angle at 50 % I_v	typ.	2Φ	120	°
正向电压 / Forward Voltage	min.	V_f	2.75	V
	typ.	V_f	3.25	V
	max	V_f	3.75	V
反向电流 / Reverse Current ($V_R=12\text{V}$)	typ.	I_r	不可施加反向 电压 / not designed for reverse operation	uA
	max.	I_r		uA
实际热阻值 (PN结-焊点) / Real Thermal Resistance (Junction / Solder Point)	max.	R_{th} JS _{real}	7.2	K/W

亮度分档 / Brightness Grouping ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 350\text{ mA}$)

档次 Grouping	光通量 Luminous Flux Φ_v (min.)	光通量 Luminous Flux Φ_v (max.)
5L	112 lm	125 lm
6L	125 lm	140 lm
7L	140 lm	159 lm
8L	159 lm	180 lm

正向电压分档 / Forward Voltage Grouping ($T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 350\text{ mA}$)

档次 Grouping	正向电压 Forward Voltage V_f (min.)	正向电压 Forward Voltage V_f (max.)
8E	2.75 V	3.00 V
8F	3.00 V	3.25 V
8G	3.25 V	3.50 V
8H	3.50 V	3.75 V



X		Y	X		Y	X		Y	X		Y
ebvF46	0.3127	0.3093	ebxD46	0.3163	0.3181	ebzB46	0.3203	0.3274	fcbB46	0.3248	0.3370
	0.3104	0.3234		0.3145	0.3330		0.3190	0.3430		0.3241	0.3534
	0.3199	0.3325		0.3246	0.3424		0.3298	0.3526		0.3355	0.3633
	0.3212	0.3175		0.3253	0.3266		0.3299	0.3361		0.3350	0.3460

标签信息 / Information on Label


例 / E.g.: 6L-ebxD46-8G

亮度档 / Brightness	颜色 / Color	正向电压 / Forward Voltage
6L	ebxD46	8G

相对发射光谱 - $V(\lambda)$ = 标准人眼视觉曲线


Relative Spectral Emission - $V(\lambda)$ = Standard Eye Response Curve

$I_{rel} = f(\lambda)$; $T_s = 25\text{ }^{\circ}\text{C}$; $I_f = 350\text{ mA}$




辐射特性 / Radiation Characteristics

$$I_{rel} = f(\phi); T_s = 25^\circ\text{C}$$




正向电流 / Forward Current

$$I_f = f(V_f); T_a = 25^\circ\text{C}$$




相对亮度特性曲线 / Relative Luminous Intensity


$$I_v/I_v(350\text{ mA}) = f(I_f); T_a = 25^\circ\text{C}$$




色坐标数据表/Chromaticity coordinate shift

 $\Delta C_x, \Delta C_y = f(I_f); T_s = 25^\circ\text{C}$ 


相对正向电压 / Relative Forward Voltage

 $\Delta V_f = V_f - V_f(25^\circ\text{C}) = f(T_j); I_f = 350\text{ mA}$ 


相对发光强度 / Relative Luminous Intensity

 $I_v/I_v(25^\circ\text{C}) = f(T_j); I_f = 350\text{ mA}$ 

色坐标数据表/Chromaticity coordinate shift


 $\Delta Cx, \Delta Cy = f(I_f); I_f = 350\text{mA}$ 

焊点温度与正向电流 / Solder Point Temperature vs. Forward Current

 $I_f = f(T_s)$ 

产品尺寸 / Package Outline

Unit: mm

Error range: ± 0.1 

备注

■ 统计质量: 60mg


■ 标 记: 阴极

NOTE

■ Approximate Weight: 60mg

■ Mark: Cathode

推荐焊盘 / Recommended Solder Pad




注释

■ 不适合超声波清洗的封装

NOTE


■ Package not suitable for ultrasonic cleaning

回流焊要求 / Reflow Soldering Profile



主要特性 Profile Feature	符号 Symbol	无铅焊接 Pb-Free (SnAgCu) Assembly			单位 Unit
		min.	rec.	max.	
预热升温速率 Ramp-up Rate to Preheat 25°C-150°C	—	—	2	3	°C/s
时间 / Time (T_{smin} to T_{smax})	T_s	60	100	120	s
峰值升温速率 Ramp-up Rate to Peak (T_{smax} to T_p)	—	—	2	3	°C/s
熔点温度 Liquidus Temperature	T_l		217		°C
高于熔点温度的时间 Time above Liquidus Temperature	t_l	—	80	100	s
峰值温度 / Peak Temperature	T_p	—	255	260	°C
规定的峰值温度 ± 5°C 以内的时间 Time within 5°C of the Specified Peak Temperature	t_p	10	20	30	s
降温速率 / Ramp-down Rate (T_p to 100°C)	—	—	3	6	°C/s
时间 / Time (25°C to T_p)	—	—	—	480	s

卷带与卷盘 / Tape and Reel



前端空带: 最小400 mm; 尾端空带: 最小160 mm; 尺寸符合: EIA 481-C标准
 Leader: min. 400 mm; Trailer: min. 160 mm; Requirement acc. to EIA 481-C

卷带尺寸 / Tape Dimensions (mm)

W	P0	P	P2	D0	E	F
12±0.3	4±0.1	8±0.1	2±0.05	1.50±0.1	1.75±0.1	5.50±0.05


卷盘尺寸 / Reel Dimensions (mm)

A	W1	W2	N	R
178.0±0.2	8.0±0.5	8.0±0.5	60.0±0.4	13.5±0.3


数量 (颗/卷) / Quantity (pcs/reel)

2000

条形码标签 / Barcode-Product-Label (BPL)



包装材料及过程 / Dry Packing Process and Materials




备注

产品包装在一个干燥的铝箔袋里，同时内附有干燥剂和湿度卡。
对于干燥包装，您可以从网络或JEDEC标准里获取。

NOTE

Moisture-sensitive product is packed in a dry bag containing desiccant and HIC (humidity indicator card).
Regarding dry pack you may find further information in the internet or JEDEC.

出货包装及材料 / Transportation Packing and Materials



出货箱尺寸 / Dimensions of Transportation Box (mm)

宽度 / Width	长度 / Length	高度 / Height
256±5	223±5	62±5
256±5	223±5	124±5

注释

典型值: 每个产品的实际值可能与这些统计出的典型值不同。

公差: 除非图纸中有说明, 公差默认为 $\pm 0.1 \text{ mm}$ 。

正向电压: 正向电压是在8ms脉冲电流并且内部再现性为 $\pm 0.05\text{V}$ 和一个 $\pm 0.1\text{V}$ 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

色度坐标: 色度坐标是在25ms脉冲电流并且内部再现性为 ± 0.005 和一个 ± 0.01 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

亮度: 亮度是在25ms脉冲电流并且内部再现性为 $\pm 8\%$ 和一个 $\pm 11\%$ 的外在不确定性 (按照GUM K=3因子) 来进行测试的。

特殊声明: 本版本最终解释权归属鸿利智汇, 当中英文意思发生歧义时, 以中文为准。

Glossary

Typical Values: Actual values of each product may differ from these statistical values .

Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with $\pm 0.1\text{mm}$.

Forward Voltage: The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of $\pm 0.05 \text{ V}$ and an expanded uncertainty of $\pm 0.1 \text{ V}$ (acc. to GUM with a coverage factor of $k = 3$).

Chromaticity coordinate groups: Chromaticity coordinate groups is measured at a current pulse of typically 25 ms, with an internal reproducibility of ± 0.005 and an expanded uncertainty of ± 0.01 (acc. to GUM with a coverage factor of $k = 3$).

Brightness: Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of $\pm 8\%$ and an expanded uncertainty of $\pm 11\%$ (acc. to GUM with a coverage factor of $k = 3$).

Special Statement: The final interpretation of this specification shall be vested in Honglitrionic, in the case of ambiguity, the Chinese version shall prevail.