

Specification Sheet

Part Number: 156-00882

Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



2-Piece Cable Tie/Fir Tree Mount, 8.0"L, 0.20 - 0.22" Mounting Hole Diameter, PA66HS, Black, 500/pkg

Article Number	156-00882
Type	T50RFT5.5SD
Color	Black (BK)
Quantity Per	carton
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Cable Tie/Fir Tree Mount, 8.0"L, 0.20 - 0.22" Mounting Hole Diameter, PA66HS, Black, 500/pkg

Global Part Name T50RFT5.5SD-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 8.0

Length L (Metric) 203.2

Fixation Method Fir Tree

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.20

Bundle Diameter Min (Metric) 5.0

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 45.0

Thickness T (Imperial) 0.05

Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.18
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	4.5
Mounting Hole Diameter D (Imperial)	0.2 - 0.22
Mounting Hole Diameter D (Metric)	5.0 - 5.7 mm
Mounting Hole Diameter D Min (Imperial)	0.224
Mounting Hole Diameter D Max (Imperial)	0.196
Mounting Hole Diameter D Max (Metric)	5.7
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS PA66HIRHS

Material Cable Tie Polyamide 6.6 heat stabilized (PA66HS)

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)