




日期/Date	档案员 Filing Clerk	1	2	3	4	5	6																																												
						技术参数: 插芯: - 插针数: 5+PE - 额定电流: 16A - 相对地额定电压: 230V - 相间额定电压: 400V - 额定脉冲电压: 4kV - 污染等级: 3 - 依据UL/CSA的额定电压: 600V - 绝缘阻抗: >10¹⁰Ω - 材料: 聚碳酸酯 - 颜色: RAL 7032 (浅灰色) - 温度范围: -40℃ - +125℃ - 依据UL 94的阻燃等级: V0 - 可插拔次数: >500 插针: - 接线方式: 冷压连接 - 材料: 铜合金 - 表面处理: · 镀银 · 镀金 - 接触电阻: <1mΩ - 线径范围: · 冷压连接: 0.14-2.5mm²(26-14 AWG) · PE连接: 2.5mm²(14 AWG) 外壳: - 材料: · 塑料外壳: 聚碳酸酯 · 金属外壳: 压铸锌 - 依据UL 94的阻燃等级: · 塑料外壳: V0 · 塑料外壳: IP67 · 金属外壳: IP44 · IP67(实现螺栓密封) - 附件: · 保险延迟针: CESM-1.0R/CESM-1.5R/CESM-2.5R · 冷压钳: TL02G(0.5-4mm²) TL02(0.14-0.37mm²) · 退针器: TL01 · 编码元件: CODE-E Technical specification: Insters: - No. of contact: 5+PE - Rated current: 16A - Rated voltage - ground: 230V - Rated voltage - conductor: 400V - Rated impulse voltage: 4kV - Pollution degree: 3 - Rated voltage acc.to UL/CSA: 600V - Insulation resistance: >10¹⁰Ω - Material: polycarbonate - Colour: RAL 7032(light grey) - Temperature range: -40℃ - +125℃ - Flammability acc.to UL 94: V0 - Mating cycles: >500 Contacts: - Terminal: crimp terminal - Material: copper alloy - Surface: · Hard-silver plated · Hard-gold plated - Contact resistance: <1mΩ - Wire gauge: · Crimp terminal: 0.14-2.5mm²(26-14 AWG) · PE contact: 2.5mm²(14 AWG) Hoods/Housings: - Material: · Plastic hoods/housings: polycarbonate · Metal hoods/housings: zinc die-cast - Flammability acc.to UL 94: V0 - Degree of protection, acc.to IEC 60529 for coupled connector: · Plastic hoods/housings: IP67 · Metal hoods/housings: IP44 · IP67(is achieved with seal screw) - Accessories: · Relay contacts: CESM-1.0R/CESM-1.5R/CESM-2.5R · Crimp contact tool: TL02G(0.5-4mm²) TL02(0.14-0.37mm²) · Contact removal tool: TL01 · Coding element: CODE-E																																													
																																																			
		<table><tr><td>标记 Mark</td><td>处数 Number</td><td colspan="2">变更描述/Description</td><td>签名 Signature</td><td>日期 Date</td></tr><tr><td>绘图 Drawn</td><td>BQ LUO</td><td>18.10.2010</td><td>标准化 Stand.</td><td>-</td><td>-</td></tr><tr><td>审核 Checked</td><td>P RAO</td><td>18.10.2010</td><td></td><td></td><td></td></tr><tr><td>工艺 Process</td><td>-</td><td>-</td><td>批准 Approved</td><td>YY LIN</td><td>18.10.2010</td></tr></table>				标记 Mark	处数 Number	变更描述/Description		签名 Signature	日期 Date	绘图 Drawn	BQ LUO	18.10.2010	标准化 Stand.	-	-	审核 Checked	P RAO	18.10.2010				工艺 Process	-	-	批准 Approved	YY LIN	18.10.2010	<table><tr><td>表面处理 Finish</td><td colspan="3">-</td></tr><tr><td>材料 Material</td><td colspan="3">-</td></tr><tr><td>比例 Scale</td><td>版本 REV.</td><td>重量 Weight</td><td>数量 Qty.</td></tr><tr><td>1:1</td><td>V1.0</td><td>13.2g</td><td>-</td></tr><tr><td colspan="2"></td><td colspan="2">All Dimensions in mm Original Size DIN A 4</td></tr></table>		表面处理 Finish	-			材料 Material	-			比例 Scale	版本 REV.	重量 Weight	数量 Qty.	1:1	V1.0	13.2g	-			All Dimensions in mm Original Size DIN A 4	
标记 Mark	处数 Number	变更描述/Description		签名 Signature	日期 Date																																														
绘图 Drawn	BQ LUO	18.10.2010	标准化 Stand.	-	-																																														
审核 Checked	P RAO	18.10.2010																																																	
工艺 Process	-	-	批准 Approved	YY LIN	18.10.2010																																														
表面处理 Finish	-																																																		
材料 Material	-																																																		
比例 Scale	版本 REV.	重量 Weight	数量 Qty.																																																
1:1	V1.0	13.2g	-																																																
		All Dimensions in mm Original Size DIN A 4																																																	
				<table><tr><td>图号 Drawing No.</td><td>-</td></tr><tr><td>产品代号 Part Code</td><td>HQ-005/0-MC</td></tr><tr><td>产品料号 Part No.</td><td>1300050100001</td></tr><tr><td>产品名称 Part Name</td><td>-</td></tr></table> 厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD		图号 Drawing No.	-	产品代号 Part Code	HQ-005/0-MC	产品料号 Part No.	1300050100001	产品名称 Part Name	-																																						
图号 Drawing No.	-																																																		
产品代号 Part Code	HQ-005/0-MC																																																		
产品料号 Part No.	1300050100001																																																		
产品名称 Part Name	-																																																		