






技术参数:

插芯:

- 插针数: 4/0+PE
 - 额定电流: 80A
 - 额定电压: 830V
 - 额定脉冲电压: 8kV
 - 污染等级: 3
 - 依据UL/CSA的额定电压: 600V
 - 绝缘阻抗: $>10^{10}\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500
- ##### 插针:
- 接线方式: 螺钉连接
 - 材料: 铜合金
 - 表面处理: 镀银
 - 接触电阻: $\leq 0.3\text{m}\Omega$
 - 线径范围: $1.5-16\text{mm}^2(16-6 \text{ AWG})$
 - 拧紧力矩:
 - $\text{mm}^2: 1.5 \quad 2.5 \quad 4 \quad 6 \quad 10 \quad 16$
 - $\text{N}\cdot\text{m}: 1.2 \quad 2 \quad 3 \quad 3 \quad 3 \quad 3$
 - 剥线长度: 14mm

Technical specification:

Insters:

- No. of contact: 4/0+PE
 - Rated current: 80A
 - Rated voltage: 830V
 - Rated impulse voltage: 8kV
 - Pollution degree: 3
 - Rated voltage acc.to UL/CSA: 600V
 - Insulation resistance: $>10^{10}\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500
- ##### Contacts:
- Terminal: screw terminal
 - Material: copper alloy
 - Surface: hard-silver plated
 - Contact resistance: $\leq 0.3\text{m}\Omega$
 - Wire gauge: $1.5-16\text{mm}^2(16-6 \text{ AWG})$
 - Tightening tourque:
 - $\text{mm}^2: 1.5 \quad 2.5 \quad 4 \quad 6 \quad 10 \quad 16$
 - $\text{N}\cdot\text{m}: 1.2 \quad 2 \quad 3 \quad 3 \quad 3 \quad 3$
 - Stripping length: 14mm

						表面处理 Finish	—			图号 Drawing No.	—
						材料 Material	—			产品代号 Part Code	HK-004/0-F
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date				产品料号 Part No.	1280040210001
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name	—
绘图 Drawn	BQ LUO	18.10.2010	标准化 Stand.	—	—	1:1	V1.0	116.3g	—		
审核 Checked	P RAO	18.10.2010									
工艺 Process	—	—	批准 Approved	YY LIN	18.10.2010	  All Dimensions in mm Original Size DIN A 4			 厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD		