

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	O	RELEASED	05APR2005	X.H	K.O
	A	REVISED	10DEC2007	D.P	K.O
	B	ECR-16-017995	11JAN2017	O.Z	I.Y

D

D

C

C






B

B

A

A

VIEW DRAWING



- NOTES:
1. FINISH: PRE-TIN PLATED 0.8um MIN. 112-16-4(REFLOWED)
 2. NO CRACK WITH THE EYE
 3. SUITABLE WIRE SIZE IS SHOWN AS TABEL I
 4. 2-1813018-* APPLICATION SPEC REFER TO 1813018-*,
 5. GENERAL TOLERANCE:

0<X<10	±0.20
10<=X<30	±0.25

TABLE I

-1 AS SHOWN

2.9~3.8DIA	2~3.0SQ	N/A			16.00	1813018-6
2.2~2.7DIA	0.85~1.25SQ	N/A			16.00	1813018-5
1.5~2.2DIA	0.3~0.5SQ	N/A			16.00	1813018-4
2.9~3.8DIA	2~3.5SQ	12.6 REF	4.6	5REF	8.00	1813018-3
2.2~2.7DIA	0.85~1.25SQ					1813018-2
1.5~2.2DIA	0.3~0.5SQ					1813018-1
2.9~3.8DIA	2~3.0SQ	11.2REF	4.24	5.7REF	7.00	2-1813018-3
2.2~2.7DIA	0.85~1.25SQ					2-1813018-2
1.5~2.2DIA	0.3~0.5SQ					2-1813018-1
INSUL RANGE	WIRE RANGE	DIM.A	DIM.B	DIM.C	PITCH	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN X.HE 05APR2005	TE Connectivity			
		CHK R.ZHOU 05APR2005				
		APVD K.OOA 05APR2005	NAME MINI FUSE RECEPTACLE JUNCTION BOX			
		PRODUCT SPEC 108-101000				
		APPLICATION SPEC 114-101000				
		WEIGHT 0.93g				
		CUSTOMER DRAWING				
		SCALE 7:1				
		SHEET 1 OF 1				
		REV B				