







- 技术参数:

插芯:

 - 插针数: 4/4+PE
 - 额定电流:
 - 电力区: 63A
 - 信号区: 16A
 - 额定电压:
 - 电力区: 690V
 - 信号区: 250V
 - 额定脉冲电压:
 - 电力区: 8kV
 - 信号区: 4kV
 - 污染等级: 3
 - 依据UL/CSA的额定电压: 600V/230V
 - 绝缘阻抗: $>10^9\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: -40°C ~ $+125^{\circ}\text{C}$
 - 阻燃性: 符合UL 94: V0
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500

插针:

 - 接线方式: 轴向螺栓连接/弹片连接
 - 材料: 铜合金
 - 表面处理: 镀银
 - 接触电阻:
 - 强电针: $<0.5\text{m}\Omega$
 - 信号针: $<1\text{m}\Omega$
 - 线径范围:
 - 强电针: 6-16mm²(10-6 AWG)
 - 信号针: 0.14-2.5mm²(26-14 AWG)
 - 最大电缆直径:
 - 强电针: 11mm
 - 剥线长度:
 - 强电针: 11*mm
 - 信号针: 7-9mm
- Technical specification:

Insters:

 - No. of contact: 4/4+PE
 - Rated current:
 - Power area: 63A
 - Signal area: 16A
 - Rated voltage:
 - Power area: 690V
 - Signal area: 250V
 - Rated impulse voltage:
 - Power area: 8kV
 - Signal area: 4kV
 - Pollution degree: 3
 - Rated voltage acc.to UL/CSA: 600V/230V
 - Insulation resistance: $>10^9\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: -40°C ~ $+125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500

Contacts:

 - Terminal: axial screw terminal/spring terminal
 - Material: copper alloy
 - Surface: hard-silver plated
 - Contact resistance:
 - Power contacts: $<0.5\text{m}\Omega$
 - Signal contacts: $<1\text{m}\Omega$
 - Wire gauge:
 - Power contacts: 6-16mm²(10-6 AWG)
 - Signal contacts: 0.14-2.5mm²(26-14 AWG)
 - Max. insulation diameter:
 - Power contacts: 11mm
 - Stripping length:
 - Power contacts: 11*mm
 - Signal contacts: 7-9mm

						表面处理 Finish	—			图号 Drawing No.	—
						材料 Material	—			产品代号 Part Code	HK-004/4.1-M
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date				产品料号 Part No.	1280080110002
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name	—
绘图 Drawn	LJ ZOU	07.05.2020	标准化 Stand.	—	—	1:1	V1.0	—	1		
审核 Checked	HZ LAN	07.05.2020									
工艺 Process	—	—	批准 Approved	HQ ZHANG	07.05.2020			All Dimensions in mm Original Size DIN A 4			厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.,LTD