











REV.	ECN NO OR DESCRIPTION	REVISED	DATE



PCB 焊盘区
 下沉避让区
RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

Connector Pin Assignment

Pin Name	Description
C1	Vcc of SIM
C2	RST of SIM
C3	CLK of SIM
C5	GND of SIM
C6	Vop of SIM
C7	I/O of SIM

- 一、材质和镀涂:
- 1、胶芯: LCP,UL 94V-0,黑色
 - 2、端子: 磷铜C5210-H, T=0.15, 镍底镀金
 - 3、外壳: 不锈钢SUS304 T=0.2
- 二、技术参数:
- 接触电阻: 100MΩ MAX
- 绝缘阻抗: 1000MΩ MIN(500DC)
- 额定电流: 每个接触件1A MAX
- 额定电压: 30V MAX(DC)
- 耐压: 500V R.M.S/MIN
- 使用温度: -40℃~85℃
- 湿度: 90%~95%
- 寿命: >5000次

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: X ±0.15 X.X ±0.10 X.XX ±0.05

ANGLES: X ±2° X.X ±1°

东莞市汉博电子科技有限公司
 DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE: 6Pin H1.8 Hinged micro sim card conn.

DWN: xiong PART NO. SMO-1545

CHKD: lee SCALE:1:1 UNIT: mm

APVD: wang SIZE: A4 SHEET:10F 1 REV: A4

CUSTOMER COPY