

# HFM101 thru HFM109

## Surface Mount Glass Passivated High Efficiency Rectifiers

### Reverse Voltage 50 to 1200V Forward Current 1.0A

#### FEATURES

- \* Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- \* Ideally suited for use in very high frequency switching power supplies, inverters and as free wheeling diodes
- \* Ultrafast recovery time for high efficiency
- \* Excellent high temperature switching
- \* Soft recovery characteristics
- \* Cavity-free glass passivated junction
- \* High temperature soldering guaranteed:
- \* 260°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

#### Mechanical Data

**Case:** JEDEC DO-214AC, molded plastic over glass die

**Terminals:** Plated axial leads, solderable per MIL-STD-750, Method 2026

**Polarity:** Color band denotes cathode end

**Mounting Position:** Any

**Weight:** 0.0023 oz., 0.065 g

**Handling precaution:** None

#### 1. Electrical Characteristic

**Maximum & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.**

Parameter Symbol	symbol	HFM 101	HFM 102	HFM 103	HFM 104	HFM 105	HFM 106	HFM 107	HFM 108	HFM 109	Unit
marking		HF1	HF2	HF3	HF4	HF5	HF6	HF7	HF8	HF9	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	300	400	600	800	1000	1200	V
Maximum RSM voltage	$V_{RSM}$	35	70	140	210	280	420	560	700	840	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	300	400	600	800	1000	1200	V
Maximum average forward rectified current at $T_c = 75^\circ\text{C}$ (note2)	$I_{F(AV)}$	1.0									A
Peak forward surge current 8.3ms single half sine-wave, superimposed on rated load (JEDEC Method)	$I_{FSM}$	30									A
Maximum full load reverse current, full cycle average, 0.375"(9.5mm) lead lengths at $\bar{T}_j = 55^\circ\text{C}$	$I_R(AV)$	100									$\mu\text{A}$
Typical thermal resistance (Note 2)	$R_{\theta JA}$	150									$^\circ\text{C/W}$
Operating junction and storage temperature range	$T_J, T_{STG}$	-50 to +150									$^\circ\text{C}$



We declare that the material of product compliance with ROHS requirements

**Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.**

Parameter Symbol	symbol	HFM 101	HFM 102	HFM 103	HFM 104	HFM 105	HFM 106	HFM 107	HFM 108	HFM 109	Unit
Maximum instantaneous forward voltage at 1.0A	$V_F$	1.00		1.30		1.85				V	
Maximum DC reverse current $T_A = 25^\circ\text{C}$ at rated DC blocking voltage $T_A = 100^\circ\text{C}$	$I_R$	5.0					50				$\mu\text{A}$
Typical reverse recovery time (Note 1)	$t_{rr}$	50				75				ns	
Typical junction capacitance at 4.0V, 1MHz	$C_J$	17									PF

NOTES:

1.  $I_F = 0.5\text{A}$ ,  $I_R = 1.0\text{A}$ ,  $IRR = 0.25\text{A}$

2. 8.0mm<sup>2</sup> (.013mm thick) land areas

# HFM101 thru HFM109

## 2. Ratings and Characteristic Curves (TA = 25°C unless otherwise noted)

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-repetitive Peak Forward Surge Current




Fig 3. - Typical Instantaneous Forward Characteristics




Fig 4. - Typical Reverse Characteristics




Fig 5. - typical transient thermal impedance








Fig 6. - Typical Junction Capacitance



## HFM101 thru HFM109

### 3. dimension:



HFM106: HF---高效快速二极管; M---贴片产品; 1---IF=1A; 06---VB=600V;

**LRC**乐山无线电股份有限公司  
Leshan Radio Company, Ltd

## HFM101 thru HFM109

### 4. Update Record

版次	更新记录	更新作者	更新日期
1	第一版	周杰	2011-7-13
2	将HFM108H更改为HFM109	周杰	2013-4-23
3	增加印字说明	周杰	2013-7-15