

■ Features


- Low forward voltage drop.
- Excellent high temperature stability.
- Fast switching capability.
- Suffix "G" indicates Halogen-free part, ex.SS24G.
- Lead-free parts meet environmental standards of MIL-STD-19500 /228

■ Mechanical data

- Epoxy:UL94-V0 rated flame retardant
- Case : Molded plastic, DO-214AC / SMA
- Terminals : Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity : Indicated by cathode band
- Weight : 0.002 ounce, 0.055 gram

■ Outline

SMA(DO-214AC)



Dimensions in inches and (millimeters)

■ Maximum ratings and electrical characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Parameter	Conditions	Symbol	MIN.	TYP.	MAX.	UNIT
Forward rectified current	See Fig.1	$I_O$			2.0	A
Forward surge current	8.3ms single half sine-wave superimposed on rate load (JEDEC method)	$I_{FSM}$			50	A
Reverse current	$V_R = V_{RRM} \quad T_A = 25^{\circ}C$	$I_R$			0.5	mA
	$V_R = V_{RRM} \quad T_A = 125^{\circ}C$				20	
Diode junction capacitance	f=1MHz and applied 4V DC reverse voltage	$C_J$		120		pF
Thermal resistance	Junction to ambient	$R_{\theta JA}$		88		°C/W
Storage temperature		$T_{STG}$	-55		+150	°C

Symbol	Marking code	Max. repetitive peak reverse voltage $V_{RRM}$ (V)	Max. RMS voltage $V_{RMS}$ (V)	Max. DC blocking voltage $V_R$ (V)	Max. forward voltage @2A, $T_A = 25^{\circ}C$ $V_F$ (V)	Operating temperature $T_J$ (°C)
SS24	SS24	40	28	40	0.50	-55 ~ +150

■ Rating and characteristic curves

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3 - TYPICAL REVERSE CHARACTERISTICS






Fig. 4 - Total Capacitance VS. Reverse Voltage



■ SMA foot print



A	B	C
0.068 (1.70)	0.104 (2.60)	0.060 (1.50)

Dimensions in inches and (millimeters)

■ Ordering Information

Part Number	Symbol	Quantity Per Reel	Reel Size	Package
SS24AG	SS24	3 ,000	13 Inch	SMA

- TITAN reserves the right to make changes to this document and its products and specifications at any time without notice.
- Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- TITAN makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does TITAN assume any liability for application assistance or customer product design.
- TITAN does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.
- No license is granted by implication or otherwise under any intellectual property rights of TITAN.
- TITAN products are not authorized for use as critical components in life support devices or systems without express written approval of TITAN.