



## **WCR380N65TF/TG 650V N-Channel Super Junction MOSFET**

### **Description**

The WCR380N65 series is new generation of high voltage MOSFET family that is utilizing an advanced charge balance mechanism for outstanding low on-resistance and lower gate charge performance. This advanced technology has been tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate and higher avalanche energy. This device is suitable for various AC/DC power conversion in switching mode operation for higher efficiency.

### **Features**

- 700V@T<sub>J</sub>=150°C
- Typ.R<sub>DS(on)</sub>=0.31Ω
- Low gate charge
- 100% avalanche tested
- 100% R<sub>g</sub> tested



### **Order Information**

Device	Package	Marking	Units/Tube	Units/Real
WCR380N65TF-3/T	TO-220F	WCR380N65TFYW <sup>(1)</sup>	50	
WCR380N65TG-3/TR	TO-252E-2L	WCR380N65TGYW <sup>(2)</sup>		2500

Note 1: WCR380N65TF=Device code ;Y=Year ;W=Week (A~z);  
 Note 2: WCR380N65TG=Device code ;Y=Year ;W=Week (A~z);

### **Absolution Maximum Ratings T<sub>A</sub>=25°C unless otherwise noted**

Parameter	Symbol	WCR380N65TG		WCR380N65TF	Unit
Drain-Source Voltage	V <sub>DS</sub>	650			V
Gate-Source Voltage	V <sub>GS</sub>	±30			
Continuous Drain Current <sup>A</sup>	T <sub>C</sub> =25°C	I <sub>D</sub>	11	6.1	A
	T <sub>C</sub> =100°C		7.1	3.9	
Pulsed Drain Current	I <sub>DM</sub>	27			A
Single Pulsed Avalanche Energy <sup>B</sup>	E <sub>AS</sub>	162			mJ
Power Dissipation	T <sub>C</sub> =25°C	P <sub>D</sub>	100	31.2	W
	Derate above 25°C		0.8	0.25	
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55~150			°C
Lead Temperature	T <sub>L</sub>	260			°C
<b>Thermal Resistance Ratings</b>					
Maximum Junction-to-Ambient	R <sub>th(ch-A)</sub>	62 <sup>D</sup>		80	°C/W
Maximum Junction-to-Case	R <sub>th(ch-c)</sub>	1.25		4	


## Electronics Characteristics ( $T_A=25^\circ\text{C}$ , unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>						
Drain-to-Source Breakdown Voltage	$\text{BV}_{\text{DSS}}$	$V_{\text{GS}} = 0 \text{ V}, I_{\text{D}} = 250\text{uA}, T_J=25^\circ\text{C}$	650			V
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{DS}} = 650\text{V}, V_{\text{GS}} = 0\text{V}, T_J=25^\circ\text{C}$			1	$\mu\text{A}$
Gate-to-source Leakage Current	$I_{\text{GSS}}$	$V_{\text{DS}} = 0 \text{ V}, V_{\text{GS}} = \pm 30\text{V}$			$\pm 100$	nA
<b>ON CHARACTERISTICS</b>						
Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}, I_{\text{D}} = 250\text{uA}$	2	3	4	V
Drain-to-source On-resistance	$R_{\text{DS}(\text{on})}^{\text{C}}$	$V_{\text{GS}} = 10\text{V}, I_{\text{D}} = 5.5\text{A}$		0.31	0.38	$\Omega$
<b>DYNAMIC PARAMETERS</b>						
Input Capacitance	$C_{\text{iss}}$	$V_{\text{GS}} = 0 \text{ V}, f = 1.0 \text{ MHz}, V_{\text{DS}} = 400 \text{ V}$		813		pF
Output Capacitance	$C_{\text{oss}}$			19.6		
Reverse Transfer Capacitance	$C_{\text{rss}}$			1		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{GS}} = 10 \text{ V}, V_{\text{DS}} = 400 \text{ V}, I_{\text{D}} = 11\text{A}$		23		nC
Gate-to-Source Charge	$Q_{\text{GS}}$			6		
Gate-to-Drain Charge	$Q_{\text{GD}}$			9		
Gate resistance	$R_g$	$V_{\text{GS}}=0\text{V}, F=1\text{MHZ}, \text{drain open}$		6.5		$\Omega$
<b>SWITCHING CHARACTERISTICS</b>						
Turn-On Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{GS}} = 10\text{V}, V_{\text{DS}} = 400 \text{ V}, I_{\text{D}} = 5.5\text{A}, R_{\text{G}}=10 \Omega$		11.5		ns
Rise Time	$t_r$			23.5		
Turn-Off Delay Time	$t_{\text{d}(\text{off})}$			43		
Fall Time	$t_f$			21.5		
<b>Drain to Source Diode Characteristics and Maximum Ratings</b>						
Forward Voltage	$V_{\text{SD}}$	$V_{\text{GS}} = 0 \text{ V}, I_{\text{S}} = 5.5\text{A}$			1.5	V
Body-Diode Continuous Current	$I_{\text{S}}$				11	A
Body-Diode Pulsed Current	$I_{\text{SM}}$				27	A
Body Diode Reverse Recovery Time	$T_{\text{rr}}$	$I_{\text{F}}=5.5\text{A}, dI/dt=100\text{A/us}, V_{\text{DS}}=400\text{V}$		240		nS
Body Diode Reverse Recovery Charge	$Q_{\text{rr}}$			1.8		$\mu\text{C}$
Peak reverse recovery Current	$I_{\text{rrm}}$			14.9		A


### NOTES:

- A. Drain current limited by maximum junction temperature. Maximum duty cycle D=0.75
- B. L=100mH,  $I_{\text{AS}}=1.8\text{A}$ ,  $V_{\text{DD}}=50\text{V}$ , Starting  $T_J=25^\circ\text{C}$
- C. Pulse Test: Pulse width  $\leq 300\text{us}$ , Duty Cycle  $\leq 2\%$  sensitively Independent of Operating Temperature Typical Characteristics
- D. These tests are performed with the device mounted on 1 in<sup>2</sup> FR-4 board with 2oz. Copper, in a still air environment with  $T_A=25^\circ\text{C}$ .


**Typical Characteristics ( $T_A=25^\circ\text{C}$ , unless otherwise noted)**




**Output characteristics**




**Transfer characteristics**




**On-Resistance vs. Drain current**




**On-Resistance vs. Junction temperature**




**Breakdown Voltage vs. Junction temperature**




**Threshold voltage vs. Junction temperature**




**Body diode forward voltage**




**Cossstored Energy**







**Capacitance**



**Gate charge Characteristics**




**Power dissipation**



## PACKAGE OUTLINE DIMENSIONS

**TO-220F-3L**



TOP VIEW


SIDE VIEW

BOTTOM VIEW

Symbol	Dimensions in Millimeters		
	Min.	Typ.	Max.
A	4.50	4.72	4.90
A1	2.45	2.56	2.65
A2	0.72Ref		
A3	2.68	2.78	2.88
A4	-	-	0.45
b	0.70	0.80	0.90
b1	1.18	1.28	1.38
c	0.45	0.52	0.60
D	15.67	15.87	16.07
D1	15.55	15.75	15.95
E	9.96	10.16	10.36
e	2.45BSC		
H1	6.48	6.68	6.88
L	12.68	12.98	13.28
L1	-	-	3.50
L2 2.54BSC			
φP	3.08	3.18	3.28
Q	3.20	-	3.40
θ	3°	5°	7°

## PACKAGE OUTLINE DIMENSIONS

**TO-252E-2L**




Symbol	Dimensions in Millimeters		
	Min.	Typ.	Max.
A	2.20	2.30	2.40
A1	0	0.08	0.15
b	0.50	0.60	0.70
b2	0.60	0.75	0.90
b3	5.20	5.35	5.50
c2	0.45	0.50	0.55
c	0.51Ref		
D	5.40	5.60	5.80
D1	4.57	-	-
E	6.40	6.60	6.80
E1	3.81	-	-
e	2.30Ref		
F	0.70	0.80	0.90
H	9.40	9.80	10.20
L	1.40	1.59	1.77
L1	2.40	2.70	3.00
L4	0.80	1.00	1.20


## TAPE AND REEL INFORMATION

### TO-252E-2L


#### Reel Dimensions



#### Tape Dimensions



#### Quadrant Assignments For PIN1 Orientation In Tape



RD	Reel Dimension	<input type="checkbox"/> 7inch <input checked="" type="checkbox"/> 13inch
W	Overall width of the carrier tape	<input type="checkbox"/> 8mm <input type="checkbox"/> 12mm <input checked="" type="checkbox"/> 16mm
P1	Pitch between successive cavity centers	<input type="checkbox"/> 2mm <input type="checkbox"/> 4mm <input checked="" type="checkbox"/> 8mm
Pin1	Pin1 Quadrant	<input type="checkbox"/> Q1 <input checked="" type="checkbox"/> Q2 <input type="checkbox"/> Q3 <input type="checkbox"/> Q4